

Threaded Conduit Hubs

For RMC and IMC

NEC/CEC — Suitable for hazardous locations:
 Class I, Division 2; Class III, Divisions 1 and 2 per NEC 501-4(B), 501.10(B)(4), 502-4(A)(2), 503-3(A)

Applications

- Insulated throat form with bonding screw.
- Provides a more vibration resistant connection with assured ground continuity

Features


- Female bushed nipple type
- Female thread for rigid conduit and IMC
- Takes less space
- Recessed O-ring seal outside the box provides a watertight threaded hub on enclosures.
- Suitable for use with service entrance conduit.

Material/Finish

- Ductile iron/zinc electroplate
- Gasket: neoprene

NEC/CEC Certifications and Compliances


- UL Standard: ANSI/UL 514B
- UL Listed: E-11853
- CSA Standard: C22.2 No. 18
- CSA Certified: 009795
- UL Listed as suitable for use in wet locations.
- NEMA: FB-1, -4, and -12.



HUB-125

APPLETON™

COMMERCIAL AND INDUSTRIAL FITTINGS: RIGID AND IMC CONDUIT FITTINGS

	Trade Size (Inches)	Hole Diameter in Millimeters (Inches)		Panel Thickness in Millimeters (Inches)		Dimensions in Millimeters (Inches)		Weight per 100 kg (lb)	Appleton™ Catalog Number
		Max.	Min.	Max.	Min.	A	B		
	1/2	22.4	23.9	1.5	2.0	27.4	28.2	7.26	HUB-50
		(0.88)	(0.94)	(0.06)	(0.08)				
		24.6	2.3	6.4					
	3/4	27.7	29.5	1.5	2.0	28.2	35.1	10.43	HUB-75
		(1.09)	(1.16)	(0.06)	(0.08)				
		31.0	2.3	6.4					
	1	34.0	35.8	1.5	2.0	31.8	43.7	17.69	HUB-100
		(1.34)	(1.41)	(0.06)	(0.08)				
		37.3	2.3	6.4					
			(1.47)	(0.09)	(0.25)				

