

EF and FHS Series Flexible Fixture Hangers

Hook and Loop

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

CEC:
Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of lighting fixtures.

Features

- Protect fixture against wind and vibration damage.
- EF hook and loop hangers
 - Malleable iron for strength and safety.
 - Hook and loop combination permits quick disconnect and removal of fixture for maintenance.
 - Offer inexpensive means of pendant flexible suspension of lighting fixtures.
 - Permit free swing in any direction.
 - EF jaw openings can be completely closed for added safety.
- FHS support hangers
 - Provide up to 75.3 kg (166 lbs) support for fixtures on the non-electrical side of mounting.
 - Straddle a maximum of 1-1/4" conduit and accepts 1/2" or 3/4" fixture hook or conduit.

Standard Materials

- Malleable iron

Standard Finishes

- Zinc electroplate and clear chromate



EFHM



EFHF




FHS

CEC Certifications and Compliances

- CSA Certified: 065180

POLES/HANGERS: NEC/CEC ORDINARY LOCATION FLEXIBLE FIXTURE HANGERS


	Size (Inches)	Length A mm (in)	Support Weight kg (lbs)	Catalog Number
EF – Safety Support Hooks – With 3/8" jaw opening				
	EFHM – Male			
	1/2	66.8 (2.63)	40.9 (90)	EFHM-50
	3/4	74.7 (2.94)		EFHM-75
	EFHF – Female			
1/2	50.8 (2.00)	40.9 (90)	EFHF-50	
3/4	52.1 (2.05)		EFHF-75	

FHS – Support for Fixtures, Dummy Side – Straddles up to 1-1/4 trade size conduit – 11/32" diameter mounting holes, spaced 3-1/4" apart



1/2 or 3/4	87.1 (3.31)	75.3 (166)	FHS5075
------------	-------------	------------	----------------

Dimensions in Millimeters (Inches)

	A	B	C	Catalog Number
	EFHM – Male			
	1/2-14 NPT	50.8 (2.00)	66.8 (2.63)	EFHM-50
	3/4-14 NPT	54.1 (2.13)	73.2 (2.88)	EFHM-75
EFHF – Female				
	1/2-14 NPT	50.8 (2.00)	N/A	EFHF-50
	3/4-14 NPT	54.1 (2.13)	N/A	EFHF-75