

Threaded Conduit Hubs With Bonding Screw For RMC and IMC

NEC/CEC — Suitable for use in:
Class I, Division 2

Applications

- Provides threaded termination in sheet metal enclosures.
- Suitable for service entrance.
- General purpose fitting.

Features

- Bonding locknut.
- Insulated throat.
- Recessed neoprene O-ring to assure water and dust-tight connections.

Material/Finish

- Body/wedge: ductile iron, zinc electroplate
- Locknut: 1/2 thru 1, 5 thru 6: steel, zinc electroplate
- Screw: steel, zinc electroplate
- O-ring: neoprene
- Liners: nylon



NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-11853
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 065178
- NEMA: FB-1

Trade Size (Inches)	Dimensions in Millimeters (Inches)		Weight per 100 kg (lb)	Catalog Number	
	A	B			
1/2	22.35 (0.88)	38.10 (1.50)	5.81 (12.80)	HUB-50B	
3/4	25.40 (1.00)	44.45 (1.75)	8.35 (18.40)	HUB-75B	
1	28.70 (1.13)	50.80 (2.00)	14.15 (31.20)	HUB-100B	
1 - 1/4	31.75 (1.25)	60.45 (2.38)	26.94 (59.40)	HUB-125B	
1 - 1/2	31.75 (1.25)	69.85 (2.75)	33.38 (73.60)	HUB-150B	
2	31.75 (1.25)	82.55 (3.25)	5.36 (100.00)	HUB-200B	
2 - 1/2	41.40 (1.63)	98.55 (3.88)	83.64 (184.40)	HUB-250B	
3	44.45 (1.75)	117.60 (4.63)	117.66 (259.40)	HUB-300B	
3 - 1/2	47.75 (1.88)	130.30 (5.13)	143.15 (315.60)	HUB-350B	
4	47.75 (1.88)	143.00 (5.63)	165.83 (365.60)	HUB-400B	
5	54.10 (2.13)	174.75 (6.88)	317.51 (700.00)	HUB-500MB	
6	54.1 (2.13)	206.5 (8.13)	415.49 (916.00)	HUB-600MB	