

Mercmaster™ Jr. Luminaires

High Pressure Sodium. Suitable for Use in Wet Locations

UNILETS® for Use with Threaded Metal Conduit. 120 V Integral Ballast. Medium Base Socket for Medium Base Lamps.

NEC:

With Globe:

35 W, 50 W:

Class I, Division 2, Groups A, B, C, D

Class II, Division 1 and 2, Groups E ②, F, G

Class III

NEC:

70 W: ①

Class I, Division 2, Groups A, B, C, D

Class II, Division 1 and 2, Groups E ②, F

100 W, 150 W: ①

Class I, Division 2, Groups A, B, C, D

NEC:

With Refractor (NEMA V):

35 W, 50 W, 70 W, 100 W:

Class I, Division 2, Groups A, B, C, D

Class II, Division 1 and 2, Groups E ②, F, G

Class III

NEC:

150 W: ①

Class I, Division 2, Groups A, B, C, D

Applications

- Inexpensive HID integrally ballasted fixture for use in hazardous locations – inexpensive to buy and inexpensive to operate (uses one-fifth as much electrical energy as incandescent and three-quarters as much as fluorescent).
- Enclosed and gasketed HID lighting fixtures for use in tunnels, walkways, bridges, storage facilities, processing plants, parking lots, foundries, manufacturing plants, power plants and other locations where moisture, dirt, dust or corrosive atmospheres are encountered.

Features

- “Wireless” design. Threading of fixture unit onto mounting hood makes electrical connection. Only wiring required is attaching two wires to connection block in mounting hood.
- Safe, easy servicing without disconnecting any wiring. “Wireless” fixture unit easily threads off mounting hood for convenient servicing.
- Quick, easy conversion from Appleton V-51® incandescent installation to Mercmaster Jr. HID. Just remove V-51® fixture unit and thread Mercmaster Jr. fixture unit onto existing V-51® mounting hood.
- Choice of mounting hoods. Standard fixtures in pendant, ceiling, outlet box, wall and stanchion mountings.
- Standard pendant mounting hood for rigid or flexible mounting. Balanced round design automatically hangs plumb when used with flexible hanger.
- Unitized construction reduces installation and maintenance costs.
- Ballast has standard non-PCB biodegradable capacitors.
- Medium base socket is furnished with 200 °C (392 °F) leads, prewired to the ballast. Porcelain socket assures trouble-free operation in high ambient installations.
- Prismatic glass globe or glass refractor is standard and threads directly into fixture housing. Eliminates glare and provides uniform light distribution.
- Fiberglass reinforced polyester reflector for exceptionally severe corrosive atmospheres. Vented for cooler, dirt-free operation, increased lumen output.

Standard Materials

- Mounting hoods: copperfree (4/10 of 1% max.) aluminum or malleable iron
- Ballast bodies: copperfree (4/10 of 1% max.) aluminum
- Guards: copperfree (4/10 of 1% max.) aluminum or steel
- Reflectors: fiberglass reinforced polyester or porcelain
- Globe: 35 W-100 W, threaded prismatic glass and threaded polycarbonate; 150 W, threaded heat-resistant prismatic glass
- Refractor: heat-resistant prismatic glass

Standard Finishes

- Ballast bodies, aluminum guard and VMA, VXHA-A, OBWV1-A, OBV1-A, JBW1-A, JB1-A, GSW2 and MS mounting hoods: epoxy powder coat finish, electrostatically applied for complete, uniform surface protection
- VA, VXHA, OBWV1, OBV1, GS-2, JBW1, and JB1 malleable iron mounting hoods: triple coat – (1) zinc electroplate; (2) chromate; and (3) epoxy powder coat
- Steel guard: zinc electroplate



Illustrated Feature

Conversion from Appleton V-51 incandescent installation to HID Mercmaster Jr. is easy and fast.



Step No. 1:

After power is shut off, remove present incandescent V-51 fixture unit from existing V-51 mounting hood.



Step No. 2:

Thread Mercmaster Jr. HID fixture unit onto existing V-51 mounting hood – and conversion is completed.

Options

- Fuses for fixtures, factory installed. Add suffix -F.

NEC Certifications and Compliances

- UL Standard: UL 1598, UL 1598A, UL 844
- UL Listed: E10444

① The MJBW Wall Mount Fixture is suitable for Class I, Division 2, Groups A, B, C and D only.

② Per NEC 500.6(1), there is no such classification as Class II, Division 2, Group E.

Mercmaster™ Jr. Luminaires

High Pressure Sodium. Suitable for Use in Wet Locations

UNILETS® for Use with Threaded Metal Conduit. 120 V Integral Ballast. Medium Base Socket for Medium Base Lamps.

NEC:
With Globe:
35 W, 50 W:
Class I, Division 2, Groups A, B, C, D
Class II, Division 1 and 2, Groups E ②, F, G
Class III

NEC:
70 W: ①
Class I, Division 2, Groups A, B, C, D
Class II, Division 1 and 2, Groups E ②, F
100 W, 150 W: ①
Class I, Division 2, Groups A, B, C, D

NEC:
With Refractor (NEMA V):
35 W, 50 W, 70 W, 100 W:
Class I, Division 2, Groups A, B, C, D
Class II, Division 1 and 2, Groups E ②, F, G
Class III

NEC:
150 W: ①
Class I, Division 2, Groups A, B, C, D

Thermal Suitability

Table at below shows maximum operating temperatures of Mercmaster Jr. fixtures for Class I, Division 2, in a 40 °C (104 °F) ambient. Per NEC 500.8(B)(4), the temperature marking on fixtures shall not exceed the ignition temperature of the specific gas or vapor to be encountered. NEC 500.8(B)(4) states that these markings (Identification Numbers) "marked on equipment nameplates shall be in accordance with Table NEC 500.8(C)." This NEC table is duplicated, as it applies to Appleton Mercmaster Jr. fixtures, in the table below.

As shown, the higher the Temperature Identification Number, the cooler the fixture operates. Keep this in mind when selecting a fixture for a specific gas or vapor.

Example:

- Gasoline (56-60 octane)
- Fixture with Globe and Reflector

To determine Mercmaster Jr. thermal suitability for the above example:

- (1) Check the Thermal Suitability on the following page for ignition temperature of gas or vapor to be encountered. It reveals that 56-60 octane gasoline has an ignition temperature of 280 °C (536 °F).
- (2) Look in table below for fixtures under "With Globe and Reflector" that do not exceed the 280 °C (536 °F) ignition temperature of the gasoline.
- (3) Select the best fixture for your purpose. The 35 W, 50 W, 70 W or 100 W fixture with globe and reflector is acceptable because none of these fixture lamp surfaces exceed the 280 °C (536 °F) ignition temperature of the gasoline.

Temperature Identification Numbers

Class I, Division 2, Groups A, B, C and D					Class II, Division 1 and 2, Groups E, F and G		
With Globe or with Globe and Reflector			With 8" Refractor		With Globe, with Globe and Reflector, or with 8" Refractor		
Lamp Watts	Name—plate Marking	Temperature Range °C (°F)	Nameplate Marking	Temperature Range °C (°F)	Nameplate Marking	Temperature Range °C (°F)	Groups
35	T4	121-135 (250-275)	T4	121-135 (250-275)	T4C	101-120 (214-248)	E, F, G
50	T2D	201-215 (394-419)	T3	181-200 (358-392)	T3C	136-160 (277-320)	E, F, G
70	T2B	231-260 (448-500)	T2C	216-230 (421-446)	T3B	161-165 (322-329)	E, F, G ③
100	T2A	261-280 (502-536)	T2B	231-260 (448-500)	—	—	E, F, G ④
150	T2	281-300 (538-572)	T2A	261-280 (502-536)	—	—	—

Ambient Suitability of Mercmaster Jr. Fixtures

All fixtures suitable for operation at -40 °C (-40 °F).

35W	50W	70W	100W	150W
40 °C (104 °F)	40 °C (104 °F)	25 °C (77 °F)	25 °C (77 °F)	25 °C (77 °F)

Retrofits Incandescent Fixtures Easily and Quickly

- 35 W HPS Comparable to 100/150 W Incandescent Lamp
- 50 W HPS Comparable to 200 W Incandescent Lamp
- 70 W HPS Comparable to 300 W Incandescent Lamp
- 100 W HPS Comparable to 1.5 300 W Incandescent Lamp ⑤
- 150 W HPS Comparable to 2.5 300 W Incandescent Lamp ⑤

Electrical Specifications (Reactor Ballasts)

Lamp Watts	Line Voltage 60 Hz	Line Current in Amperes		Input Watts
		Starting HPF	Operating HPF	
35	120	0.41	0.38	43
50	120	0.62	0.56	60
70	120	0.70	0.73	82
100	120	1.10	1.00	115
150	120	1.70	1.50	170

Optional Factory-Installed Fuses – Add Suffix -F

Available as a factory installed item with Mercmaster Jr. fixtures.

① The MJBW Wall Mount Fixture is suitable for Class I, Division 2, Groups A, B, C and D only.

② Per NEC 500.6(1), there is no such classification as Class II, Division 2, Group E.

③ 70W suitable for Groups E and F with globe; suitable for Groups E, F, and G with refractor.

④ 100W suitable for Groups E, F and G with refractor only.

⑤ These are guidelines only. Light distribution and other factors must be taken into consideration.

Mercmaster™ Jr. Luminaires

35 W, 50 W, 70 W, 100 W, 150 W HPS

Complete with Mounting Hood. Medium Base Socket. High Power Factor (Min. P.F. 90%). Integral Ballast for 120 V Line Operation.

NEC:

With Globe:

35 W, 50 W:

Class I, Division 2, Groups A, B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEC:

70 W: ①

Class I, Division 2, Groups A, B, C, D

Class II, Division 1 and 2, Groups E, F, G

100 W, 150 W: ①

Class I, Division 2, Groups A, B, C, D

NEC:

With Refractor (NEMA V):

35 W, 50 W, 70 W, 100 W:

Class I, Division 2, Groups A, B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

NEC:

150 W: ①

Class I, Division 2, Groups A, B, C, D

With Globe, Less Guard	With Refractor (NEMA V)	Lamp Watts	ANSI Lamp Type	Hub Size (Inches)	Catalog Number ⑥	
Pendant — Aluminum mounting hood and ballast body. One Hub, Rigid or Flexible Mounting						
		35	S76	3/4 1	MA3575-120 MA3510-120	MA3575J-120 MA3510J-120
		50	S68	3/4 1	MA5075-120 MA5010-120	MA5075J-120 MA5010J-120
		70	S62	3/4 1	MA7075-120 MA7010-120	MA7075J-120 MA7010J-120
		100	S54	3/4 1	MA1075-120 MA1010-120	MA1075J-120 MA1010J-120
		150	S55	3/4 1	MA1575-120 MA1510-120	MA1575J-120 MA1510J-120
Ceiling — Aluminum mounting hood and ballast body. Five Hubs, Four Close-Up Plugs						
		35	S76	3/4 1	MC3575-120 MC3510-120	MC3575J-120 MC3510J-120
		50	S68	3/4 1	MC5075-120 MC5010-120	MC5075J-120 MC5010J-120
		70	S62	3/4 1	MC7075-120 MC7010-120	MC7075J-120 MC7010J-120
		100	S54	3/4 1	MC1075-120 MC1010-120	MC1075J-120 MC1010J-120
		150	S55	3/4 1	MC1575-120 MC1510-120	MC1575J-120 MC1510J-120
Wall ⑥ — Malleable iron mounting hood and aluminum ballast body. Gasket and screws furnished with fixture. Fits GSU Cast Boxes						
		35	S76	—	MGSW35-120	MGSW35J-120
		50	S68	—	MGSW50-120	MGSW50J-120
		70	S62	—	MGSW70-120	MGSW70J-120
		100	S54	—	MGSW10-120	MGSW10J-120
		150	S55	—	MGSW15-120	MGSW15J-120
Wall ⑥⑥ — Class I, Division 2 only. Aluminum mounting hood and ballast body. Gasket and screws furnished with fixture. Fits JBX Cast Boxes						
		35	S76	—	MJBW35-120	MJBW35J-120
		50	S68	—	MJBW50-120	MJBW50J-120
		70	S62	—	MJBW70-120	MJBW70J-120
		100	S54	—	MJBW10-120	MJBW10J-120
		150	S55	—	MJBW15-120	MJBW15J-120
25° Stanchion ⑥ — Aluminum mounting hood and ballast body. One hub						
		35	S76	1-1/4 1-1/2	MS35125-120 MS35150-120	MS35125J-120 MS35150J-120
		50	S68	1-1/4 1-1/2	MS50125-120 MS50150-120	MS50125J-120 MS50150J-120
		70	S62	1-1/2 1-1/2	MS70125-120 MS70150-120	MS70125J-120 MS70150J-120
		100	S54	1-1/4 1-1/2	MS10125-120 MS10150-120	MS10125J-120 MS10150J-120
		150	S55	1-1/4 1-1/2	MS15125-120 MS15150-120	MS15125J-120 MS15150J-120

① Per NEC 500.6(1), there is no such classification as Class II, Division 2, Group E.

② The MJBW Wall Mount Fixture is suitable for Class I, Division 2, Groups A, B, C and D only.

③ All fixtures on this page comply with UL Standard 844 except MJBW Wall Mount Fixture, which is not suitable for Class II, Division 1.

④ Using cast outlet box with Wall Mount Fixture provides the following clearances: for the globe – JBX box, 1-5/8" from wall; GSU box, 2" from wall; for the refractor – JBX box, 15/16" from wall; GSU box, 1-5/16" from wall. Reflectors cannot be used with the wall mount fixtures.

⑤ Stanchion Mount can be used with standard dome or 30° angle reflector.

⑥ To order fixture with guard, add -G before voltage (example: MA3575G-120).

Mercmaster™ III Low Profile Luminaires

High Pressure Sodium and Pulse Start Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.


NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Mercmaster III Low Profile Family Tree



① Mounting hood with a 120 V or 208-277 V factory installed photocell is available.

② Standard and deep dome reflectors may interfere with bottom conduit entry if used with KPST and KPWB mounting hoods..

③ Available in clear, amber, blue, green and red.

④ Available in NEMA Type II, III, IV and V. Polymeric Refractor suitable for Class II, Groups F and G, NEMA 4X and Marine Type Electric Fixtures Outside Type (Salt Water) only (100 W PSMH Max.).

⑤ Available in NEMA Type I, III and V.

Mercmaster™ III Low Profile Compact Fluorescent Luminaires

Enclosed and Gasketed. For Hazardous and Wet Locations

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure (Class I, Division 2/
Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

CEC:

Class I, Zone 2, Ex nR IIC (Z)

Order using catalog numbering guide below or select catalog number from tables on following pages.

Catalog Numbering Guide For Zone 2 Mercmaster III Compact Fluorescent Luminaires

ML	A	F	84	2	G2	G	BU	L	Z2
Series: ML - Mercmaster III Low Profile	Lamp Type: F - Fluorescent			Hub Size: 2 - 3/4" NPT 3 - 1" NPT 4 - 1-1/4" NPT Stanchion 5 - 1-1/2" NPT Stanchion		Guard Options: G - Cast Guard (Glass Refractor and Globe only) N - No Guard		Lamp Options: L - Lamp(s) included Blank - Lamp(s) excluded	
Mounting Hood: A - Pendant (Rigid or Flexible) C - Ceiling D - Pendant Cone R - 90° Stanchion S - 25° Stanchion W - Wall	Wattage: 26 - One 26 Watt PL-T 32 - One 32 Watt PL-T 42 - One 42 Watt PL-T 52 - Two 26 Watt PL-T 57 - One 57 Watt PL-T ④ 64 - Two 32 Watt PL-T 84 - Two 42 Watt PL-T 114 - Two 57 Watt PL-T ④	Optical Assembly: ① G2 - VPGL2HR Globe (not for 57, 114 Watt) G4 - VPGL4HR Globe (57, 114 Watt only) ④ J1 - NEMA I Glass Refractor J3 - NEMA III Glass Refractor J5 - NEMA V Glass Refractor P2 - NEMA II Polymeric Refractor P3 - NEMA III Polymeric Refractor P4 - NEMA IV Polymeric Refractor P5 - NEMA V Polymeric Refractor	Voltage: BU - 120 to 277 V, 50/60 Hz and 125 Vdc A5 - 347 V, 60 Hz ④	Suffix: DP - Safety Cable SC - Safety Chain Z2 - Zone 2 Suffix (Required for AEx nA nR rating) C - Safety Cable ④ F - Fused Mtg. Hood ③④ (Non-Haz. Loc. only) P - Non-Haz. Photocell (Specify Voltage) ④ Q - Division 2 Haz. Photocell (Specify Voltage) ④ T - Terminal Blocks ④ V - Vibration Protection ④ X - Appledapter ② Mounting Hood Adapter ④ Z - Zone 2 suffix (required for Ex nR) ④					

① Polymeric refractors suitable for Class II, Groups F and G; NEMA 4X; and Marine Type Electric Fixture Outside Type (Salt Water) only.

Reflectors ordered separately (for use with globe fixtures only): Standard Dome: KR2-ST 30-degree Angle: KR2-AN

② Appledapter is available for use with the pendant, ceiling and angled stanchion mounting only.

③ Canadian Electrical Code (CEC) does NOT allow fusing in hazardous locations.

④ Certified to meet the Canadian Electrical Code (CEC) only.