

Mercmaster™ III Low Profile Luminaires

High Pressure Sodium and Pulse Start Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Order using catalog numbering guide below or select catalog number from tables on following pages.

Catalog Numbering Guide

ML	A	L	15	2	G1	G	MT	R	Z2
Series: ML - Mercmaster III Low Profile		Lamp Type: I - Incandescent L - High Pressure Sodium P - Pulse Start Metal Halide		Hub Size: 2 - 3/4" NPT 3 - 1" NPT 4 - 1-1/4" NPT stanchion 5 - 1-1/2" NPT stanchion		Guard Options: G - Cast Guard N - No Guard		Options: E - Emergency Quartz ⑤ F - Fuse Kit (Specify Voltage) R - Hot Restrike ③ S - Smart Starter ④ H1 - Photocontrol 120 V H2 - Photocontrol 208 V H3 - Photocontrol 240 V H4 - Photocontrol 277 V D - E-27 Export Socket <i>Optional Fusing</i> ⑥ FN - 120 V FP - 208 V FS - 240 V FT - 277 V FF - 480 V	
	Mounting: A - Pendant (rigid mounting) C - Ceiling D - Pendant Cone Hood F - Pendant (flexible mounting) R - 90° Stanchion S - 25° Stanchion W - Wall	Wattage: 10 - 100 W HPS, PSMH 15 - 150 W HPS, PSMH and 60-150 W max. Incandescent 17 - 175 W PSMH 50 - 50 W HPS, PSMH 70 - 70 W HPS, PSMH		Optical Assembly: ② G1 - Globe J1 - NEMA I Glass Refractor J3 - NEMA III Glass Refractor J5 - NEMA V Glass Refractor P2 - NEMA II Polymeric Refractor P3 - NEMA III Polymeric Refractor P4 - NEMA IV Polymeric Refractor P5 - NEMA V Polymeric Refractor		Voltage: ① LB - Incandescent, 120, 60 Hz MT - 120/208/240/277, 60 Hz 5MT - 120/208/240/ 277/480, 60 Hz 48 - 480, 60 Hz 125 - 120, 50 Hz 225 - 225, 50 Hz 226 - 220, 60 Hz 236 - 230, 60 Hz 245 - 240, 50 Hz 246 - 240, 60 Hz		Suffix: Z2 - Zone 2 suffix (required for AEx nA nR rating) ZB - Zone 2 suffix (required for AEx nR)	

① Other voltages, frequencies available – contact your local sales representative. Voltages shown are limited to specific combinations; refer to following pages.

② Polymeric Refractor suitable for Class II, Groups F and G, NEMA 4X and Marine Type Electric Fixtures Outside Type (Salt Water) only (100 W PSMH Max.). Reflectors ordered separately.

③ Available for 50-150 W HPS fixtures only.

④ Available for HPS or PSMH fixtures.

⑤ Fixtures equipped with quartz auxiliary lamp do not comply with NEC/CEC requirements and are not suitable for use in classified locations

⑥ Optional fusing is available for use with MT, 5MT and 48 voltage suffixes ONLY.

Mercmaster™ III Low Profile Compact Fluorescent Luminaires

Enclosed and Gasketed. For Hazardous and Wet Locations

Compact Fluorescent listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure (Class I, Division 2/
Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

CEC:

Class I, Zone 2, Ex nR IIC (Z)

Applications

- Enclosed and gasketed fixtures suitable for use in marine and wet locations, and in a wide range of industrial, chemical processing and other areas where flammable gases and vapors or combustible dusts are present under conditions defined by the National Electrical Code as Class I, Division 2; Class II, Division 1 and 2; and Class III. The method of protection for the Zone 2 Mercmaster is AEx nA nR – Restricted Breathing/Nonsparking.
- For use in areas of low clearance, low ceiling heights or where fixture weights must be minimized.
- Suited for use in non-hazardous locations where severe weather conditions, excessive moisture, dirt, dust or corrosive atmospheres are present.
- Typical applications include oil refineries, pulp and paper mills, chemical plants, food-processing areas, inspection facilities, foundries, power plants, storage areas, waste and sewage treatment, parking garages, and other areas where dust, water, dirt and rough usage are a problem.

Features

- Energy-efficient, compact fluorescent light sources possess superior lamp efficiency.
- Fluorescent provides long lamp life, thereby reducing relamping costs.
- “Instant on” nature of this electronically ballasted fluorescent eliminates the possibility of an extended blackout due to a momentary power dip.
- High efficacies (up to 75 lumens per Watt) offer a desirable low-glare/instant-on alternative to low wattage HID sources.
- High output under widely varying conditions: Greater than 90% of rated lumens in ambient temperatures from -5 °C to +54 °C (+23 °F to +130 °F).
- Excellent color rendering (82 CRI) makes it the best choice for food processing and inspection facilities.
- A wide variety of lamp wattages: 26 W, 32 W, 42 W, 52 W, 64 W, 84 W.
- Electronic ballast permits low operating costs with power factor greater than 99%. Also allows flicker-free starting.
- Cold weather starting to a minimum temperature of -18 °C (0 °F).
- Fixtures are available for operation from an external 125 Vdc source.
- Compact, light-weight low profile design creates ease of installation and maintenance.
- Modular design, with multiple mounting hoods, optics and reflectors, permits a wide array of fixtures to meet installation and lighting needs.
- Body gaskets and optic gaskets are high temperature silicone O-Rings that provide superior sealing.
- Mounting hoods have a high hinge for added safety during installation and servicing.
- Choice of heat-resistant prismatic glass refractor (NEMA I, III or V), heat-resistant clear globes, color globes or polymeric refractors (NEMA II, III, IV or V). (Polymeric refractors are not listed for Zone 2.)



Pendant Mount Fixture
with Glass Globe



Ceiling Mount Fixture with
Prismatic Glass Refractor

Standard Materials

- Standard dome or 30° angle reflectors: highly reflective fiberglass reinforced white polyester to provide strength, corrosion resistance and excellent photometrics
- Fixture housing, mounting hoods, and guards: die-cast, copperfree (4/10 of 1% max.) aluminum with epoxy finish for corrosion resistance
- Exposed hardware: stainless steel. Latch assemblies have stainless steel bolt and captive nut; reflectors and guards attach with stainless steel screws threading into stainless steel inserts
- Globes and glass refractors: heat-resistant prismatic glass
- Polymeric refractor: spun aluminum reflector and a lens made of an engineered thermoplastic

Standard Finishes

- Epoxy powder coat finish electrostatically applied for complete, uniform surface protection

Options

- Fuse can be field installed. Kits include fuse block, wire connectors and screws for attachment to mounting hood.
 - Fixtures with fuses do not comply with UL 1598A for marine listing
 - Canadian Electrical Code does NOT allow fusing in hazardous locations
- Guards with gray epoxy painted to match fixtures, supplied with stainless steel screws. Add suffix **-G**.
- Reflectors are available as standard dome and 30° angle polyester. Order separately.

NEC/CEC Certifications and Compliances

- UL Standard: UL 1598, UL 1598A, UL 844, UL 60079-0, UL 60079-15
- UL Listed: E10444
- CSA Standard: C22.2 No. 250, C22.2 No. 137, CAN E60079-0, CAN E60079-15
- CSA Certified: 025428

Mercmaster™ III Low Profile Compact Fluorescent Luminaires

Enclosed and Gasketed. For Hazardous and Wet Locations

Compact Fluorescent listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure (Class I, Division 2/
Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

CEC:

Class I, Zone 2, Ex nR IIC (Z)

Illustrated Features



Globe Chamber

Completely sealed from the ballast housing and outside vapors/air (nA nR).

Epoxy Finish

Ballast housing, hoods and guards are copperfree aluminum with epoxy powder coat finish.

Photocell

Installs through knock-out in mounting hoods except cone and ceiling mount. Provides continuous on-off dusk-to-dawn control. Not for use in hazardous (classified) areas. Hazardous location rated photocells also available. See Accessories page.



Stainless Steel Latch Assembly

Captive, stainless steel latch assembly bolt and nut closes securely, resists attack of corrosive atmospheres. Swing-away design simplifies servicing.



Vented Reflectors

Reflectors are thick, tough fiberglass-reinforced white polyester, vented for cooler operation. Quickly attach with furnished stainless steel screws.

Terminal Blocks (Zone 2)

A seven-point terminal block is provided to facilitate wiring. Terminal block accommodates wire size ranging from #8 to #24 AWG.

Stainless Steel Inserts

Ballast bodies have stainless steel threaded inserts to receive stainless steel screws for reflectors and guard. Prevents "freezing", allowing guards and reflectors to be easily removed and replaced at any time, without damage to the housing.

Prismatic Glass Globes and Refractors

Heat-resistant globes and glass refractors and polymeric refractors thread directly into ballast housing and seal against a high temperature silicone rubber gasket. (Polymeric refractors are not listed for Zone 2 areas.)



Ballast Assembly

Utilizing non-sparking components avoiding the ignition of gases or vapors that may be present (nA).

Hood/Ballast Gasket

Silicone rubber gasket seals out moisture, dirt and dust. Stays flexible, withstands high temperatures. Closure design assures uniform gasket compression.

Electrical Protection

Ground wire provided to bond mounting hood to ballast housing.



Cooler Operating Cone Hood

Larger sloped surface sheds dusts, dirt and combustible fibers providing better heat dissipation.



Fuses

Two screws secure fuse kit to mounting boss in any Mercmaster mounting hood. Fuse included.



"Safety" High Hinge

Extra-high hinge provides additional protection against accidental ballast housing disengagement during installation or maintenance.



Mercmaster™ III Low Profile Compact Fluorescent Luminaires

Enclosed and Gasketed. For Hazardous and Wet Locations

Compact Fluorescent listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class II, Division 1 and 2, Groups E, F, G
Class III


NEC/CEC:

Simultaneous Exposure (Class I, Division 2/
Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

CEC:

Class I, Zone 2, Ex nR IIC (Z)

Mercmaster III Low Profile Compact Fluorescent Family Tree



① Mounting hood with a 120 V or 208-277 V factory installed photocell is available.

② Standard and deep dome reflectors may interfere with bottom conduit entry if used with KPST and KPWB mounting hoods..

③ Available in clear, amber, blue, green and red.

④ Available in NEMA Type II, III, IV and V. Polymeric Refractor suitable for Class II, Groups F and G, NEMA 4X and Marine Type Electric Fixtures Outside Type (Salt Water) only (100 W PSMH Max.).

⑤ Available in NEMA Type I, III and V.

Mercmaster™ III Low Profile Compact Fluorescent Luminaires

Enclosed and Gasketed. For Hazardous and Wet Locations

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure (Class I, Division 2/
Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

CEC:

Class I, Zone 2, Ex nR IIC (Z)

Order using catalog numbering guide below or select catalog number from tables on following pages.

Catalog Numbering Guide For Zone 2 Mercmaster III Compact Fluorescent Luminaires

ML	A	F	84	2	G2	G	BU	L	Z2
Series: ML - Mercmaster III Low Profile		Lamp Type: F - Fluorescent		Hub Size: 2 - 3/4" NPT 3 - 1" NPT 4 - 1-1/4" NPT Stanchion 5 - 1-1/2" NPT Stanchion		Guard Options: G - Cast Guard (Glass Refractor and Globe only) N - No Guard		Lamp Options: L - Lamp(s) included Blank - Lamp(s) excluded	
Mounting Hood: A - Pendant (Rigid or Flexible) C - Ceiling D - Pendant Cone R - 90° Stanchion S - 25° Stanchion W - Wall		Wattage: 26 - One 26 Watt PL-T 32 - One 32 Watt PL-T 42 - One 42 Watt PL-T 52 - Two 26 Watt PL-T 57 - One 57 Watt PL-T ④ 64 - Two 32 Watt PL-T 84 - Two 42 Watt PL-T 114 - Two 57 Watt PL-T ④		Optical Assembly: ① G2 - VPGL2HR Globe (not for 57, 114 Watt) G4 - VPGL4HR Globe (57, 114 Watt only) ④ J1 - NEMA I Glass Refractor J3 - NEMA III Glass Refractor J5 - NEMA V Glass Refractor P2 - NEMA II Polymeric Refractor P3 - NEMA III Polymeric Refractor P4 - NEMA IV Polymeric Refractor P5 - NEMA V Polymeric Refractor		Voltage: BU - 120 to 277 V, 50/60 Hz and 125 Vdc A5 - 347 V, 60 Hz ④		Suffix: DP - Safety Cable SC - Safety Chain Z2 - Zone 2 Suffix (Required for AEx nA nR rating) C - Safety Cable ④ F - Fused Mtg. Hood ③④ (Non-Haz. Loc. only) P - Non-Haz. Photocell (Specify Voltage) ④ Q - Division 2 Haz. Photocell (Specify Voltage) ④ T - Terminal Blocks ④ V - Vibration Protection ④ X - Appledapter ② Mounting Hood Adapter ④ Z - Zone 2 suffix (required for Ex nR) ④	

① Polymeric refractors suitable for Class II, Groups F and G; NEMA 4X; and Marine Type Electric Fixture Outside Type (Salt Water) only.

Reflectors ordered separately (for use with globe fixtures only): Standard Dome: KR2-ST 30-degree Angle: KR2-AN

② Appledapter is available for use with the pendant, ceiling and angled stanchion mounting only.

③ Canadian Electrical Code (CEC) does NOT allow fusing in hazardous locations.

④ Certified to meet the Canadian Electrical Code (CEC) only.

Mercmaster™ III Low Profile Compact Fluorescent Luminaires

Class I, Division 2; Class II, Division 1; Simultaneous Exposure to Hazardous Conditions

Temperature identification numbers of Mercmaster III Low Profile Fluorescent Fixtures

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure (Class I, Division 2/
Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

CEC:

Class I, Zone 2, Ex nR IIC (Z)

Thermal Performance

Lamp Watts	Ambient Temp °C (°F) ①	Class I, Division 2				Class II, Division 1 Groups E, F and G ②				Simultaneous Exposure (Class I, Div 2 and Class II, Division 1)			
		Globe	Reflector	Glass Refractor	Polymeric Refractor	Globe	Reflector	Glass Refractor	Polymeric Refractor	Globe	Reflector	Glass Refractor	Polymeric Refractor
26	40 °C (104 °F)	T3	T3	T3	—	T5	T5	T5	T6	T3	T3	T3	—
32	40 °C (104 °F)	T3	T3	T3	—	T5	T5	T5	T6	T3	T3	T3	—
42	40 °C (104 °F)	T3	T3	T3	—	T5	T5	T5	T6	T3	T3	T3	—
52	40 °C (104 °F)	T2D	T2D	T3	—	T4A	T4A	T4A	T6	T2C	T2C	T2C	—
	55 °C (151 °F)	T2C	T2C	T2C	—	T4	T4	T4	—	T2C	T2C	T2C	—
57 ③	40 °C (104 °F)	T2D	T2D	T3	—	T4A	T4A	T4A	T6	—	—	—	—
64	40 °C (104 °F)	T2D	T2D	T3	—	T4A	T4A	T4A	T6	T2C	T2C	T2C	—
	55 °C (151 °F)	T2C	T2C	T2C	—	T4	T4	T4	—	—	—	—	—
84	40 °C (104 °F)	T2C	T2C	T2D	—	T3C	T3C	T3C	T6	T2B	T2B	T2B	—
114 ③	40 °C (104 °F)	T2C	T2C	T2D	—	T3C	T3C	T3C	T6	—	—	—	—

“T” Numbers Represent the Maximum Lamp Temperature for Class I, Division 2 Locations and Maximum Surface Temperature Under Dust Blanket for Class II, Division 1 Locations.

“T” Number	T1	350	325	T2	T2A	T2B	T2C	T2D	T3	T3A	T3B	T3C	T4	T4A	T5	T6
Temp. Range (°C)	351-450	326-350	301-325	281-300	261-280	231-260	216-230	201-215	181-200	166-180	161-165	136-160	121-135	101-120	86-100	85
Temp. Range (°F)	664-842	619-662	574-617	538-572	502-536	448-500	421-446	394-419	358-392	331-356	322-329	277-320	250-275	214-248	187-212	185

Lamp Watts	Supply Wire Temp. °C (°F)	Ambient Temp. °C (°F)	Class I, Zone 2, AEx nA nR — Ex nR		
			Globe	Globe and Reflector	Refractor
26	75 °C (167 °F)	40 °C (104 °F)	T5	T5	T6
32	75 °C (167 °F)	40 °C (104 °F)	T5	T5	T6
42	75 °C (167 °F)	40 °C (104 °F)	T5	T5	T6
52	75 °C (167 °F)	40 °C (104 °F)	T5	T5	T6
	75 °C (167 °F)	55 °C (131 °F)	T4	T4	T4
57 ③	75 °C (167 °F)	40 °C (104 °F)	T6	T6	T6
64	75 °C (167 °F)	40 °C (104 °F)	T5	T5	T6
	75 °C (167 °F)	55 °C (131 °F)	T4	T4	T4
84	75 °C (167 °F)	40 °C (104 °F)	T5	T5	T6
114 ③	75 °C (167 °F)	40 °C (104 °F)	T6	T6	T6

“T” Numbers Represent the Maximum Surface Temperature for Luminaires with AEx nA nR Rating

“T” Number	T1	T2	T3	T4	T5	T6
Temperature Range (°C)	301-450	201-300	136-200	101-135	86-100	85
Temperature Range (°F)	574-842	394-572	277-392	214-275	187-212	185

① Use +75 °C (+167 °F) rated supply wire.

② Fixtures with Polymeric Refractor are listed for Groups F and G only.

③ Certified to meet the Canadian Electrical Code (CEC) only.

Mercmaster™ III Low Profile Compact Fluorescent Luminaires

Enclosed and Gasketed. For Hazardous and Wet Locations

High Power Factor Electronic Ballast (Min. P.F. 99%), PL-T Lamps.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure (Class I, Division 2/
Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

CEC:

Class I, Zone 2, Ex nR IIC (Z)

		Catalog Numbers ②③		
Lamp Watts	Hub Size (Inches)	With Globe ①④	With Type V 8" Glass Refractor ①④⑤	With Type V Polymeric Refractor ⑥
Ceiling — Five Hubs, Four Close-Up Plugs				
	1 x 26 W	MLCF262G2N	MLCF262J5N	MLCF262P5N
	1	MLCF263G2N	MLCF263J5N	MLCF263P5N
	1 x 32 W	MLCF322G2N	MLCF322J5N	MLCF322P5N
	1	MLCF323G2N	MLCF323J5N	MLCF323P5N
	1 x 42 W	MLCF422G2N	MLCF422J5N	MLCF422P5N
	1	MLCF423G2N	MLCF423J5N	MLCF423P5N
	2 x 26 W	MLCF522G2N	MLCF522J5N	MLCF522P5N
	1	MLCF523G2N	MLCF523J5N	MLCF523P5N
	1 x 57 W	MLCF572G4N ⑦	MLCF572J5N ⑦	MLCF572P5N ⑦
	1	MLCF573G4N ⑦	MLCF573J5N ⑦	MLCF573P5N ⑦
	2 x 32 W	MLCF642G2N	MLCF642J5N	MLCF642P5N
	1	MLCF643G2N	MLCF643J5N	MLCF643P5N
	2 x 42 W	MLCF842G2N	MLCF842J5N	MLCF842P5N
	1	MLCF843G2N	MLCF843J5N	MLCF843P5N
Shown with Polymeric Refractor				
	2 x 57 W	MLCF1142G4N ⑦	MLCF1142J5N ⑦	MLCF1142P5N ⑦
	1	MLCF1143G4N ⑦	MLCF1143J5N ⑦	MLCF1143P5N ⑦
Wall Bracket — Five Hubs, Four Close-Up Plugs				
	1 x 26 W	MLWF262G2N	MLWF262J5N	MLWF262P5N
	1	MLWF263G2N	MLWF263J5N	MLWF263P5N
	1 x 32 W	MLWF322G2N	MLWF322J5N	MLWF322P5N
	1	MLWF323G2N	MLWF323J5N	MLWF323P5N
	1 x 42 W	MLWF422G2N	MLWF422J5N	MLWF422P5N
	1	MLWF423G2N	MLWF423J5N	MLWF423P5N
	2 x 26 W	MLWF522G2N	MLWF522J5N	MLWF522P5N
	1	MLWF523G2N	MLWF523J5N	MLWF523P5N
	1 x 57 W	MLWF572G4N ⑦	MLWF572J5N ⑦	MLWF572P5N ⑦
	1	MLWF573G4N ⑦	MLWF573J5N ⑦	MLWF573P5N ⑦
	2 x 32 W	MLWF642G2N	MLWF642J5N	MLWF642P5N
	1	MLWF643G2N	MLWF643J5N	MLWF643P5N
	2 x 42 W	MLWF842G2N	MLWF842J5N	MLWF842P5N
	1	MLWF843G2N	MLWF843J5N	MLWF843P5N
Shown with 8" Glass Refractor				
	2 x 57 W	MLWF1142G4N ⑦	MLWF1142J5N ⑦	MLWF1142P5N ⑦
	1	MLWF1143G4N ⑦	MLWF1143J5N ⑦	MLWF1143P5N ⑦

① For fixtures with guard, substitute **G** for **N** before adding voltage suffix.

② Add voltage suffix **-BU** for 120 through 277 V, 50/60 Hz and 125 Vdc. Add voltage suffix **-A5** for 347 V, 60 Hz.

③ Add **L** after voltage suffix to include lamp.

④ Add **Z2** suffix for factory-sealed non-sparking/restricted breathing protection (Aex nA nR).

⑤ To order fixture with NEMA Type I or III glass refractor, change **J5** to **J1** or **J3** respectively.

⑥ To order fixture with NEMA Type II, III, or IV polymeric refractor, change **P5** to **P2**, **P3** or **P4** respectively. Polymeric refractor fixtures are UL Listed and CSA Certified for Class II, Division 1 and 2, Groups F and G; Class III; Marine Outdoor Salt Water (UL1598A); NEMA 4X and CSA Type 4X.

⑦ Certified to meet the Canadian Electrical Code (CEC) only.