

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:
Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA IIC
Class II, Division 1, Group E, F, G
Class II, Division 2, Group F, G
Class III

NEC/CEC:
Type 3R, 4, 4X
IP66/67
Simultaneous Exposure
Suitable for Use in Wet Locations
Marine Outside Type (Salt Water)

ATEX/IECEx:
Zone 2 and 22
II 2 GD
IP66/67

Applications

- Enclosed and gasketed fixtures suitable for use in:
 - Marine and wet locations
 - A wide range of industrial, chemical processing and other areas where flammable gases and vapors are present
 - Areas of low clearance or low ceiling heights
 - Non-hazardous locations where severe weather conditions, excessive moisture, dirt, dust, corrosive atmosphere or high ambient temperatures are encountered
- Typical applications include:
 - Pulp and paper mills
 - Processing plants
 - Chemical plants
 - Oil refineries
 - Foundries
 - Manufacturing plants
 - Storage areas
 - Waste and sewage treatment
 - Parking garages
 - Other areas where dust, water, dirt and rough usage are a problem



Features

- Compact light weight low profile design is suited for low mounting heights.
- Modular design allows scores of fixture component combinations to meet installation needs. Uses same mounting hoods as Mercmaster III.
- Fixture housing and mounting hoods are copperfree cast aluminum with baked epoxy finish. All exposed hardware is stainless steel.
- Accommodates a wide range of voltages.
- Ambient temperatures:
 - 70 W to 100 W equivalent: -40 °C to +65 °C (-40 °F to +149 °F)
 - 150 W to 175 W equivalent: -40 °C to +55 °C (-40 °F to +131 °F)
 - 250 W equivalent: -40 °C to +50 °C (-40 °F to +122 °F)
 - 350 W equivalent: -40 °C to +50 °C (-40 °F to +122 °F)
 - 400 W equivalent: -40 °C to +55 °C (-40 °F to +131 °F)
- Electrical: 120-277 Vac, 50/60 Hz; 347-480 Vac, 50/60 Hz, Volts +/- 10%.
- Pole terminal block: 1 x 8-24 AWG; 1 x 0.75 to 6 mm² (0.0012 to 0.0093 in²).
- Hinge has high lip for added safety during installation and servicing. Hinge and bolt construction assures 360° compression at all points on ballast housing gasket for positive sealing. Swing away design of captive bolt and nut simplifies servicing.
- All Mercmaster mounting hoods have provision for easy field installation of fuses in fixtures (see Fixture Unit — Electrical Specification).
- NPT and metric threads standard.
- NEMA Type V light distribution is standard.
 - Type V distribution is required in areas where sufficient, evenly distributed light is necessary. It produces a circular distribution that has the same intensity at all angles.

- NEMA Type I light distribution is available as an option for select NEC/CEC certified fixtures.
 - Type I distribution is the perfect lighting for walkways, Type I distribution is perfect for lighting walkways, catwalks or anyplace where a narrow beam of light is required.
- For ATEX/IECEx rated fixtures, ballast bodies and mounting hoods must be purchased separately.

Standard Materials

- Mounting hoods and bodies: cast copperfree (4/10 of 1% max.) aluminum
- All hardware and catch assemblies: stainless steel
- Globe: polycarbonate

Standard Finishes

- Mounting hoods, bodies and guards: baked gray epoxy-clad finish, electrostatically applied for complete uniform protection

NEC/CEC Certifications and Compliances

- UL Standard: UL 50; UL 844; UL 1598; UL 1598A; UL 8750
- CSA Standard: C22.2 No 0; C22.2 No. 0.4; C22.2 No. 0.5; C22.2 No. 94; C22.2 No. 60529; C22.2 No. 137; C22.2 No. 250.0; C22.2 No. 60079; E60079-15
- ANSI/UL Standards: 60079-0; 60079-15
- ANSI/IEC Standards: 60529
- cCSAus Certified: 65182

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA IIC
Class II, Division 1, Group E, F, G
Class II, Division 2, Group F, G
Class III

NEC/CEC:

Type 3R, 4, 4X
IP66/67
Simultaneous Exposure
Suitable for Use in Wet Locations
Marine Outside Type (Salt Water)

ATEX/IECEx:

Zone 2 and 22
II 2 GD
IP66/67

ATEX/IECEx Certification and Compliances

- ATEX
 - Gas: Zone 2
 - Conforming to ATEX 94/9/CE: Ⓜ II 3 G
 - Type of Protection: Ex nA IIC Gc
 - Temperature class:
 - 70 W and 100 W equivalent: T4 [+40 °C (+104 °F)], T4 [+55 °C (+131 °F)], T3 [+65 °C (+149 °F)]
 - 150 W to 175 W equivalent: T4 [+40 °C (+104 °F)], T4 [+55 °C (+131 °F)]
 - 250 W equivalent: T4 [+40 °C (+104 °F)], T4 [+50 °C (+122 °F)]
 - Dust: Zone 22
 - Conforming to ATEX 94/9/CE: Ⓜ II 3 D
 - Type of Protection: Ex tc IIIc Dc
 - Surface Temperature:
 - 70 W and 175 W equivalent: T92 °C (T197.6 °F)
 - 250 W equivalent: T79 °C (T174.2 °F)
 - Ambient Temperature:
 - 70 W and 100 W equivalent: -40 °C to +65 °C (-40 °F to +149 °F)
 - 150 W to 175 W equivalent: -40 °C to +55 °C (-40 °F to +131 °F)
 - 250 W equivalent: -40 °C to +50 °C (-40 °F to 122 °F)
 - ATEX Certificate: LCIE 11 ATEX 1008, LCIE 14 ATEX 3063
 - IECEx Certificate: IECEx LCI 11.0058
 - Index of Protection according EN/IEC 60529: IP66
- IECEx
 - Gas: Zone 2
 - Type of Protection: Ex nA IIC Gc
 - Temperature class:
 - 70 W to 175 W equivalent: T4 [+40 °C (+104 °F)], T4 [+55 °C (+131 °F)]
 - 250 W equivalent: T4 [+40 °C (+104 °F)], T4 [+50 °C (+122 °F)]
 - Dust: Zone 22
 - Type of Protection: Ex tc IIIc Dc
 - Surface Temperature:
 - 70 W and 175 W equivalent: T92 °C (198 °F)
 - 250 W equivalent: T79 °C (198 °F)
 - Ambient Temperature:
 - 70 W and 175 W equivalent: -40 °C to +55 °C (-40 °F to +131 °F)
 - 250 W equivalent: -40 °C to +50 °C (-40 °F to +122 °F)
 - IECEx Certificate: IECEx LCI 11.0058
 - Index of Protection according EN/IEC 60529: IP66

EURASEC Certification

- EURASEC N° TC RU C-FR.Г505.B.00912

Other Certification

- INMETRO Certificate: BVC12.1522 ①

NEC/CEC Related Products

- NEC, Class I, Division 2 photocells for classified use are available, see *PCD2 Series*.
- Mounting hoods with photocontrols are not rated IP66/67, Type 4X or Marine Outside Type (Salt Water).

DesignLights™ Consortium (for the following models)

- MLEDN15
- MLEDN17
- MLEDN25
- MLEDN35
- MLEDN40

Appleton®

LED/AREA: NEC/CEC, ATEX/IECEx ENCLOSED AND GASKETED

① Inmetro certification available on special request only. Contact your local sales representative for more information.

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA IIC
Class II, Division 1, Group E, F, G
Class II, Division 2, Group F, G
Class III

NEC/CEC:

Type 3R, 4, 4X
IP66/67
Simultaneous Exposure
Suitable for Use in Wet Locations
Marine Outside Type (Salt Water)

ATEX/IECEx:

Zone 2 and 22
II 2 GD
IP66/67

Illustrated Features



Heatsink

Reliable heat transfer via the cast, epoxy powder coat aluminum body. Provides maximum heat dissipation from the LED assembly to the outside environment.



Driver Assembly

Utilizing non-sparking components avoiding the ignition of gases or vapors that may be present (nA).

Modular Plug between LED and driver.

Terminal Blocks (Zone 2)

A seven-point terminal block is provided to facilitate wiring. Terminal block accommodates wire size ranging from #8 to #24AWG, 0.75 to 6 mm² (0.0012 to 0.0093 in²)

Epoxy Finish

Ballast housing, hoods and guards are copperfree aluminum with epoxy powder coat finish.

Electrical Protection

Ground wire provided to bond mounting hood to ballast housing.

Safety

Rounded heatsink edges prevent possible injury during installation.

"Safety" High Hinge

Extra-high hinge provides additional protection against accidental ballast housing disengagement during installation or maintenance.

Stainless Steel Latch Assembly

Captive, stainless steel latch assembly bolt and nut closes securely, resists attack of corrosive atmospheres. Swing-away design simplifies servicing.



LED Chamber

Protected by polycarbonate lens, allows for easy maintenance access.




Cooler Operating Cone Hood

Larger sloped surface sheds dusts, dirt and combustible fibers providing better heat dissipation.

Mounting Hood and Globe Gaskets

Silicone rubber gaskets seals out moisture, dirt and dust. Stays flexible, withstands high temperatures. Closure design assures uniform gasket compression.



Fuses ①

Two screws secure fuse kit to mounting boss in any Mercmaster mounting hood. Fuse included.

Photocell ①

Available for all fixtures except cone and ceiling mount. Installs through knock-out in mounting hood. Provides continuous ON-OFF dusk-to-dawn control.



① Fuses and photocells are available on the NEC/CEC versions only. Not for use in ATEX/IEC.

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
 Class I, Zone 2, AEx nA IIC
 Class II, Division 1, Group E, F, G
 Class II, Division 2, Group F, G
 Class III

NEC/CEC:

Type 3R, 4, 4X
 IP66/67
 Simultaneous Exposure
 Suitable for Use in Wet Locations
 Marine Outside Type (Salt Water)

ATEX/IECEX:

Zone 2 and 22
 Ⓢ II 2 GD
 IP66/67

Order using catalog numbering guides below or select catalog number from tables on following pages.

Catalog Numbering Guide — NEC/CEC Certified Mercmaster LED

| | | | | | | | |
|---|---|---|---|--|--|--|--|
| MLEDN | A | 17 | 2 | P | 5 | BU | H1 |
| MLEDN - NEC/CEC Certified Mercmaster LED Series | | Light Level Equivalent: 70 - 70 W HPS/PSMH 10 - 100 W HPS/PSMH 15 - 150 W HPS/PSMH 17 - 175 W PSMH ② 25 - 250 W HPS/PSMH 35 - 350 W PSMH ⑥ 40 - 400 W HPS/PSMH ⑦ | | Optical Assembly: P - Polycarbonate Globe | | Voltage: BU - Universal Voltages 120-277 Vac, 50/60 Hz BH - 347-480 Vac, 50/60 Hz | |
| | Mounting: A - Pendant C - Ceiling ① D - Pendant Cone R - 90° Stanchion S - 25° Stanchion W - Wall | | Hub Size: 2 - 3/4" NPT 3 - 1" NPT 4 - 1-1/4" NPT stanchion 5 - 1-1/2" NPT stanchion 6 - Metric M20 | | Light Distribution: 1 - NEMA Type I Elliptical (100 W HPS and 175 W PSMH Only) 5 - NEMA Type V Symmetrical | | Options: D - Diffused Globe F - Fusing ③ H1 - Photocontrol 120 V ④ H2 - Photocontrol 208 V ④ H3 - Photocontrol 240 V ④ H4 - Photocontrol 277 V ④ |

Catalog Numbering Guide — ATEX/IECEX Certified Mercmaster LED ⑤

| | | | | | | | |
|---|--|---|--|--|--|---|--------------------------------|
| MLEDNA | — | 17 | — | P | 5 | BU | D |
| MLEDNA - ATEX/IECEX Certified Mercmaster LED Series | | Light Level Equivalent: 70 - 70 W HPS/PSMH 10 - 100 W HPS/PSMH 15 - 150 W HPS/PSMH 17 - 175 W PSMH ② 25 - 250 W HPS/PSMH | | Optical Assembly: P - Polycarbonate Globe | | Voltage: BU - Universal Voltages 120-277 Vac, 50/60 Hz | |
| | Mounting: ATEX/IECEX version is not available as a complete fixture (not sold with mounting hood) | | Hub Size: ATEX/IECEX version is not available as a complete fixture (hub size does not apply) | | Light Distribution: 5 - NEMA Type V Symmetrical | | Options: D - Diffused Globe |

① Ceiling mount luminaires are not designed to use the PCD2 photocontrol. Ceiling mounts must use an FS/FD box with a photocontrol. Contact your local sales representative for more information.

② 175 W Pulse Start Metal Halide only. Does not have a High Pressure Sodium equivalent.

③ Canadian Electrical Code does NOT allow fusing in hazardous locations. Fuse not CEC rated.

④ Luminaires with photocontrol are not rated IP66/67 or marine outside type (salt water).

⑤ For ATEX/IECEX rated fixtures, ballast bodies and mounting hoods must be purchased separately.

⑥ Available for use with the BH voltage only (347-480 Vac, 50/60 Hz).

⑦ Available for use with the BU voltage only (120-277 Vac, 50/60 Hz).

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:
 Class I, Division 2, Groups A, B, C, D
 Class I, Zone 2, AEx nA IIC
 Class II, Division 1, Group E, F, G
 Class II, Division 2, Group F, G
 Class III

NEC/CEC:
 Type 3R, 4, 4X
 IP66/67
 Simultaneous Exposure
 Suitable for Use in Wet Locations
 Marine Outside Type (Salt Water)

ATEX/IECEX:
 Zone 2 and 22
 II 2 GD
 IP66/67

Technical Data

| Lamp | | Ambient Temperature °C (°F) | Supply Wire Temperature °C (°F) | NEC/CEC | | | | ATEX/IECEX | | | |
|-------------------------------|------|-----------------------------|---------------------------------|-----------------------|------------|--|------------------------------|-------------|---|-------------------|----------------------------|
| Light Level Equivalent to HID | Type | | | Class I, Division 2 ① | Gas Groups | Class I, Zone 2, AEx nA IIC, Ex nA IIC | Class II, Division 1 and 2 ② | Dust Groups | Gas/Dust Simultaneous ① Class I, Division 2/ Class II, Division 1 | Gas Ex II 3G ① nA | Dust Ex II 3D ② Ex tc IIIC |
| 70 Watt NEMA Type V | LED | 40 (104) | 60 (140) | T4A | A, B, C, D | T4 | T6 | E, F, G | T4 | T4 | T92°C (T197.6°F) Dc |
| | | 55 (131) | 75 (167) | T4 | | T4 | T6 | | T4 | | |
| | | 65 (149) | 90 (194) | T3C | | T3 | T6 | | T3C | | |
| 100 Watt NEMA Type V | LED | 40 (104) | 60 (140) | T4A | A, B, C, D | T4 | T6 | E, F, G | T4 | T4 | T92°C (T197.6°F) Dc |
| | | 55 (131) | 75 (167) | T4 | | T4 | T6 | | T4 | | |
| | | 65 (149) | 90 (194) | T3C | | T3 | T6 | | T3C | | |
| 100 Watt NEMA Type I ③ | LED | 40 (104) | 60 (140) | T4 | A, B, C, D | T4 | T5 | E, F, G | T4 | — | — |
| | | 55 (31) | 75 (167) | T3C | | T3 | T5 | | T3C | | |
| | | 65 (143) | 90 (194) | T3C | | T3 | T4A | | T3C | | |
| 150 Watt NEMA Type V | LED | 40 (104) | 60 (140) | T4A | A, B, C, D | T4 | T6 | E, F, G | T4 | T6 | T92°C (T197.6°F) Dc IP66 |
| | | 55 (131) | 75 (167) | T4 | | T4 | T6 | | T4 | | |
| 175 Watt NEMA Type V | LED | 40 (104) | 60 (140) | T4A | A, B, C, D | T4 | T6 | E, F, G | T4 | T6 | T92°C (T197.6°F) Dc IP66 |
| | | 55 (131) | 75 (167) | T4 | | T4 | T6 | | T4 | | |
| 175 Watt NEMA Type I ③ | LED | 40 (104) | 60 (140) | T4 | A, B, C, D | T4 | T5 | E, F, G | T4 | — | — |
| | | 55 (131) | 75 (167) | T3C | | T3 | T5 | | T3C | | |
| 250 Watt NEMA Type V ③ | LED | 40 (104) | 60 (140) | T4A | A, B, C, D | T4 | T6 | E, F, G | T4A | T4 | T79°C (T174.2°F) Dc |
| | | 50 (122) | 75 (167) | T4 | | T4 | T6 | | T4 | | |
| 350 Watt NEMA Type V ③ | LED | 40 (104) | 75 (167) | T3A | A, B, C, D | T3 | — | — | — | — | — |
| | | 50 (122) | 75 (167) | T3 | | T3 | — | | — | | |
| 400 Watt NEMA Type V ③ | LED | 40 (104) | 75 (167) | T3A | A, B, C, D | T3 | — | — | — | — | — |
| | | 55 (131) | 75 (167) | T3 | | T3 | — | | — | | |

“T” Numbers Represent the Maximum Internal Temperature ① or Maximum Surface Temperature ②

| “T” # | NEC/CEC | | | | | | | | | | | | | | | |
|---------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|-------------------|------------------|----------|
| | T1 | 350 | 325 | T2 | T2A | T2B | T2C | T2D | T3 | T3A | T3B | T3C | T4 | T4A | T5 | T6 |
| Temp. Range °C (°F) | 351-450 (664-842) | 326-350 (619-662) | 301-325 (574-617) | 281-300 (538-572) | 261-280 (502-536) | 231-260 (448-500) | 216-230 (421-446) | 201-215 (394-419) | 181-200 (358-392) | 166-180 (331-356) | 161-165 (322-329) | 136-160 (277-320) | 121-135 (250-275) | 101-120 (214-248) | 86-100 (187-212) | 85 (185) |

| “T” # | ATEX/IECEX | | | | | |
|---------------------|-------------------|-------------------|-------------------|-------------------|------------------|----------|
| | T1 | T2 | T3 | T4 | T5 | T6 |
| Temp. Range °C (°F) | 301-450 (547-842) | 201-300 (394-572) | 136-200 (277-392) | 101-135 (214-275) | 86-100 (187-212) | 85 (185) |

- ① T numbers represent the maximum internal temperature for Class I, Division 2 and Class I, Zone 2 locations designated by the NEC.
- ② T numbers represent the maximum surface temperature under a dust blanket for Class II, Division 1 and Class I, Zone 2 as designated by the NEC or Zone 2 (Gas) and 22 (Dust) locations as designated by the IEC.
- ③ Lamp type is not certified for use in ATEX/IEC.

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:
 Class I, Division 2, Groups A, B, C, D
 Class I, Zone 2, AEx nA IIC
 Class II, Division 1, Group E, F, G
 Class II, Division 2, Group F, G
 Class III

NEC/CEC:
 Type 3R, 4, 4X
 IP66/67
 Simultaneous Exposure
 Suitable for Use in Wet Locations
 Marine Outside Type (Salt Water)

ATEX/IECEX:
 Zone 2 and 22
 II 2 GD
 IP66/67

Lamp Comparison Chart

| Lamp Data | Line Current Amps | Input Power | Lumens | CRI | Lamp Life (Hours) | Color Temp CCT |
|--------------------|-------------------|-------------|--------|-----|-------------------|----------------|
| NEMA Type V | | | | | | |
| MLEDN70 | .31 @ 120 V | 35 | 2300 | 70 | 60,000+ | 5650 |
| | .17 @ 277 V | 33 | | | | |
| | .24 @ 347 V | 34 | | | | |
| | .11 @ 480 V | 32 | | | | |
| MLEDN100 | .41 @ 120 V | 47.5 | 3450 | 70 | 60,000+ | 5650 |
| | .20 @ 277 V | 46 | | | | |
| | .25 @ 347 V | 42 | | | | |
| | .12 @ 480 V | 44 | | | | |
| MLEDN150 | .53 @ 120 V | 61 | 4850 | 70 | 60,000+ | 5650 |
| | .25 @ 277 V | 62 | | | | |
| | .29 @ 347 V | 62 | | | | |
| | .14 @ 480 V | 64 | | | | |
| MLEDN175 | .63 @ 120 V | 74 | 6076 | 70 | 60,000+ | 5650 |
| | .28 @ 277 V | 72 | | | | |
| | .25 @ 347 V | 86 | | | | |
| | .16 @ 480 V | 88 | | | | |
| MLEDN250 ① | .83 @ 120 V | 95.5 | 9455 | 70 | 60,000+ | 5650 |
| | .36 @ 277 V | 92 | | | | |
| | .45 @ 347 V | 96 | | | | |
| | .31 @ 480 V | 95 | | | | |
| MLEDN350 ① | .30 @ 347 V | 102 | 11425 | 70 | 60,000+ | 5650 |
| | .23 @ 480 V | 103 | | | | |
| MLEDN400 | 1.04 @ 120 V | 127 | 12850 | 70 | 60,000+ | 5650 |
| | .47 @ 277 V | 128 | | | | |
| NEMA Type I | | | | | | |
| MLEDN100 ① | .41 @ 120 V | 47.5 | 2900 | 70 | 60,000+ | 5650 |
| | .20 @ 277 V | 46 | | | | |
| | .25 @ 347 V | 47.5 | | | | |
| | .12 @ 480 V | 46 | | | | |
| MLEDN175 ① | .61 @ 120 V | 70 | 6200 | 70 | 60,000+ | 5650 |
| | .28 @ 277 V | 69 | | | | |
| | .24 @ 347 V | 70 | | | | |
| | .16 @ 480 V | 69 | | | | |

① Lamp type is not certified for use in ATEX/IEC.

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:
 Class I, Division 2, Groups A, B, C, D
 Class I, Zone 2, AEx nA IIC
 Class II, Division 1, Group E, F, G
 Class II, Division 2, Group F, G
 Class III

NEC/CEC:
 Type 3R, 4, 4X
 IP66/67
 Simultaneous Exposure
 Suitable for Use in Wet Locations
 Marine Outside Type (Salt Water)

Fixture Unit — Electrical Specification



| LED Wattage BU/BH | Light Level Equivalent | NEMA Type | Current Draw | Catalog Number | | | Voltage Range | Voltage Suffix |
|--|---------------------------|-----------|---|----------------|--------------|-------------|--------------------------|-------------------|
| | | | | Fuse Kit ① | Fixture Unit | Conformance | | |
| NEC/CEC Certified Ballast Housing | | | | | | | | |
| 35/33 W | 70 W HPS | Type V | 120 Vac @ .31 Amps 277 Vac @ .17 Amps | F3 | MLEDN70P5 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |
| 34/32 W | 70 W HPS | Type V | 347 Vac @ .24 Amps 480 Vac @ .11 Amps | F3 | MLEDN70P5 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 47.5/46 W | 100 W HPS | Type V | 120 Vac @ .41 Amps 277 Vac @ .20 Amps | F3 | MLEDN10P5 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |
| 47.5/46 W | 100 W HPS | Type I | 120 Vac @ .41 Amps 277 Vac @ .20 Amps | F3 | MLEDN10P1 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |
| 42/44 W | 100 W HPS | Type V | 347 Vac @ .25 Amps 480 Vac @ .12 Amps | F3 | MLEDN10P5 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 47.5/46 W | 100 W HPS | Type I | 347 Vac @ .25 Amps 480 Vac @ .12 Amps | F3 | MLEDN10P1 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 61/62 W | 150 W HPS | Type V | 120 Vac @ .53 Amps 277 Vac @ .25 Amps | F3 | MLEDN15P5 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |
| 62/64 W | 150 W HPS | Type V | 347 Vac @ .29 Amps 480 Vac @ .14 Amps | F3 | MLEDN15P5 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 74/72 W | 175 W PSMH | Type V | 120 Vac @ .63 Amps 277 Vac @ .28 Amps | F3 | MLEDN17P5 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |
| 70/69 W | 175 W PSMH | Type I | 120 Vac @ .61 Amps 277 Vac @ .28 Amps | F3 | MLEDN17P1 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |
| 86/88 W | 175 W PSMH | Type V | 347 Vac @ .25 Amps 480 Vac @ .16 Amps | F3 | MLEDN17P5 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 70/69 W | 175 W PSMH | Type I | 347 Vac @ .24 Amps 480 Vac @ .16 Amps | F3 | MLEDN17P1 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 95.5/92 W | 250 W HPS/PSMH | Type V | 120 Vac @ .83 Amps 277 Vac @ .36 Amps | F3 | MLEDN25P5 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |
| 96/95 W | 250 W HPS/PSMH | Type V | 347 Vac @ .45 Amps 480 Vac @ .31 Amps | F3 | MLEDN25P5 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 102/103 W | 350 W PSMH | Type V | 347 Vac @ .30 Amps 480 Vac @ .23 Amps | F3 | MLEDN35P5 | NEC/CEC | 347-480 Vac, 50/60 Hz | BH |
| 127/128 W | 400 W HPS/PSMH | Type V | 120 Vac @ 1.04 Amps 277 Vac @ .47 Amps | F3 | MLEDN40P5 | NEC/CEC | 120-277 Vac, 50/60 Hz | BU |

① Canadian Electrical Code does NOT allow fusing in hazardous locations. Fuse not CEC rated.

Mercmaster™ LED Series Luminaires

Enclosed and Gasketed Fixtures

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
 Class I, Zone 2, AEx nA IIC
 Class II, Division 1, Group E, F, G
 Class II, Division 2, Group F, G
 Class III

NEC/CEC:

Type 3R, 4, 4X
 IP66/67
 Simultaneous Exposure
 Suitable for Use in Wet Locations
 Marine Outside Type (Salt Water)

ATEX/IECEX:

Zone 2 and 22
 II 2 GD
 IP66/67

Photometric Data – DATA SHOWN IS ABSOLUTE


REPORT NUMBER: **MLEDN10P1BU (NEMA Type I)**

Lamps: Mercmaster LED, Class I, Division 2, Polycarbonate Optic

| Candela Distribution | |
|----------------------|--------|
| Zone | Lumen |
| 0-10 | 276.95 |
| 10-20 | 715.67 |
| 20-30 | 650.02 |
| 30-40 | 492.78 |
| 40-50 | 369.94 |
| 50-60 | 232.10 |
| 60-70 | 127.75 |
| 70-80 | 22.49 |
| 80-90 | 2.23 |

| CIE Type – Direct | |
|-------------------|------------------|
| Plane | Spacing Criteria |
| 0-Deg | 90-Deg |
| 0.74 | 0.74 |

| Zonal Lumen Summary | | |
|---------------------|---------|-----------|
| Zone | Lumens | % Fixture |
| 0-20 | 992.62 | 34.3 |
| 0-30 | 1642.65 | 56.8 |
| 0-40 | 2135.42 | 73.8 |
| 0-60 | 2737.46 | 94.7 |
| 0-80 | 2887.70 | 99.8 |
| 0-90 | 2889.93 | 99.9 |




REPORT NUMBER: **MLEDN15P5BU**

Lamps: Mercmaster LED, Class I, Division 2, Polycarbonate Optic

| | Candela Distribution | | | | | |
|----|----------------------|------|------|------|------|------|
| | 0.0 | 22.5 | 45.0 | 67.5 | 90.0 | Flux |
| 0 | 2208 | 2208 | 2208 | 2208 | 2208 | |
| 5 | 2202 | 2195 | 2197 | 2195 | 2202 | 209 |
| 15 | 2137 | 2131 | 2127 | 2131 | 2137 | 603 |
| 25 | 2045 | 2003 | 1977 | 2003 | 2045 | 926 |
| 35 | 1669 | 1658 | 1735 | 1658 | 1669 | 1051 |
| 45 | 1252 | 1282 | 1297 | 1282 | 1252 | 988 |
| 55 | 836 | 850 | 838 | 850 | 834 | 746 |
| 65 | 276 | 307 | 333 | 307 | 276 | 298 |
| 75 | 16 | 12 | 11 | 12 | 16 | 22 |
| 85 | 2 | 1 | 1 | 1 | 2 | 2 |
| 90 | 1 | 0 | 0 | 0 | 1 | |

| Zonal Lumen Summary | | |
|---------------------|--------|-----------|
| Zone | Lumens | % Fixture |
| 0-30 | 1738 | 35.8 |
| 0-40 | 2789 | 57.5 |
| 0-60 | 4523 | 93.3 |
| 0-90 | 4844 | 99.9 |

| CIE Type – Direct | |
|-------------------|------------------|
| Plane | Spacing Criteria |
| 0-Deg | 90-Deg |
| 1.2 | 1.2 |



Appleton

LED/AREA: NEC/CEC, ATEX/IECEX ENCLOSED AND GASKETED