

MD2SR Factory Sealed Interlocked Switched Receptacles

Dead Front Interlocked Construction; No External Seals Required.

NEC:

Class I, Division 2, Groups B, C, D
Class II, Division 1 and 2, Groups F, G
Class III
Class I, Zone 2, Group IIC T3
NEMA 3*, 3R*, 4^T, 4X^T, 9FG, 12

Applications

- Locations where receptacles are used with stationary or portable electrically operated devices such as:
 - Lighting systems
 - Conveyors
 - Heaters
 - Motor generator sets
 - Air conditioners
 - Compressors
 - Pumps

Features

- Factory sealed; no external seals required.
- Available in fused and unfused versions.
- UL Listed for use with Appleton ACP plugs.
- Positive polarization; only plugs of the same style, number of poles, and Amperage rating may be used with these receptacles.
- Plug must be inserted into the receptacle before the switch can be turned on. Plug cannot be withdrawn unless the switch is in the off position.
- Cover bolts are stainless steel and captive.
- Insulated, dual-color polymer operating handle clearly indicates the switch being energized. Ergonomically designed handle is made of high-impact polymer material for exceptional ruggedness, durability and corrosion resistance.
- Style 2 (shell and extra pole) grounding.
- Removable hinged cover allows for ease of installation and maintenance.
- Short circuit withstand rated to 200,000 RMS symmetrical amperes (Class J fusing).
- Short circuit withstand rated to 10,000 RMS symmetrical amperes (unfused).
- Conduit entry is drilled and tapped to 1-1/2". Reducer bushings 1-1/2"-1-1/4" and 1-1/2"-1" provided at no additional cost.
- Stainless steel key-hole mounting feet for easy installation.
- Accommodates #8 – #4/0 AWG copper wire.
- Unit is equipped with defeatable door interlock which allows emergency access when switch is energized.
- Cover can be padlocked closed.
- Operating handle can be locked in the "OFF" position with provision to lock in the "ON" position.

Standard Materials

- Enclosure: copperfree (4/10 of 1% max.) aluminum
- Operating handle: high impact polymer
- Hardware: stainless steel

Standard Finish

- Enclosure: epoxy powder coating inside and outside

Options

- One normally opened, one normally closed auxiliary switch, add suffix **-AUX**.



- Special Polarization: Prevents plug insertion in a receptacle or connector wired for a different voltage. In installations where there are different line voltages, the special polarization option is desirable. This allows only plugs and receptacles wired for the same line voltage to be mated together. The receptacle or connector interior is positioned 22-1/2°, relative to the polarization rivet, to the right (as specified) of standard, and plug is polarized to correspond. Add Suffix **-P4** to receptacle.

NEC Certifications and Compliances

- UL Standard: UL 894, UL 1203, UL 1604, UL 1682
- UL Listed: E10784

• Flip cover suitable for NEMA 3, 3R only.

▼ NEMA 4/4X rating maintained with an ACP Powertite™ plug installed. Install screw cover for 4, 4X. Both covers are included with product.

Visit our website at www.appletonelec.com or contact us at (800) 621-1506 or +33.3.22.54.27.54.
© March 2022

APPLETON™

PLUGS AND RECEPTACLES: NEC/CEC HAZARDOUS LOCATION

451

EMERSON

MD2SR Factory Sealed Interlocked Switched Receptacles

Dead Front Interlocked Construction; No External Seals Required.

NEC:

Class I, Division 2, Groups B, C, D
 Class II, Division 1 and 2, Groups F, G
 Class III
 Class I, Zone 2, Group IIC T3
 NEMA 3*, 3R*, 4†, 4X†, 9FG, 12

Amp	Wires/Poles	Max HP	Fusing *	Catalog Number ①†	Mating Plug
30	2W, 3P	3 HP @ 240 Vac	Non-Fused	MD2SR3023U	ACP3023BC
			Fused	MD2SR3023F	
	3W, 4P	20 HP @ 600 Vac 30 HP @ 600 Vac	Non-Fused	MD2SR3034U	ACP3034BC
			Fused	MD2SR3034F	
60	3W, 4P	50 HP @ 600 Vac	Non-Fused	MD2SR6034U	ACP6034BC
			Fused	MD2SR6034F	
100	3W, 4P	50 HP @ 600 Vac	Non-Fused	MD2SR1034U	ACP1034BC
			Fused	MD2SR1034F	

ACP Plugs for MD2SR Receptacles

Cable Dia. (Inches)	30 Amp		60 Amp		100 Amp	
	2W, 3P	3W, 4P	2W, 3P	3W, 4P	2W, 3P	3W, 4P
.500 to 1.125	ACP3023BC	ACP3034BC	—	—	—	—
.500 to 1.375	—	—	ACP6023BC	ACP6034BC	—	—
.875 to 1.906	—	—	—	—	ACP1023CD	ACP1034CD



CPH Plugs for MD2SR Receptacles

Cable Dia. (Inches)	30 Amp		60 Amp ②	
	2W, 3P	3W, 4P	2W, 3P	3W, 4P
.500 to 1.125	CPH3023BC	CPH3034BC	—	—
.500 to 1.375	—	—	CPH6023BC	CPH6034BC



Replacement Parts

Description	Catalog Number
Heavy Duty Disconnect Switch Operating Handle	WSRHANDLE
30 Amp, Powertite™ ACP Plug Twist Clamping Ring	30CRING
30 Amp, Receptacle Screw Cover with Gasket and Chain	30SCAP

• Flip cover suitable for NEMA 3, 3R only.

▼ NEMA 4/4X rating maintained with an ACP Powertite™ plug installed. Install screw cover for 4, 4X. Both covers are included with product.

* Fused units contain fuse holders; fuses not included.

① For auxiliary switch: one normally opened, one normally closed, add suffix **-AUX**.

② 60 Amp CPH plugs with **-BC** suffix are NOT UL listed.

† For special polarization add **-P4**.