

# Mercmaster™ III Low Profile Luminaires

## High Pressure Sodium, Pulse Start Metal Halide and Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

**CEC:**  
Class I, Division 2, Groups A, B, C, D  
Class I, Zone 2 Ex nR IIC (Z)  
Class II, Division 1 and 2, Groups E, F, G  
Class III

**CEC:**  
Type 4X  
IP66

### Applications

- Enclosed and gasketed fixtures suitable for use in:
  - Marine and wet locations
  - A wide range of industrial, chemical processing and other areas where flammable gases and vapors or combustible dusts are present under conditions defined by the National Electrical Code as Class I, Division 2; Class II, Division 1 and 2; and Class III
  - Areas of low clearance, low ceiling heights or where fixture weights must be minimized
  - For Zone 2, the method of protection is Ex nR – Restricted Breathing
  - Non-hazardous locations where severe weather conditions, excessive moisture, dirt, dust, corrosive atmosphere or high ambient temperatures are encountered
- Typical applications include:
  - Pulp and paper mills
  - Processing plants
  - Chemical plants
  - Oil refineries
  - Foundries
  - Manufacturing plants
  - Storage areas
  - Waste and sewage treatment
  - Parking garages
  - Other areas where dust, water, dirt and rough usage are a problem



Low Profile Mercmaster III with Prismatic Globe and Guard

### Standard Materials

- Mounting hoods, bodies and guard: cast copperfree (4/10 of 1% max.) aluminum
- All hardware and catch assemblies: stainless steel
- Reflectors: Fiberglass reinforced white polyester
- Globes and Refractors: heat-resistant prismatic glass

### Standard Finishes

- Mounting hoods, bodies and guards: baked gray epoxy-clad finish, electrostatically applied for complete uniform protection

### Options

- Quartz Auxiliary comes to full brightness immediately and remains lit until the HID lamp attains 60-70% of full illumination. Quartz Auxiliary supplied with relay switch and socket to accept 120 V quartz double-contact bayonet base lamp (not included). Add suffix **-E** ①.
- Guards with gray epoxy painted to match fixtures, supplied with stainless steel screws. Add suffix **-G** before voltage suffix.
- Hot Restrike to restrike HPS lamp immediately when power is restored after a momentary power interruption. Add suffix **-R**.
- Smart Starter incorporates a 1-1/2 minute timer and performs as a conventional starter to normally start lamp. Removes itself from circuit if lamp burns out or is removed from socket. Eliminates starter failures caused by prolonged operation with cycling or failing lamps and simplifies finding their location, reducing maintenance and repair costs. Available for all fixtures. Add suffix **-S**.
- Ex nR fixtures, add suffix **-Z**.
- Reflectors are available as standard dome and 30° angle polyester. Order separately.

### CEC Certifications and Compliances ②

- CSA Certified: 025428
- CSA Standard: CSA C22.2 No. 9, C22.2 No. 137; CAN/CSA E60079-0, E60079-15

### Related Products

- Photocells for classified use are available, see *PCD2 Series*.

### Features

- Compact light weight low profile design is suited for low mounting heights in conjunction with lower wattage fixtures.
- Modular design allows scores of fixture component combinations to meet installation and lighting needs. Uses same mounting hoods and optical accessories as Mercmaster III.
- A choice of heat-resistant prismatic glass refractors (NEMA I, III or V) or heat-resistant globes which thread directly into ballast housing. Photometrics available upon request – contact your local sales representative.
- Standard dome or 30° angle reflectors made of fiberglass reinforced white polyester. Highly resistant to corrosive atmospheres.
- Accommodates medium base lamps.
- A wide range of voltages available (120 to 600 Volt) and ballast types (Reactor, CWA, CWI and Super CWA).
- Medium base lamp type and watts:
  - HPS 50 W-150 W
  - PSMH 50 W-175 W ③
- Hinge has high lip for added safety during installation and servicing. Hinge and bolt construction assures 360° compression at all points on ballast housing gasket for positive sealing. Swing away design of captive bolt and nut simplifies servicing.
- All Mercmaster III mounting hoods have provision for easy field installation of fuses in fixtures (see fuse kits).
- Fixtures are for use in Class I, Zone 2 hazardous locations.
- The Ex nR factory sealed Mercmaster III prevents vapors and gases from entering the globe chamber. There are no seals or putty required which will reduce installation time and installation errors.

① Fixtures equipped with quartz auxiliary lamp do not comply with CEC requirements and are not suitable for use in classified locations.

② Compliance data varies for specific fixtures. Consult Appleton regarding suitability of specific fixtures for a particular application.

③ Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your country's governing legislation regarding allowable lamp types before ordering.

# Mercmaster™ III Low Profile Luminaires

## High Pressure Sodium, Pulse Start Metal Halide and Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

**CEC:**  
Class I, Division 2, Groups A, B, C, D  
Class I, Zone 2 Ex nR IIC (Z)  
Class II, Division 1 and 2, Groups E, F, G  
Class III

**CEC:**  
Type 4X  
IP66

### Illustrated Features



#### High Temperature Sockets

Medium base high-temperature porcelain sockets.

#### Aluminum Inner Reflector


Solid aluminum inner reflector (for refractor ballast housings only) improves photometric efficiency.

#### Globe Chamber

Completely sealed from the ballast housing and outside vapors/air (nR).

#### Electrical Protection

Ground wire provided to bond mounting hood to ballast housing.



#### Fuses

Two screws secure fuse kit to mounting boss in any Mercmaster mounting hood. Fuse included.

#### Photocell

Available for all fixtures except cone and ceiling mount. Installs through knock-out in mounting hood. Provides continuous ON-OFF dusk-to-dawn control.



#### Vented Reflectors

Reflectors are thick, tough fiberglass-reinforced white polyester, vented for cooler operation. Quickly attach with furnished stainless steel screws.

#### Stainless Steel Inserts

Ballast bodies have stainless steel threaded inserts to receive stainless steel screws for reflectors and guard. Prevents "freezing", allowing guards and reflectors to be easily removed and replaced at any time, without damage to the housing.

#### Epoxy Finish

Ballast housing, hoods and guards are copperfree aluminum with epoxy powder coat finish.

#### Prismatic Glass Globes and Refractors

Heat-resistant globes and refractors thread directly into ballast housing and seal against a high-temperature silicone rubber gasket.



#### Ballast Assembly

Utilizing non-sparking components avoiding the ignition of gases or vapors that may be present (nA).

#### Mounting Hood and Globe Gaskets

Silicone rubber gaskets seals out moisture, dirt and dust. Stays flexible, withstands high temperatures. Closure design assures uniform gasket compression.

#### Terminal Blocks (Zone 2)

A seven-point terminal block is provided to facilitate wiring. Terminal block accommodates wire size ranging from #8 to #24 AWG.



#### Cooler Operating Cone Hood

Larger sloped surface sheds dusts, dirt and combustible fibers providing better heat dissipation.



#### "Safety" High Hinge

Extra-high hinge provides additional protection against accidental ballast housing disengagement during installation or maintenance.



#### Stainless Steel Latch Assembly

Captive, stainless steel latch assembly bolt and nut closes securely, resists attack of corrosive atmospheres. Swing-away design simplifies servicing.

# Mercmaster™ III Low Profile Luminaires


## High Pressure Sodium, Pulse Start Metal Halide and Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

**CEC:**  
Class I, Division 2, Groups A, B, C, D  
Class I, Zone 2 Ex nR IIC (Z)  
Class II, Division 1 and 2, Groups E, F, G  
Class III

**CEC:**  
Type 4X  
IP66

### Mercmaster III Low Profile Family Tree



① Mounting hood with a 120 V or 208-277 V factory installed photocell is available.

② Standard and deep dome reflectors may interfere with bottom conduit entry if used with KPST and KPWB mounting hoods..

③ Available in clear, amber, blue, green and red.

④ Available in NEMA Type II, III, IV and V. Polymeric Refractor suitable for Class II, Groups F and G, NEMA 4X and Marine Type Electric Fixtures Outside Type (Salt Water) only (100 W PSMH Max.).

⑤ Available in NEMA Type I, III and V.

⑥ Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.

# Mercmaster™ III Low Profile Luminaires

## High Pressure Sodium, Pulse Start Metal Halide and Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

**CEC:**  
 Class I, Division 2, Groups A, B, C, D  
 Class I, Zone 2 Ex nR IIC (Z)  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III

**CEC:**  
 Type 4X  
 IP66

Order using catalog numbering guide below or select catalog number from tables on following pages.

### Catalog Numbering Guide

ML	A	L	15	2	G1	G	MT	R	Z2
Series: ML - Mercmaster III Low Profile	Lamp Type: I - Incandescent H - 175 W Metal Halide L - High Pressure Sodium H - Pulse Start Metal Halide			Hub Size: 2 - 3-1/4" NPT 3 - 1" NPT 4 - 1-1/4" NPT stanchion 5 - 1-1/2" NPT stanchion		Guard Options: G - Cast Guard N - No Guard		Options: E - Emergency Quartz ⑤ R - Hot Restrike ③ S - Smart Starter ④ H1 - Photocontrol 120 V H2 - Photocontrol 208 V H3 - Photocontrol 240 V H4 - Photocontrol 277 V C - Safety Cable Adapted D - E-27 Export Socket T - Terminal Blocks V - Anti-Vibration Modifications X - Appledapter ⑥ Mounting Hood Adapter	
Mounting: A - Pendant (rigid mounting) C - Ceiling D - Pendant Cone Hood F - Pendant (flexible mounting) R - 90° Stanchion S - 25° Stanchion W - Wall		Wattage ⑦: 10 - 100 W HPS/MH 15 - 150 W HPS/MH and 60-150 W max. Incandescent 17 - 175 W MH 50 - 50 W HPS/MH 70 - 70 W HPS/MH		Optical Assembly: ② G1 - Globe J1 - NEMA I Glass Refractor J3 - NEMA III Glass Refractor J5 - NEMA V Glass Refractor P2 - NEMA II Polymeric Refractor P3 - NEMA III Polymeric Refractor P4 - NEMA IV Polymeric Refractor P5 - NEMA V Polymeric Refractor		Voltage: ① LB - Incandescent, 120 V 60 Hz MT - 120/208/240/277 V 60 Hz TT - 120/277/347 V 60 Hz, CWA C2 - 208 V 60 Hz, CWI C3 - 240 V 60 Hz, CWI C6 - 480 V 60 Hz, CWI C7 - 600 V 60 Hz, CWI		Suffix: Z - Zone 2 suffix (required for Ex nR)	

① Other voltages, frequencies available – contact your local sales representative. Voltages shown are limited to specific combinations; refer to following pages.  
 ② Polymeric Refractor suitable for Class II, Groups F and G and NEMA 4X only (100 W PSMH Max.). Reflectors ordered separately.

③ Available for 50-150 W HPS fixtures only.

④ Available for HPS fixtures.

⑤ Fixtures equipped with quartz auxiliary lamp do not comply with CEC requirements and are not suitable for use in classified locations.

⑥ Appledapter is available for use with the pendant, ceiling and angled stanchion mounting only.

⑦ Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.

# Mercmaster™ III Low Profile Luminaires

Class I, Division 2; Class II, Division 1; Simultaneous exposure to hazardous conditions in both classifications

Temperature identification numbers of Mercmaster III Low Profile High Pressure Sodium and Pulse Start Metal Halide

**CEC:**  
Class I, Division 2, Groups A, B, C, D  
Class I, Zone 2 Ex nR IIC (Z)  
Class II, Division 1 and 2, Groups E, F, G  
Class III

**CEC:**  
Type 4X  
IP66

Watts	Lamp Type	Supply Wire Min. Temp. °C (°F)		Ambient Temp. °C (°F)			Class I, Division 2			Class II, Division 1 Groups E, F and G			Simultaneous Exposure Class I, Division 2 / Class II, Division 1		
							Globe	Globe & Reflector	Refractor	Globe	Globe & Reflector	Refractor	Globe	Globe & Reflector	Refractor
50	HPS	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3B	T4A	T4A	T5	T3	T3	T3	T2D	T2D	T2D
		90 °C (194 °F)	55 °C (131 °F)	T3	T3	T3A	T4A	T4A	T4A	T2C	T2C	T2C	T2C	T2C	T2C
		90 °C (194 °F)	65 °C (149 °F)	T3	T3	T3A	T4	T4	T4A	T2B	T2B	T2B	T2B	T2B	T2B
70	HPS	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3	T4	T4	T5	T2B	T2B	T2B	T2B	T2B	T2B
		90 °C (194 °F)	55 °C (131 °F)	T2D	T2D	T3	T3C	T3C	T4A	T2B	T2B	T2B	T2B	T2B	T2B
		90 °C (194 °F)	65 °C (149 °F)	—	—	T3	—	—	T4	—	—	—	—	—	—
100	HPS	90 °C (194 °F)	40 °C (104 °F)	T2C	T2C	T2D	T4	T4	T4A	T2B	T2B	T2B	T2A	T2A	T2A
		90 °C (194 °F)	55 °C (131 °F)	T2B	T2B	T2C	T3C	T3C	T4	T2A	T2A	T2A	T2A	T2A	T2A
		90 °C (194 °F)	65 °C (149 °F)	—	—	—	—	—	—	—	—	—	—	—	—
150	HPS	90 °C (194 °F)	40 °C (104 °F)	T2A	T2A	T2B	T3A ①	—	T4	325	—	T2	—	—	—
50	PSMH	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3A	T4A	T4A	T6	T2D	T2D	T3	T2C	T2C	T2D
		90 °C (194 °F)	55 °C (131 °F)	T3	T3	T3	T4	T4	T5	T2C	T2C	T2D	T2B	T2B	T2D
		90 °C (194 °F)	65 °C (149 °F)	T3	T3	T3	T4	T4	T4A	T2B	T2B	T2D	T2B	T2B	T2D
70	PSMH	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3	T3C	T3C	T4A	T2B	T2B	T2C	T2B	T2B	T2C
		90 °C (194 °F)	55 °C (131 °F)	T2D	T2D	T3	T3C	T3C	T4A	T2A	T2A	T2B	T2B	T2A	T2B
		110 °C (230 °F)	65 °C (149 °F)	—	—	T3	—	—	T4	—	—	—	—	—	T2B
100	PSMH	90 °C (194 °F)	40 °C (104 °F)	T2A	T2A	T2B	T3B	T3B	T4A	T2	T2	T2A	T1	T1	T2
		90 °C (194 °F)	55 °C (131 °F)	T2A	T2A	T2B	T3A ①	T3A ①	T4	T1	T1	T2	T1	T1	T2
150	PSMH	105 °C (221 °F)	40 °C (104 °F)	350	350	325	—	—	T3B	—	—	T1	—	—	T1
175	PSMH	105 °C (221 °F)	40 °C (104 °F)	350	350	325	—	—	T3B	—	—	T1	—	—	T1
175	MH ②	110 °C (230 °F)	40 °C (104 °F)	—	—	325	—	—	T3B	—	—	—	—	—	—
60	Inc.	90 °C (194 °F)	40 °C (104 °F)	T3B	T3B	T3C	—	—	—	—	—	—	—	—	—
		90 °C (194 °F)	55 °C (131 °F)	T3A	T3A	T3C	—	—	—	—	—	—	—	—	—
		90 °C (194 °F)	65 °C (149 °F)	T3A	T3A	T3C	—	—	—	—	—	—	—	—	—
100	Inc.	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3	—	—	—	—	—	—	—	—	—
		90 °C (194 °F)	55 °C (131 °F)	T3	T3	T3	—	—	—	—	—	—	—	—	—
		90 °C (194 °F)	65 °C (149 °F)	T2D	T2D	T3	—	—	—	—	—	—	—	—	—
150	Inc.	90 °C (194 °F)	40 °C (104 °F)	T2D	T2D	T3	—	—	—	—	—	—	—	—	—
		90 °C (194 °F)	55 °C (131 °F)	T2B	T2B	T2D	—	—	—	—	—	—	—	—	—
		90 °C (194 °F)	65 °C (149 °F)	T2B	T2B	T2D	—	—	—	—	—	—	—	—	—

“T” Numbers Represent the Maximum Lamp Temperature for Class I, Division 2 Locations and Maximum Surface Temperature Under Dust Blanket for Class II, Division 1 Locations.

“T” #	T1	350	325	T2	T2A	T2B	T2C	T2D	T3	T3A	T3B	T3C	T4	T4A	T5	T6
Temp. Range (°C)	351-450	326-350	301-325	281-300	261-280	231-260	216-230	201-215	181-200	166-180	161-165	136-160	121-135	101-120	86-100	85
Temp. Range (°F)	664-842	619-662	574-617	538-572	502-536	448-500	421-446	394-419	358-392	331-356	322-329	277-320	250-275	214-248	187-212	185

① “T” numbers are for Groups E and F only.

② Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.

# Mercmaster™ III Low Profile Luminaires

## Class I, Zone 2; Ex nR IIC; IP66; NEMA 4X

Temperature identification numbers of Mercmaster III Zone 2 Low Profile High Pressure Sodium and Pulse Start Metal Halide.

**CEC:**  
 Class I, Division 2, Groups A, B, C, D  
 Class I, Zone 2 Ex nR IIC (Z)  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III

**CEC:**  
 Type 4X  
 IP66

Watts	Lamp Type	Supply Wire Temp. °C (°F)	Ambient Temp. °C (°F)	Class I, Zone 2 AEx nA nR IIC / Ex nR IIC		
				Globe	Globe w/Reflector	Refractor
50	HPS	90 °C (194 °F)	40 °C (104 °F)	T6	T6	T6
		90 °C (194 °F)	55 °C (131 °F)	T5	T5	T5
		90 °C (194 °F)	65 °C (149 °F)	T4	T4	T5
70	HPS	90 °C (194 °F)	40 °C (104 °F)	T5	T5	T5
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T4
		90 °C (194 °F)	65 °C (149 °F)	—	—	T4
100	HPS	90 °C (194 °F)	40 °C (104 °F)	T4	T4	T4
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T4
150	HPS	90 °C (194 °F)	40 °C (104 °F)	T4	T4	T4
50	PSMH	90 °C (194 °F)	40 °C (104 °F)	T5	T5	T6
		90 °C (194 °F)	55 °C (131 °F)	T5	T5	T6
		90 °C (194 °F)	65 °C (149 °F)	T4	T4	T5
70	PSMH	90 °C (194 °F)	40 °C (104 °F)	T5	T5	T6
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T6
		110 °C (230 °F)	65 °C (149 °F)	—	—	T4
100	PSMH	90 °C (194 °F)	40 °C (104 °F)	T4	T4	T6
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T4
150	PSMH	105 °C (221 °F)	40 °C (104 °F)	T3	T3	T4
175	PSMH	105 °C (221 °F)	40 °C (104 °F)	T3	T3	T4
175	MH ①	110 °C (230 °F)	40 °C (104 °F)	—	—	T3

**"T" Numbers represent the maximum surface temperature for luminaires with Ex nR rating:**

The "T" number is established by separately determining the maximum temperature of the globe surface and ballast compartment. The hotter of the two is taken to determine the "T" number for the overall fixture.

"T" Number	T1	T2	T3	T4	T5	T6
Temp. Range (°C)	301-450	201-300	136-200	101-135	86-100	85
Temp. Range (°F)	547-842	394-572	277-392	214-275	187-212	185

① Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your country's governing legislation regarding allowable lamp types before ordering.