

Mercmaster™ III Low Profile Luminaires

High Pressure Sodium and Pulse Start Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Applications

- Enclosed and gasketed fixtures suitable for use in:
 - Marine and wet locations
 - A wide range of industrial, chemical processing and other areas where flammable gases and vapors or combustible dusts are present under conditions defined by the National Electrical Code as Class I, Division 2; Class II, Division 1 and 2; and Class III
 - Areas of low clearance, low ceiling heights or where fixture weights must be minimized
 - For Zone 2, the method of protection is AEx nA nR – Restricted Breathing/Nonsparking or AEx nR – Restricted Breathing
 - Non-hazardous locations where severe weather conditions, excessive moisture, dirt, dust, corrosive atmosphere or high ambient temperatures are encountered
- Typical applications include:
 - Pulp and paper mills
 - Processing plants
 - Chemical plants
 - Oil refineries
 - Foundries
 - Manufacturing plants
 - Storage areas
 - Waste and sewage treatment
 - Parking garages
 - Other areas where dust, water, dirt and rough usage are a problem

Features

- Compact light weight low profile design is suited for low mounting heights in conjunction with lower wattage fixtures.
- Modular design allows scores of fixture component combinations to meet installation and lighting needs. Uses same mounting hoods and optical accessories as Mercmaster III.
- A choice of heat-resistant prismatic glass refractors (NEMA I, III or V) or heat-resistant globes which thread directly into ballast housing. Photometrics available upon request – contact your local sales representative.
- Standard dome or 30° angle reflectors made of fiberglass reinforced white polyester. Highly resistant to corrosive atmospheres.
- Accommodates medium base lamps.
- A wide range of voltages available (120 to 600 Volt) and ballast types (Reactor, CWA and Super CWA).
- Medium base lamp type and watts:
 - HPS 50 W-150 W
 - PSMH 50 W-175 W
- Hinge has high lip for added safety during installation and servicing. Hinge and bolt construction assures 360° compression at all points on ballast housing gasket for positive sealing. Swing away design of captive bolt and nut simplifies servicing.
- All Mercmaster III mounting hoods have provision for easy field installation of fuses in fixtures (see fuse kits).
- Fixtures are for use in Class I, Zone 2 hazardous locations.
- The AEx nA nR factory sealed Mercmaster III prevents vapors and gases from entering the globe chamber. There are no seals or putty required which will reduce installation time and installation errors.



Low Profile Mercmaster III with Prismatic Globe and Guard

Standard Materials

- Mounting hoods, bodies and guard: cast copperfree (4/10 of 1% max.) aluminum
- All hardware and catch assemblies: stainless steel
- Reflectors: Fiberglass reinforced white polyester
- Globes and Refractors: heat-resistant prismatic glass

Standard Finishes

- Mounting hoods, bodies and guards: baked gray epoxy-clad finish, electrostatically applied for complete uniform protection

Options

- Quartz Auxiliary comes to full brightness immediately and remains lit until the HID lamp attains 60-70% of full illumination. Quartz Auxiliary supplied with relay switch and socket to accept 120 V quartz double-contact bayonet base lamp (not included). Add suffix **-E** ①.
- Guards with gray epoxy painted to match fixtures, supplied with stainless steel screws. Add suffix **-G** before voltage suffix.
- Hot Restrike to restrike HPS lamp immediately when power is restored after a momentary power interruption. Add suffix **-R**.
- Smart Starter incorporates a 1-1/2 minute timer and performs as a conventional starter to normally start lamp. Removes itself from circuit if lamp burns out or is removed from socket. Eliminates starter failures caused by prolonged operation with cycling or failing lamps and simplifies finding their location, reducing maintenance and repair costs. Available for all fixtures. Add suffix **-S**.
- AEx nA nR fixtures, add suffix **-Z2**.
- AEx nR fixtures, add suffix **-ZB**.
- Reflectors are available as standard dome and 30° angle polyester. Order separately.

NEC/CEC Certifications and Compliances ②

- cULus Listed: E10444
- UL Standard: ANSI/UL 844, 1598, 60079-0, 60079-15, Marine Type Electric Fixtures Outside Type (Salt Water)
- CSA Certified: 025428
- CSA Standard: CSA C22.2 No. 9, C22.2 No. 137; CAN/CSA E60079-0, E60079-15

Related Products

- Photocells for classified use are available, see *PCD2 Series*.

① Fixtures equipped with quartz auxiliary lamp do not comply with NEC/CEC requirements and are not suitable for use in classified locations.

② Compliance data varies for specific fixtures. Consult Appleton regarding suitability of specific fixtures for a particular application.

Mercmaster™ III Low Profile Luminaires

High Pressure Sodium and Pulse Start Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Illustrated Features



High Temperature Sockets

Medium base high-temperature porcelain sockets.

Aluminum Inner Reflector


Solid aluminum inner reflector (for refractor ballast housings only) improves photometric efficiency.

Globe Chamber

Completely sealed from the ballast housing and outside vapors/air (nR).

Electrical Protection

Ground wire provided to bond mounting hood to ballast housing.



Fuses

Two screws secure fuse kit to mounting boss in any Mercmaster mounting hood. Fuse included.

Photocell

Available for all fixtures except cone and ceiling mount. Installs through knock-out in mounting hood. Provides continuous ON-OFF dusk-to-dawn control.



Vented Reflectors

Reflectors are thick, tough fiberglass-reinforced white polyester, vented for cooler operation. Quickly attach with furnished stainless steel screws.

Stainless Steel Inserts

Ballast bodies have stainless steel threaded inserts to receive stainless steel screws for reflectors and guard. Prevents "freezing", allowing guards and reflectors to be easily removed and replaced at any time, without damage to the housing.

Epoxy Finish

Ballast housing, hoods and guards are copperfree aluminum with epoxy powder coat finish.

Prismatic Glass Globes and Refractors

Heat-resistant globes and refractors thread directly into ballast housing and seal against a high-temperature silicone rubber gasket.



"Safety" High Hinge

Extra-high hinge provides additional protection against accidental ballast housing disengagement during installation or maintenance.



Ballast Assembly

Utilizing non-sparking components avoiding the ignition of gases or vapors that may be present (nA).

Mounting Hood and Globe Gaskets

Silicone rubber gaskets seals out moisture, dirt and dust. Stays flexible, withstands high temperatures. Closure design assures uniform gasket compression.

Terminal Blocks (Zone 2)

A seven-point terminal block is provided to facilitate wiring. Terminal block accommodates wire size ranging from #8 to #24 AWG.



Cooler Operating Cone Hood

Larger sloped surface sheds dusts, dirt and combustible fibers providing better heat dissipation.



Stainless Steel Latch Assembly

Captive, stainless steel latch assembly bolt and nut closes securely, resists attack of corrosive atmospheres. Swing-away design simplifies servicing.

Appleton®

HID/AREA: NEC/CEC ENCLOSED AND GASKETED

Mercmaster™ III Low Profile Luminaires

High Pressure Sodium and Pulse Start Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.


NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Mercmaster III Low Profile Family Tree



① Mounting hood with a 120 V or 208-277 V factory installed photocell is available.

② Standard and deep dome reflectors may interfere with bottom conduit entry if used with KPST and KPWB mounting hoods..

③ Available in clear, amber, blue, green and red.

④ Available in NEMA Type II, III, IV and V. Polymeric Refractor suitable for Class II, Groups F and G, NEMA 4X and Marine Type Electric Fixtures Outside Type (Salt Water) only (100 W PSMH Max.).

⑤ Available in NEMA Type I, III and V.

Mercmaster™ III Low Profile Luminaires

High Pressure Sodium and Pulse Start Metal Halide

Listed for simultaneous exposure to combustible dusts and flammable gases or vapors.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Order using catalog numbering guide below or select catalog number from tables on following pages.

Catalog Numbering Guide

ML	A	L	15	2	G1	G	MT	R	Z2
Series: ML - Mercmaster III Low Profile		Lamp Type: I - Incandescent L - High Pressure Sodium P - Pulse Start Metal Halide		Hub Size: 2 - 3/4" NPT 3 - 1" NPT 4 - 1-1/4" NPT stanchion 5 - 1-1/2" NPT stanchion		Guard Options: G - Cast Guard N - No Guard		Options: E - Emergency Quartz ⑤ F - Fuse Kit (Specify Voltage) R - Hot Restrike ③ S - Smart Starter ④ H1 - Photocontrol 120 V H2 - Photocontrol 208 V H3 - Photocontrol 240 V H4 - Photocontrol 277 V D - E-27 Export Socket <i>Optional Fusing</i> ⑥ FN - 120 V FP - 208 V FS - 240 V FT - 277 V FF - 480 V	
	Mounting: A - Pendant (rigid mounting) C - Ceiling D - Pendant Cone Hood F - Pendant (flexible mounting) R - 90° Stanchion S - 25° Stanchion W - Wall	Wattage: 10 - 100 W HPS, PSMH 15 - 150 W HPS, PSMH and 60-150 W max. Incandescent 17 - 175 W PSMH 50 - 50 W HPS, PSMH 70 - 70 W HPS, PSMH		Optical Assembly: ② G1 - Globe J1 - NEMA I Glass Refractor J3 - NEMA III Glass Refractor J5 - NEMA V Glass Refractor P2 - NEMA II Polymeric Refractor P3 - NEMA III Polymeric Refractor P4 - NEMA IV Polymeric Refractor P5 - NEMA V Polymeric Refractor		Voltage: ① LB - Incandescent, 120, 60 Hz MT - 120/208/240/277, 60 Hz 5MT - 120/208/240/ 277/480, 60 Hz 48 - 480, 60 Hz 125 - 120, 50 Hz 225 - 225, 50 Hz 226 - 220, 60 Hz 236 - 230, 60 Hz 245 - 240, 50 Hz 246 - 240, 60 Hz		Suffix: Z2 - Zone 2 suffix (required for AEx nA nR rating) ZB - Zone 2 suffix (required for AEx nR)	

① Other voltages, frequencies available – contact your local sales representative. Voltages shown are limited to specific combinations; refer to following pages.

② Polymeric Refractor suitable for Class II, Groups F and G, NEMA 4X and Marine Type Electric Fixtures Outside Type (Salt Water) only (100 W PSMH Max.). Reflectors ordered separately.

③ Available for 50-150 W HPS fixtures only.

④ Available for HPS or PSMH fixtures.

⑤ Fixtures equipped with quartz auxiliary lamp do not comply with NEC/CEC requirements and are not suitable for use in classified locations

⑥ Optional fusing is available for use with MT, 5MT and 48 voltage suffixes ONLY.

Mercmaster™ III Low Profile Luminaires

Class I, Division 2; Class II, Division 1; Simultaneous exposure to hazardous conditions in both classifications

Temperature identification numbers of Mercmaster III Low Profile High Pressure Sodium and Pulse Start Metal Halide

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Lamp		Supply Wire Min.	Ambient Temp.	Class I, Division 2			Class II, Division 1 Groups E, F and G			Simultaneous Exposure Class I, Division 2 / Class II, Division 1		
Watts	Type	Temp. °C (°F)	°C (°F)	Globe	Reflector	Refractor	Globe	Reflector	Refractor	Globe	Reflector	Refractor
50	HPS	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3B	T4A	T4A	T5	T3	T3	T3
		90 °C (194 °F)	55 °C (131 °F)	T3	T3	T3A	T4A	T4A	T4A	T2D	T2D	T2D
		90 °C (194 °F)	65 °C (149 °F)	T3	T3	T3A	T4	T4	T4A	T2C	T2C	T2C
70	HPS	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3	T4	T4	T5	T2B	T2B	T2D
		90 °C (194 °F)	55 °C (131 °F)	T2D	T2D	T3	T3C	T3C	T4A	T2B	T2B	T2C
		90 °C (194 °F)	65 °C (149 °F)	—	—	T3	—	—	T4	—	—	T2B
100	HPS	90 °C (194 °F)	40 °C (104 °F)	T2C	T2C	T2D	T4	T4	T4A	T2B	T2B	T2B
		90 °C (194 °F)	55 °C (131 °F)	T2B	T2B	T2C	T3C	T3C	T4	T2A	T2A	T2A
		90 °C (194 °F)	65 °C (149 °F)	—	—	—	—	—	—	—	—	—
150	HPS	90 °C (194 °F)	40 °C (104 °F)	T2A	T2A	T2B	T3A ①	—	T4	325	—	T2
50	PSMH	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3A	T4A	T4A	T6	T2D	T2D	T3
		90 °C (194 °F)	55 °C (131 °F)	T3	T3	T3	T4	T4	T5	T2C	T2C	T2D
		90 °C (194 °F)	65 °C (149 °F)	T3	T3	T3	T4	T4	T4A	T2B	T2B	T2D
70	PSMH	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3	T3C	T3C	T4A	T2B	T2B	T2C
		90 °C (194 °F)	55 °C (131 °F)	T2D	T2D	T3	T3C	T3C	T4A	T2A	T2A	T2B
		110 °C (230 °F)	65 °C (149 °F)	—	—	T3	—	—	T4	—	—	T2B
100	PSMH	90 °C (194 °F)	40 °C (104 °F)	T2A	T2A	T2B	T3B	T3B	T4A	T2	T2	T2A
		90 °C (194 °F)	55 °C (131 °F)	T2A	T2A	T2B	T3A ①	T3A ①	T4	T1	T1	T2
150	PSMH	105 °C (221 °F)	40 °C (104 °F)	350	350	325	—	—	T3B	—	—	T1
175	PSMH	105 °C (221 °F)	40 °C (104 °F)	350	350	325	—	—	T3B	—	—	T1
60	Inc.	90 °C (194 °F)	40 °C (104 °F)	T3B	T3B	T3C	—	—	—	—	—	—
		90 °C (194 °F)	55 °C (131 °F)	T3A	T3A	T3C	—	—	—	—	—	—
		90 °C (194 °F)	65 °C (149 °F)	T3A	T3A	T3C	—	—	—	—	—	—
100	Inc.	90 °C (194 °F)	40 °C (104 °F)	T3	T3	T3	—	—	—	—	—	—
		90 °C (194 °F)	55 °C (131 °F)	T3	T3	T3	—	—	—	—	—	—
		90 °C (194 °F)	65 °C (149 °F)	T2D	T2D	T3	—	—	—	—	—	—
150	Inc.	90 °C (194 °F)	40 °C (104 °F)	T2D	T2D	T3	—	—	—	—	—	—
		90 °C (194 °F)	55 °C (131 °F)	T2B	T2B	T2D	—	—	—	—	—	—
		90 °C (194 °F)	65 °C (149 °F)	T2B	T2B	T2D	—	—	—	—	—	—

“T” Numbers Represent the Maximum Lamp Temperature for Class I, Division 2 Locations and Maximum Surface Temperature Under Dust Blanket for Class II, Division 1 Locations.

“T” #	T1	350	325	T2	T2A	T2B	T2C	T2D	T3	T3A	T3B	T3C	T4	T4A	T5	T6
Temp. Range (°C)	351-450	326-350	301-325	281-300	261-280	231-260	216-230	201-215	181-200	166-180	161-165	136-160	121-135	101-120	86-100	85
Temp. Range (°F)	664-842	619-662	574-617	538-572	502-536	448-500	421-446	394-419	358-392	331-356	322-329	277-320	250-275	214-248	187-212	185

① “T” numbers are for Groups E and F only.

Mercmaster™ III Low Profile Luminaires

Class I, Zone 2, AEx nA nR IIC, AEx nR IIC IP66, NEMA 4X

Temperature identification numbers of Mercmaster III Zone 2 Low Profile High Pressure Sodium and Pulse Start Metal Halide.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

Lamp		Class I, Zone 2 AEx nA nR IIC					Class I, Zone 2 AEx nR IIC		
Watts	Type	Supply Wire Temp. °C (°F)	Ambient Temp. °C (°F)	Globe	Globe w/ Reflector	Reflector	Globe	Globe w/ Reflector	Reflector
50	HPS	90 °C (194 °F)	40 °C (104 °F)	T6	T6	T6	T6	T6	T6
		90 °C (194 °F)	55 °C (131 °F)	T5	T5	T5	T5	T5	T5
		90 °C (194 °F)	65 °C (149 °F)	T4	T4	T5	T4	T4	T5
70	HPS	90 °C (194 °F)	40 °C (104 °F)	T5	T5	T5	T5	T5	T5
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T4	T4	T4	T4
		90 °C (194 °F)	65 °C (149 °F)	—	—	T4	—	—	T4
100	HPS	90 °C (194 °F)	40 °C (104 °F)	T4	T4	T4	T4	T4	T4
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T4	T4	T4	T4
150	HPS	90 °C (194 °F)	40 °C (104 °F)	T4	T4	T4	T4	T4	T4
50	PSMH	90 °C (194 °F)	40 °C (104 °F)	T5	T5	T6	T5	T5	T6
		90 °C (194 °F)	55 °C (131 °F)	T5	T5	T6	T5	T5	T6
		90 °C (194 °F)	65 °C (149 °F)	T4	T4	T5	T4	T4	T5
70	PSMH	90 °C (194 °F)	40 °C (104 °F)	T5	T5	T6	T5	T5	T6
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T6	T4	T4	T6
		110 °C (230 °F)	65 °C (149 °F)	—	—	T4	—	—	T4
100	PSMH	90 °C (194 °F)	40 °C (104 °F)	T4	T4	T6	T4	T4	T6
		90 °C (194 °F)	55 °C (131 °F)	T4	T4	T4	T4	T4	T4
150	PSMH	105 °C (221 °F)	40 °C (104 °F)	T3	T3	T4	T3	T3	T4
175	PSMH	105 °C (221 °F)	40 °C (104 °F)	T3	T3	T4	T3	T3	T4

“T” Numbers represent the maximum surface temperature for luminaires with AEx nA nR and AEx nR rating:

The “T” number is established by separately determining the maximum temperature of the globe surface and ballast compartment. The hotter of the two is taken to determine the “T” number for the overall fixture.

“T” Number	T1	T2	T3	T4	T5	T6
Temp. Range (°C)	301-450	201-300	136-200	101-135	86-100	85
Temp. Range (°F)	547-842	394-572	277-392	214-275	187-212	185

Appleton®

HID/AREA: NEC/CEC ENCLOSED AND GASKETED

Mercmaster™ III Low Profile Luminaires

50 W – 150 W HPS

High Power Factor (min. P.F. 90%). Medium base lamps.

NEC/CEC:

Class I, Division 2, Groups A, B, C, D
Class I, Zone 2, AEx nA nR IIC (Z2)
Class I, Zone 2, AEx nR IIC (ZB)
Class II, Division 1 and 2, Groups E, F, G
Class III

NEC/CEC:

Simultaneous Exposure
(Class I, Division 2/Class II, Division 1)
Fixtures Outside Type (Salt Water)
Type 4X
IP66

			Hub Size (Inches)	Catalog Numbers ③④⑤		
Lamp Type			Lamp Watts	With Globe	With Type V 8" Refractor ②	
Pendant — One Hub, Rigid Mounting ①						
	HPS	50	3/4 1	MLAL502G1N MLAL503G1N	MLAL502J5N MLAL503J5N	
	HPS	70	3/4 1	MLAL702G1N MLAL703G1N	MLAL702J5N MLAL703J5N	
	HPS	100	3/4 1	MLAL102G1N MLAL103G1N	MLAL102J5N MLAL103J5N	
	Shown with Globe and Optional Guard	HPS	150	3/4 1	MLAL152G1N ⑥ MLAL153G1N ⑥	MLAL152J5N ⑥ MLAL153J5N ⑥
	Pendant Cone — One Hub, Rigid Mounting					
		HPS	50	3/4 1	MLDL502G1N MLDL503G1N	MLDL502J5N MLDL503J5N
		HPS	70	3/4 1	MLDL702G1N MLDL703G1N	MLDL702J5N MLDL703J5N
HPS		100	3/4 1	MLDL102G1N MLDL103G1N	MLDL102J5N MLDL103J5N	
Shown with Refractor		HPS	150	3/4 1	MLDL152G1N ⑥ MLDL153G1N ⑥	MLDL152J5N ⑥ MLDL153J5N ⑥
Ceiling — Five Hubs, Four Close-up Plugs						
		HPS	50	3/4 1	MLCL502G1N MLCL503G1N	MLCL502J5N MLCL503J5N
		HPS	70	3/4 1	MLCL702G1N MLCL703G1N	MLCL702J5N MLCL703J5N
	HPS	100	3/4 1	MLCL102G1N MLCL103G1N	MLCL102J5N MLCL103J5N	
	Shown with Globe	HPS	150	3/4 1	MLCL152G1N ⑥ MLCL153G1N ⑥	MLCL152J5N ⑥ MLCL153J5N ⑥

① For Flexible Pendant Mount, change **A** to **F** in catalog number (except 50 W HPS).

② To order fixture with NEMA Type I or NEMA Type III refractor, change final digit **5** in catalog number to **1** or **3**.

③ For fixtures with guards, substitute a **G** for the **N** before adding voltage suffix. See following pages for accessory ordering information.

④ Add the following voltage and frequency designation before **Z2** suffix:

Lamp Type	Lamp Watts	LB	MT	5MT	48	125	Voltage Suffixes					
							225	226	235	236	245	246
Inc.	150 Max.	X	—	—	—	—	—	—	—	—	—	—
HPS	50	—	X	—	—	—	X	X	—	X	X	X
HPS	70	—	X	—	X	X	X	X	—	X	X	X
HPS	100	—	X	—	X	X	X	X	—	X	X	X
HPS	150	—	X	—	X	X	X	X	—	—	X	—
PSMH	50	—	X	—	X	—	—	—	—	—	—	—
PSMH	70	—	X	—	X	X	X	—	—	—	X	—
PSMH	100	—	X	—	X	X	X	—	—	—	X	—
PSMH	150	—	X	—	X	—	—	—	—	—	X	—
PSMH	175	—	X	X	X	—	—	—	—	—	X	—

Volts:

LB - Incandescent, 120 V 60 Hz

48 - 480 V 60 Hz

226 - 220 V 60 Hz

MT - 120/208/240/277 V 60 Hz

125 - 120 V 50 Hz

235 - 230 V 50 Hz

245 - 240 V 50 Hz

5MT - 120/208/240/277/480 V 60 Hz

225 - 225 V 50 Hz

236 - 230 V 60 Hz

246 - 240 V 60 Hz

⑤ Add **Z2** suffix for factory sealed non-sparking/restricted breathing protection (AEx nA nR). Add **ZB** suffix for restricted breathing protection (AEx nR).

⑥ For 150 W HPS fixtures, use S-55 lamp type only.

Mercmaster™ III Low Profile Luminaires

50 W – 150 W HPS

High Power Factor (min. P.F. 90%). Medium base lamps.

CEC:
Class I, Division 2, Groups A, B, C, D
Class I, Zone 2 Ex nR IIC (Z)
Class II, Division 1 and 2, Groups E, F, G
Class III

CEC:
Type 4X
IP66

		Lamp Type	Lamp Watts	Hub Size (Inches)	Catalog Numbers ③④⑤ With Globe	With Type V 8" Refractor ②
Pendant — One Hub, Rigid Mounting ①						
	HPS	50	3/4	MLAL502G1N	MLAL502J5N	
			1	MLAL503G1N	MLAL503J5N	
	HPS	70	3/4	MLAL702G1N	MLAL702J5N	
			1	MLAL703G1N	MLAL703J5N	
	HPS	100	3/4	MLAL102G1N	MLAL102J5N	
			1	MLAL103G1N	MLAL103J5N	
	Shown with Globe and Optional Guard	HPS	150	3/4	MLAL152G1N ⑥	MLAL152J5N ⑥
				1	MLAL153G1N ⑥	MLAL153J5N ⑥
Pendant Cone — One Hub, Rigid Mounting						
	HPS	50	3/4	MLDL502G1N	MLDL502J5N	
			1	MLDL503G1N	MLDL503J5N	
	HPS	70	3/4	MLDL702G1N	MLDL702J5N	
			1	MLDL703G1N	MLDL703J5N	
	HPS	100	3/4	MLDL102G1N	MLDL102J5N	
			1	MLDL103G1N	MLDL103J5N	
	Shown with Refractor	HPS	150	3/4	MLDL152G1N ⑥	MLDL152J5N ⑥
				1	MLDL153G1N ⑥	MLDL153J5N ⑥
Ceiling — Five Hubs, Four Close-up Plugs						
	HPS	50	3/4	MLCL502G1N	MLCL502J5N	
			1	MLCL503G1N	MLCL503J5N	
	HPS	70	3/4	MLCL702G1N	MLCL702J5N	
			1	MLCL703G1N	MLCL703J5N	
	HPS	100	3/4	MLCL102G1N	MLCL102J5N	
			1	MLCL103G1N	MLCL103J5N	
	Shown with Globe	HPS	150	3/4	MLCL152G1N ⑥	MLCL152J5N ⑥
				1	MLCL153G1N ⑥	MLCL153J5N ⑥

① For Flexible Pendant Mount, change **A** to **F** in catalog number (except 50 W HPS).

② To order fixture with NEMA Type I or NEMA Type III refractor, change final digit **5** in catalog number to **1** or **3**.

③ For fixtures with guards, substitute a **G** for the **N** before adding voltage suffix. See following pages for accessory ordering information.

④ Add the following voltage and frequency designation before **Z** suffix:

Lamp Type	Lamp Watts	LB	MT	TT	Voltage Suffixes			
					C2	C3	C6	C7
Inc.	150 Max.	X	—	—	—	—	—	—
HPS	50	—	X	X	—	—	—	—
HPS	70	—	X	X	X	X	X	X
HPS	100	—	X	X	X	X	X	X
HPS	150	—	X	X	X	X	X	X
PSMH	50	—	X	X	—	—	—	—
PSMH	70	—	X	X	—	—	—	—
PSMH	100	—	X	X	—	—	—	—
PSMH	150	—	X	X	—	—	—	—
PSMH	175	—	X	X	—	—	—	—
MH ⑦	175	—	—	X	X	X	X	X

Voltages:

LB - Incandescent, 120 V 60 Hz

MT - 120/208/240/277 V 60 Hz

TT - 120/277/347 V 60 Hz, CWA

C2 - 208 V 60 Hz, CWI

C3 - 240 V 60 Hz, CWI

C6 - 480 V 60 Hz, CWI

C7 - 600 V 60 Hz, CWI

⑤ Add **Z** for factory sealed restricted breathing protection (Ex nR)

⑥ For 150 W HPS fixtures, use S-55 lamp type only.

⑦ Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.