

Unicode™ 2 Series Fiberglass Reinforced Polyester Control Stations and Switches

Increased Safety

NEC:
 Class I, Division 2, Groups A, B, C, D
 Class II, Groups F, G
 Class III
 Ex de IIC/DIP A21
 IP66, Type 4X^①

CEC:
 Class I, Division 2, Groups A, B, C, D
 Class II, Groups F, G
 Class III; Type 4X^①
 Class I, Zone 1, AEx de IIC/ AEx tD 21
 IP66

ATEX/IECEx:
 Zone 1 and 2 – 21 and 22
 II 2 GD
 Ex de IIC/Ex demb IIC/ Ex tD A21
 IP66 – IK10

Applications

- Local control stations and motor control stations for use in hazardous areas covering the broadest possible range of applications.
- Control of equipment at:
 - Power plants
 - Chemical and petrochemical plants
 - Petroleum refineries
 - Reverse osmosis plants
 - Pulp and paper processing plants
 - Various industrial applications
- Push buttons and selector switches are used in conjunction with contactors or magnetic starters for remote control of motors in hazardous locations. They provide circuit control and/or selection.
- Pilot lights provide visual assurance that an electrical function is being performed at a remote or hazardous location.
- For use in washdown areas.

Features

- Employs Ex de method of protection which eliminates the need for external seals.
- Operators include push buttons, illuminated push buttons, selector switches, control and load break switches and LED pilot lights.
- Pilot light employs high intensity single LED with lifetime of 100,000 hours that can be used at:
 - 12 Vac to 254 Vac 50/60 Hz
 - 12 Vdc to 60 Vdc
- Up to 3 contact blocks per actuator can be used.
- Contact block technical data:
 - IEC rated operating voltage (Ue): 500 Vac – 110 Vdc
 - IEC switching capacity:
 - AC12: 16 Amp/400 Vac
 - AC14: 10 Amp/400 Vac
 - AC15: 6 Amp/500 Vac
 - DC13: 2 Amp/24 Vdc and 1 Amp/110 Vdc
 - NEMA switching capacity: A600: 10 Amp/600 Vac
- Selector switch technical data:
 - IEC rated operating voltage: 690 Vac
 - IEC rated operating current: maximum 16 Amp
 - IEC switching capacity:
 - AC1: 16 Amp/690 Vac
 - AC15: 16 Amp/415 Vac
 - AC3: 8 Amp/500 Vac
 - AC3: 4 Amp/690 Vac
 - AC3: 16 Amp/690 Vac
 - DC1: 10 Amp/24 Vdc
 - DC1: 6 Amp/60 Vdc
 - DC1: 6 Amp/110 Vdc (2 contacts wired in series)
 - DC1: 6 Amp/220 Vdc (3 contacts in series)
 - NEMA switching capacity: A600: 10 Amp/600 Vac
- Enclosures are rated for IP66 with firmly secured gasket.
- Operators and contact blocks are spaced for easy wiring.
- Wide selection of termination methods available.
- Choice of DIN rail mounted high performance contact block suitable for low intensity (less than 5 mA).
- TS35 rail mounted components are held securely in place during operation and easily removed for service.



U22W2PGA5

- Brass Inserts are provided for TS35 DIN rails or mounting plates to be installed inside the enclosure.
- Captive, corrosion resistant stainless steel cover screws.

Standard Materials

- Body and cover: fiberglass reinforced polyester (FRP) with black finish
- Cover screws: 316 stainless steel

Accessories

- Key for changing actuator blocks.
- Guard for mushroom head actuator.
- Padlockable guard.
- M5 and M6 earth stud.
- Combination drain and breather available in brass, polyamide and stainless steel.

Options

- Nameplates: Stainless Steel or Lamacoid with different color combinations.
- Padlocking facility at left, center, right or any position on selector switches.
- Padlocking facility for momentary and maintained push buttons.
- Special contact arrangements available, see *Unicode™ 2 Series Customized Control Stations*.

NEC/CEC Certifications and Compliances

- Certification Type CSPe
 - Temperature Class: T5 or T6
 - Ambient Temperature: -55°C to +60°C (-67°F to +140°F)
 - CAN/CSA Standards: C22.2 No. 0-M91, No. 25-M66, No. 213-M1987, No. 94-M91, No. 60079-0:07, No. 60529-2005, E60079-7-2003
 - UL Standards: 60079-0, 60079-7, 50
 - Other Standards: ANSI/IEC 60529-2004, ANSI/ISA 12.12.01-2011
 - cCSAus Certificate: 2356952

^① Overall hazardous location and ingress protection rating depends on the rating of the optional certified components used.

Unicode™ 2 Series Fiberglass Reinforced Polyester Control Stations and Switches

Increased Safety

CONTROLS: NEC/CEC, ATEX/IECEx INCREASED SAFETY CONTROL STATIONS

NEC:

Class I, Division 2, Groups A, B, C, D
Class II, Groups F, G
Class III
Ex de IIC/DIP A21
IP66, Type 4X①

CEC:

Class I, Division 2, Groups A, B, C, D
Class II, Groups F, G
Class III; Type 4X①
Class I, Zone 1, AEx de IIC/ AEx tD 21
IP66

ATEX/IECEx:

Zone 1 and 2 – 21 and 22
Ex II 2 GD
Ex de IIC/Ex demb IIC/ Ex tD A21
IP66 – IK10

ATEX/IECEx Certification and Compliances

- Certification Type CSPe
 - Gas: Zone 1 and 2
 - Conforming to ATEX 94/9/CE: Ex II 2 G
 - Type of Protection: Ex de IIC/Ex demb IIC
 - Temperature Class: T6
 - Dust: Zone 21 and 22
 - Conforming to ATEX 94/9/CE: Ex II 2 D
 - Type of Protection: Ex tD A21
 - Surface Temperature: T75 °C (T167 °F)
 - Ambient Temperature: -55 °C to +60 °C (-67°F to +140°F)
(empty enclosure, temperature to be determine according actuator)
 - CE Declaration of Conformity: 52084
 - ATEX Certificate: LCIE 00 ATEX 3032X
 - IECEx Certificate: IECEx LCI 09.0016X

EURASEC Certification

- Certification Type CSPe
 - EURASEC RU C-FR Г505.B.00911

Other Certification ②

- Certification Type CSPe
 - INMETRO Certificate: BVC 11.0637-X

① Overall hazardous location and ingress protection rating depends on the rating of the optional certified components used.
② INMETRO certification available on special request only. Contact your local sales representative for more information.

Unicode™ 2 Series Fiberglass Reinforced Polyester Control Stations and Switches

Increased Safety







NEC:
Class I, Division 2, Groups A, B, C, D
Class II, Groups F, G
Class III
Ex de IIC/DIP A21
IP66, Type 4X①

CEC:
Class I, Division 2, Groups A, B, C, D
Class II, Groups F, G
Class III; Type 4X①
Class I, Zone 1, AEx de IIC/ AEx tD 21
IP66

ATEX/IECEX:
Zone 1 and 2 – 21 and 22
Ex II 2 GD
Ex de IIC/Ex demb IIC/ Ex tD A21
IP66 – IK10

Size 2 Polyester Control Station

Included: 1 white self-adhesive laminated plastic nameplate, 1 brass earth continuity plate, 1 blanking plug ②, 1 cable gland ②.

Description/Function	Diagram	Entry Location	Entry Size	Weight kg (lb)	Volume dm³ (in³)	Catalog Number
Twin Push Buttons + Push-Pull Emergency Stop						
 1x green push button 'I' with 1NO contacts 1x red push button 'O' with 1NC contacts momentary contacts 1x red mushroom head push-pull with 1x NC maintained contact		Bottom	2 x M20	1.3 (2.87)	4.0 (244.10)	U22W2A5A9D9
		Bottom	2 x M25	1.3 (2.87)	4.0 (244.10)	U22W4A5A9D9
		Feed-Thru	1 x 3/4"	1.3 (2.87)	4.0 (244.10)	U22Z3A5A9D9
		Feed-Thru	2 x 3/4"	1.3 (2.87)	4.0 (244.10)	U22X3A5A9D9
Pilot Light + Push Button						
1x green light ③ 1x green push button 'I' with 1NO momentary contact		Bottom	2 x M20	1.2 (2.65)	4.0 (244.10)	U22W2PGA5
		Bottom	2 x M25	1.2 (2.65)	4.0 (244.10)	U22W4PGA5
		Feed-Thru	1 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22Z3PGA5
		Feed-Thru	2 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22X3PGA5
 1x green light ③ 1x green push button 'I' with 1NO + 1NC momentary contacts		Bottom	2 x M20	1.2 (2.65)	4.0 (244.10)	U22W2PGA3
		Bottom	2 x M25	1.2 (2.65)	4.0 (244.10)	U22W4PGA3
		Feed-Thru	1 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22Z3PGA3
		Feed-Thru	2 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22X3PGA3
1x red light ③ 1x red push button 'O' with 1NC momentary contact		Bottom	2 x M20	1.2 (2.65)	4.0 (244.10)	U22W2PRA9
		Bottom	2 x M25	1.2 (2.65)	4.0 (244.10)	U22W4PRA9
		Feed-Thru	1 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22Z3PRA9
		Feed-Thru	2 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22X3PRA9
1x red light 1x red push button 'O' with 1NO + 1NC momentary contact		Bottom	2 x M20	1.2 (2.65)	4.0 (244.10)	U22W2PRA3
		Bottom	2 x M25	1.2 (2.65)	4.0 (244.10)	U22W4PRA3
		Feed-Thru	1 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22Z3PRA3
		Feed-Thru	2 x 3/4"	1.2 (2.65)	4.0 (244.10)	U22X3PRA3

Additional combinations available, please refer to Unicode 2 Series - Customized Control Stations section.

① Overall hazardous location and ingress protection rating depends on the rating of the optional certified components used.

② Not included if NPT hubs are selected.

③ 12 Vac to 254 Vac 50/60 Hz - 12 Vdc to 60 Vdc.