

Contender™ 4/4X Series Factory Sealed Control Stations

NEC/CEC:

Class I, Division 2, Groups B, C, D

Class I, Zone 2, Group IIB+H2

Class II, Division 1 and 2, Groups E, F, G

Class III

NEC/CEC:

Type 3, 3R, 4*, 4X*, 12

IP66 ▲

Applications

- For use in washdown and other damp, wet and highly corrosive or dusty areas where ignitable vapors, gases or highly combustible dusts are abnormally present.
- Push buttons and selector switches are used in conjunction with contactors or magnetic starters for remote control of motors.
- Pilot lights provide visual assurance that an electrical function is being performed at a remote or local hazardous location.

Features

- Covers are UL Classified for use with Crouse-Hinds+ EDS series back boxes.
- Corrosion resistant captive stainless steel screws holds cover to back box.
- Silicone cover gasket ensures high degree of water and dust ingress protection.
- The Labyrinth switch used in push buttons and selector switches, is rated A600 heavy pilot duty and P150.
- Temperature rating: -25 °C to +40 °C (-13 °F to +104 °F).
- Wide variety of devices and options results in a control station tailor-made to the application.
- Improved pilot light features enhanced circuitry to prevent induced voltage.
- Pilot light employs LED cluster with lifetime of 100,000 hours that can be used at either 120 Vac or 240 Vac. Optional pilot light can be used at either 12 or 24 Vac/Vdc.
- Back Box furnished with internal ground screw.
- Factory sealed, no external seals required.
- Selector switch knob and momentary push button guard accepts 1/4" padlocks to prevent unauthorized startup or turnoff.

Standard Materials

- Back box: malleable iron or optional copperfree (4/10 of 1% max.) aluminum
- Cover: die-cast aluminum
- Screws: stainless steel
- Gasket: silicone
- O-Rings: buna n

Standard Finishes

- Malleable iron back box: triple coat—(1) zinc electroplate, (2) chromate, and (3) epoxy powder coat
- Cover and optional aluminum back box: epoxy powder coat

Options

- 1- or 2-gang aluminum back box for Type 4X rating, add suffix **-A**.
- UCPL pilot light. Standard color is red. Order by suffixes if color desired is other than red, as follows:
 - Green **-JGBG**
 - Amber **-JGBA**
 - Blue **-JGBB**
 - White **-JGBW**
- For 12 or 24 Vac/Vdc pilot light rating, add suffix **-DC**
- Standard momentary push button colors are listed next to catalog numbers for assembled control stations. Order by suffixes for desired color as follows:
 - Red **-PBRE**
 - Green **-PBGR**
 - Black **-PBBL**

▼ Product with iron back box is Type 4 rated and Type 4X with aluminum back box.

▲ When a pilot light is selected, assembly is rated IP56.

+ Crouse-Hinds is a registered trademark of Cooper Crouse-Hinds.




1-Gang Push Button and Pilot Light



1-Gang HOA Selector Switch



1-Gang Emergency Stop Push Button



2-Gang Push Buttons and Pilot Lights

- Push button front operated mushroom head (maintained contact). Standard color is red. Order by suffixes if color desired is other than red, as follows:
 - Green **-NMRBMGR**
 - Black **-NMRBMBL**
- Push button front operated mushroom head (momentary contact). Order by suffixes if color desired is other than black, as follows:
 - Red **-NMRBRE**
 - Green **-NMRBGR**
 - Black **-NMRBBL**
- Three position selector switches with modified operation:
 - Momentary contact right position, spring return to center, maintained contact left position add suffix **-SRC**.
 - Momentary contact left position, spring return to center, maintained contact right position add suffix **-SLC**.
 - Momentary contact left and right positions, spring return to center with alternate contacts add suffix **-SRLALT**.
 - Alternate contacts add suffix **-ALT**.

NEC/CEC Certifications and Compliances

- UL Standards: UL 508, UL 698, UL 1203, UL 1604, ISA 12.12.01
- CSA Standards: C22.2 No. 14-M, C22.2 No. 213-M, C22.2 No. 25, C22.2 No. 30
- cULus Listed: E10449, E81751, E157407

APPLETON™

CONTROLS: NEC/CEC EXPLOSIONPROOF CONTROL STATIONS AND SWITCHES

Contender™ 4/4X Series Factory Sealed Control Stations

NEC/CEC:

Class I, Division 2, Groups B, C, D

Class I, Zone 2, Group IIB+H2

Class II, Division 1 and 2, Groups E, F, G

Class III

Standard Legend Plates ①

Description	Catalog Number	Description	Catalog Number
Two Position Selector Switch			
Forward—Reverse	UCLP-FR	Run—Jog	UCLP-RG
Hand—Auto	UCLP-HA	Off—Remote	UCLP-OR
On—Off	UCLP-00	Auto—Hand	UCLP-AH
Start—Stop	UCLP-SS	Auto—Off	UCLP-AO
Local—Remote	UCLP-LR	Off—Auto	UCLP-0A
Up—Down	UCLP-UD	Blank	UCLP-B
Three Position Selector Switch			
Reverse—Off—Forward	UCLP-R0F	Hand—Off—Remote	UCLP-H0R
Forward—Off—Reverse	UCLP-F0R	Local—Off—Remote	UCLP-L0R
Hand—Off—Auto	UCLP-H0A	Remote—Off—Local	UCLP-R0L
Auto—Off—Hand	UCLP-A0H	Auto—Off—Manual	UCLP-A0M
Jog—Off—Run	UCLP-J0R	Open—Off—Close	UCLP-00C
Run—Off—Jog	UCLP-R0J	Test—Off—On	UCLP-T00
Off—Run—Start	UCLP-0RS	1—Off—2	UCLP-102
Stop—Run—Start	UCLP-SRS	Blank	UCLP-B
Jog—Off—Auto	UCLP-J0A	Emergency Stop	UCLP-ESTP
Push Buttons (Standard, Momentary and Maintained Mushroom Heads)			
Blank	UCLP-B	Fast	UCLP-FAST
Off	UCLP-OFF	Slow	UCLP-SLOW
On	UCLP-ON	Raise	UCLP-RAISE
Forward	UCLP-FWD	Lower	UCLP-LOWER
Reverse	UCLP-REV	Open	UCLP-OPEN
Jog	UCLP-JOG	Close	UCLP-CLOSE
Run	UCLP-RUN	Low	UCLP-LOW
Start	UCLP-ST	High	UCLP-HIGH
Stop	UCLP-SP	Test	UCLP-TEST
Up	UCLP-UP	Reset	UCLP-RESET
Down	UCLP-DOWN	Emergency Stop	UCLP-ESTP
Pilot Lights			
Blank	UCPLP-B	On	UCPLP-ON
Run	UCPLP-RUN	Off	UCPLP-OFF
Stop	UCPLP-SP	Open	UCPLP-OPEN
		Start	UCPLP-CLOSE



① Custom legend plates are available. Contact your local sales representative for details.