

Unicode™ 2 Series Polyamide Control Stations

Increased Safety

For use in IEC governed hazardous areas. Polyamide is not recognized for use in any NEC/CEC governed hazardous areas.

ATEX:

Zone 1 and 2 – 21 and 22

II 2 GD

Ex de IIC/Ex demb IIC/Ex tD A21

IP66 – IK09

Applications

- For use in IEC governed hazardous areas. Polyamide is not recognized for use in any NEC/CEC governed hazardous areas.
- Local control stations and motor control stations for use in hazardous areas covering the broadest possible range of applications.
- Control of equipment at:
 - Power plants
 - Chemical and petrochemical plants
 - Petroleum refineries
 - Reverse osmosis plants
 - Pulp and paper processing plants
 - Various industrial applications
- Push buttons and selector switches are used in conjunction with contactors or magnetic starters for remote control of motors in hazardous locations. They provide circuit control and/or selection.
- Pilot lights provide visual assurance that an electrical function is being performed at a remote or hazardous location.
- For use in washdown areas.

Features

- Employs Ex de method of protection which eliminates the need for external seals.
- Operators include push buttons, illuminated push buttons, selector switches, control and load break switches and LED pilot lights.
- Pilot light employs high intensity single LED with lifetime of 100,000 hours that can be used at:
 - 12 Vac to 254 Vac 50/60 Hz
 - 12 Vdc to 60 Vdc
- Up to 3 contact blocks per actuator can be used.
- Contact block technical data:
 - IEC rated operating voltage (Ue): 500 Vac – 110 Vdc
 - IEC switching capacity:
 - AC12: 16 Amp/400 Vac
 - AC14: 10 Amp/400 Vac
 - AC15: 6 Amp/500 Vac
 - DC13: 2 Amp/24 Vdc and 1 Amp/110 Vdc
 - NEMA switching capacity: A600: 10 Amp/600 Vac
- Selector switch technical data:
 - IEC rated operating voltage: 690 Vac
 - IEC rated operating current: maximum 16 Amp
 - IEC switching capacity:
 - AC1: 16 Amp/690 Vac
 - AC15: 16 Amp/415 Vac
 - AC3: 8 Amp/500 Vac
 - AC3: 4 Amp/690 Vac
 - AC3: 16 Amp/690 Vac
 - DC1: 10 Amp/24 Vdc
 - DC1: 6 Amp/60 Vdc
 - DC1: 6 Amp/110 Vdc (2 contacts wired in series)
 - DC1: 6 Amp/220 Vdc (3 contacts in series)
 - NEMA switching capacity: A600: 10 Amp/600 Vac
- Enclosures are rated for IP66 with firmly secured gasket.
- Operators and contact blocks are spaced for easy wiring.
- Wide selection of termination methods available.
- Choice of DIN rail mounted high performance contact block suitable for low intensity (less than 5 mA).



U43W2 VA13A5A9



U42W2 A5A9

- TS35 rail mounted components held securely in place during operation and easily removed for service.
- Brass Inserts are provided for TS35 DIN rails or mounting plate to be installed inside the enclosure.
- Captive, corrosion resistant stainless steel cover screws.

Standard Materials

- Body, cover, cable gland and blanking plug: polyamide, black finish
- Cover screws: stainless steel
- Optional nameplates: stainless steel

Accessories

- Key for changing actuator blocks.
- Guard for mushroom head actuator.
- Padlockable guard.
- M5 earth stud.
- Combination drain and breather available in brass, polyamide and stainless steel.

Options

- Nameplates: Lamacoid with different color combinations.
- Padlocking ability at left, center, right or any position on selector switches.
- Padlocking ability for momentary and maintained push buttons.
- Special contact arrangements available, see *Unicode 2 Series Customized Control Stations*.

Unicode™ 2 Series Polyamide Control Stations

Increased Safety

For use in IEC governed hazardous areas. Polyamide is not recognized for use in any NEC/CEC governed hazardous areas.

ATEX:

Zone 1 and 2 – 21 and 22

⊕ II 2 GD

Ex de IIC/Ex demb IIC/Ex tD A21

IP66 – IK09

ATEX Certifications and Compliances

- Certification Type PCe
 - Gas: Zone 1 and 2
 - Conforming to ATEX 94/9/CE: ⊕ II 2 G
 - Type of Protection: Ex de IIC/Ex demb IIC (depending of the actuator)
 - Temperature Class: T6
 - Dust: Zone 21 and 22
 - Conforming to ATEX 94/9/CE: ⊕ II 2 D
 - Type of Protection: Ex tD A21
 - Surface Temperature: T75 °C (T167 °F)
 - Ambient Temperature: -20 °C to +55 °C (-4 °F to +131 °F)
 - CE Declaration of Conformity: 50221
 - ATEX Certificate: LCIE 00 ATEX 6047
 - Index of Protection according EN/IEC 60529: IP66
 - Impact Resistance (shock): IK09

EURASEC Certification

- EURASEC RU C-FR ГБ05.В.00911

Other Certification ①

- INMETRO Certificate: BVC 11.0640-X

① INMETRO certification available on special request only. Contact your local sales representative for more information.

Unicode™ 2 Series Polyamide Control Stations

Increased Safety

For use in IEC governed hazardous areas. Polyamide is not recognized for use in any NEC/CEC governed hazardous areas.

ATEX:
 Zone 1 and 2 – 21 and 22
 II 2 GD
 Ex de IIC/Ex demb IIC/Ex tD A21
 IP66 – IK09

CONTROLS: NEC/CEC, ATEX/IECex INCREASED SAFETY CONTROL STATIONS

Size 1 Polyamide Control Station:

Included: 1 white self-adhesive laminated plastic nameplate, 2 x M20 bottom clearance entries, 1 blanking plug, 1 cable gland in polyamide [Ø 6.5 mm to 14.5 mm (0.26" to 0.57")], 2 locknuts.




Description/Function	Diagram	Bottom Entries	Weight kg (lb)	Volume dm³ (in³)	Catalog Number
Pilot Light					
1x red pilot light ①		2 x M20	0.48 (1.06)	2.5 (152.56)	U41W2PR
1x green pilot light ①		2 x M20	0.48 (1.06)	2.5 (152.56)	U41W2PG
1x blue pilot light ①		2 x M20	0.48 (1.06)	2.5 (152.56)	U41W2PB
1x yellow pilot light ①		2 x M20	0.48 (1.06)	2.5 (152.56)	U41W2PY
1x white pilot light ①		2 x M20	0.48 (1.06)	2.5 (152.56)	U41W2PW

2-Position Selector Switch



2 fixed positions '0 - I'
 1NO + 1NC contacts




2 x M20 0.48 (1.06) 2.5 (152.56) U41W2H3

3-Position Selector Switch




3 fixed positions 'I - 0 - II'
 2NO contact




2 x M20 0.48 (1.06) 2.5 (152.56) U41W2J1

3 positions 'I - 0 - II'
 With spring return from I to 0
 1NO + 1NC contacts



2 x M20 0.48 (1.06) 2.5 (152.56) U41W2N3

3 positions 'I - 0 - II'
 With spring return from II to 0
 1NO + 1NC contacts



2 x M20 0.48 (1.06) 2.5 (152.56) U41W2M3

Size 2 Polyamide Control Station:

Included: 1 white self-adhesive laminated plastic nameplate, 2 x M20 bottom clearance entries, 1 blanking plug, 1 cable gland in polyamide [Ø 6.5 mm to 14.5 mm (0.26" to 0.57")], 2 locknuts.



Description/Function	Diagram	Bottom Entries	Weight kg (lb)	Volume dm³ (in³)	Catalog Number
Twin Push Button					
1x green push button 'I' with 1NO contact 1x red push button 'O' with 1NC contact Momentary contacts		2 x M20	0.62 (1.37)	2.5 (152.56)	U42W2A5A9
1x green push button 'I' with 1NO + 1NC contacts 1x red push button 'O' with 1NO + 1NC contacts Momentary contacts		2 x M20	0.62 (1.37)	2.5 (152.56)	U42W2A3A3

① 12 Vac to 254 Vac 50/60 Hz - 12 Vdc to 60 Vdc.

Unicode™ 2 Series Polyamide Control Stations


Increased Safety

For use in IEC governed hazardous areas. Polyamide is not recognized for use in any NEC/CEC governed hazardous areas.


ATEX:
 Zone 1 and 2 – 21 and 22
 II 2 GD
 Ex de IIC/Ex demb IIC/Ex tD A21
 IP66 – IK09

CONTROLS: NEC/CEC, ATEX/IECex INCREASED SAFETY CONTROL STATIONS


Dimensions in Millimeters (Inches)




Size 1 Enclosure




Size 1 Mounting/Fixing Details



Size 2 Enclosure



Size 2 and 3 Mounting/Fixing Details



Size 3 Enclosure