

Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.
Hazardous Location.

NEC: Class I, Division 2, Groups A, B, C, D

CEC: Class I, Division 2, Groups A, B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Enclosure 4X

Applications

- Enclosed and gasketed lighting fixtures for use in storage areas, tunnels, subways, chemical plants and other areas where moisture, dirt or corrosive atmospheres are a problem.
- Suitable for use in wet locations.
- Standard fixtures designed for 60 to 300 Watt medium base incandescent lamps.
- Pendant, feed-thru, ceiling, stanchion and wall mounts available.

Features

- Modern styling, with clean-line mounting hood and prismatic glass globe, plus optional guard.
- Prismatic globe, furnished as standard, eliminates glare and distributes light evenly.
- Globe seats firmly against composition gasket in mounting hood to keep out dirt and moisture. Full threads eliminate “cross threading.”
- Fixture is complete with gaskets and socket. Socket is shock-absorbing to prolong lamp life and can be easily removed for wiring without tools.
- Porcelain socket construction assures long trouble-free operation in high ambient installations.
- Guards have exclusive snap-on attachment feature for quick installation and fast servicing.
- Maximum input voltage 277 V (suitable for DC applications).

Standard Materials

- Mounting hoods: copperfree (4/10 of 1% max.) aluminum
- Guards: pressure cast copperfree (4/10 of 1% max.) aluminum
- Socket: porcelain with brass screw shell
- Globes: prismatic glass

Standard Finishes

- Mounting hoods and guards: epoxy powder coat
- Socket and globes: natural finish

Options

- To order fixture with other than standard clear glass globe, add suffix letters to catalog number as indicated in table, and adjust difference in price.

Color	Glass Globe	Plastic Globe
Amber	-AM	-PAM
Blue	-BL	-PBL
Green	-GR	-PGR
Red	-RE	-PRE
Clear Heat-Resistant	-HR	—

NEC/CEC Certifications and Compliances

- UL Standard: UL 1598, UL 844
- UL Listed: E10444
- CSA Standard: C22.2 No. 250, C22.2 No. 137
- CSA Certified: 025428



Illustrated Features



Mounting Hood

Pendant style shown has setscrew to prevent fixture stem from turning. Other styles include stanchion, ceiling and wall mounting.



Shock-Absorbing Medium Base Socket

Spring absorbs vibration to prolong lamp life. Porcelain construction for trouble-free operation in high ambient installations.



Globe

Attractive, tapered prismatic glass globes for glare elimination and uniform light distribution. Colors available – also vandal-resistant plastic globes. Globe seats firmly against gasket to exclude moisture, dirt and vapors.

Guard

Snap-on guards (and reflectors) – simply snap-in and twist. Spring action balls snap into detents of fixture body.

Guard



Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.
Hazardous Location.

NEC: Class I, Division 2, Groups A, B, C, D

CEC: Class I, Division 2, Groups A, B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Enclosure 4X

				Catalog Numbers		
		Type	Lamp Watts	Color	Glass ③	Polycarbonate ④
Glass and Polycarbonate Globes ①						
		A-23	60-200	Clear	—	VPGL-2PL
				Clear Heat-Resistant	VPGL-1HR	—
				Amber	VPGL-1AM	VPGL-2AMPL
				Blue	VPGL-1BL	VPGL-2BLPL
				Green	VPGL-1GR	VPGL-2GRPL
				Red	VPGL-1RE	VPGL-2REPL
Glass Globes						
	PS-30	200-300	Clear	—	—	
			Clear Heat-Resistant	VPGL-2HR	—	
			Amber	VPGL-2AM	—	
			Blue	VPGL-2BL	—	
			Green	VPGL-2GR	—	
			Red	VPGL-2RE	—	
Coated Tuff-Skin® ② Glass Globes Contains globe safely even if glass is broken ④						
	Heat-Resistant			VPGL-2HRT ④	—	
VPGL-2HRT ④						
		Type	Lamp Watts	Catalog Numbers		
				NEC	CSA	
Guards						
		A-23	60-200	VPGU-1	VCFGU-1	
		PS-30	200-300	VPGU-2	VCFGU-2	
Replacement Porcelain Shock-Absorbing Sockets						
		A-23	60-200	VPLR-123	VCLR-1	
		PS-30	200-300			
		Medium Base				
Replacement Gasket for Globes						
		Neoprene – for all Stylmaster globes			VPGL-GK	VCGL-GK
		Globe Gasket				

① Shatter-resistant for use in food processing plants, canneries, dairies, breweries, bakeries or anywhere broken glass would prove a hazard. Ideally suited for areas where vandalism, high replacement and high maintenance costs are a problem. CAUTION: Use maximum 200 W lamp less reflector, 100 W max. with reflector or colored globe. Do not use in ambients exceeding 25 °C/77 °F. For burning in vertical base-up position only.

② Registered trademark of Thomas Manufacturing Corporation, Parkton, Md.

③ Only listed for UL/NEC Fixtures.

④ Not an UL Listed option.

Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.
Hazardous Location.

NEC: Class I, Division 2, Groups A, B, C, D
CEC: Class I, Division 2, Groups A, B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Enclosure 4X

Weights

Typical Mounting Hoods

Pendant	kg (lb)	Ceiling	kg (lb)	Wall	kg (lb)	Stanchion	kg (lb)
VPA75	0.9 (1.98)	VPX75	0.9 (1.98)	VPOBW10	1.4 (3.09)	VPAN-125	1.4 (3.09)
VCA75		VCX75		VCOWB10		VCAN-125	

Globes and Guards

Type	Globe	kg (lb)	Guard	kg (lb)
60-200 W	VPGL-1	0.9 (1.98)	VPGU-1	0.5 (1.10)
200-300 W	VPGL-2	1.4 (3.09)	VPGU-2	0.5 (1.10)