

Stylmaster™ HID Globes, Guards and Gasket

	Item	Description	Catalog Number	
Glass Globe 	Prismatic Glass Globes			
	Coated Glass Globe 	For 50 W-150 W HPS, and 175 W-250 W MH	Clear*	VPGL-2
			Clear Heat-Resistant*	VPGL-2HR
			Amber	VPGL-2AM
			Blue	VPGL-2BL
			Green	VPGL-2GR
		Red	VPGL-2RE	
Polycarbonate Globe 	Coated "Tuff-Skin"®† Glass Globes			
	For use in areas where fixture is subject to extreme thermal shock	Clear Heat-Resistant	VPGL-2HRT	
	Polycarbonate Globes — Impact-Resistant**			
	Guard 	Use 100-watt lamp max. Do not use in ambients exceeding 25 °C	Clear	VPGL-2PL
			Amber	VPGL-2AMPL
		Green	VPGL-2GRPL	
		Red	VPGL-2REPL	
Copper-Free Aluminum Guard				
Socket 	50 W-150 W HPS, and 175 W-250 W MH (Mogul Base)	Pendant	VPTS-2	
		Wall & Ceiling	VPLR-25	
Globe Gasket 	Replacement Porcelain Shock-Absorbing Socket			
	Replacement Globe Gasket — Silicone Rubber			
	50 W-150 W HPS, and 175 W-250 W MH		VPGL-GK	

* Heat-resistant glass furnished as standard with 150 W HPS and 175 W and 250 W MH. Clear glass furnished as standard with 50 W-100 W HPS.

** Polycarbonate globes are shatter-resistant – for use in processing plants, canneries, dairies, bakeries or anywhere broken glass would prove a hazard. Ideally suited for areas where vandalism and high replacement and high maintenance costs are a problem. Do not use in ambients exceeding 25 °C. For burning in vertical base up position only.

† Registered Trademark of Thomas Manufacturing Corporation, Parkton, Md. It is recommended that guards be used with these globes.