

Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.
Hazardous Location.

NEC: Class I, Division 2, Groups A, B, C, D
CEC: Class I, Division 2, Groups A, B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Enclosure 4X

Applications

- Enclosed and gasketed lighting fixtures for use in storage areas, tunnels, subways, chemical plants and other areas where moisture, dirt or corrosive atmospheres are a problem.
- Suitable for use in wet locations.
- Standard fixtures designed for 60 to 300 Watt medium base incandescent lamps.
- Pendant, feed-thru, ceiling, stanchion and wall mounts available.

Features

- Modern styling, with clean-line mounting hood and prismatic glass globe, plus optional guard.
- Prismatic globe, furnished as standard, eliminates glare and distributes light evenly.
- Globe seats firmly against composition gasket in mounting hood to keep out dirt and moisture. Full threads eliminate “cross threading.”
- Fixture is complete with gaskets and socket. Socket is shock-absorbing to prolong lamp life and can be easily removed for wiring without tools.
- Porcelain socket construction assures long trouble-free operation in high ambient installations.
- Guards have exclusive snap-on attachment feature for quick installation and fast servicing.
- Maximum input voltage 277 V (suitable for DC applications).

Standard Materials

- Mounting hoods: copperfree (4/10 of 1% max.) aluminum
- Guards: pressure cast copperfree (4/10 of 1% max.) aluminum
- Socket: porcelain with brass screw shell
- Globes: prismatic glass

Standard Finishes

- Mounting hoods and guards: epoxy powder coat
- Socket and globes: natural finish

Options

- To order fixture with other than standard clear glass globe, add suffix letters to catalog number as indicated in table, and adjust difference in price.

Color	Glass Globe	Plastic Globe
Amber	-AM	-PAM
Blue	-BL	-PBL
Green	-GR	-PGR
Red	-RE	-PRE
Clear Heat-Resistant	-HR	—

NEC/CEC Certifications and Compliances

- UL Standard: UL 1598, UL 844
- UL Listed: E10444
- CSA Standard: C22.2 No. 250, C22.2 No. 137
- CSA Certified: 025428




Illustrated Features



Mounting Hood

Pendant style shown has setscrew to prevent fixture stem from turning. Other styles include stanchion, ceiling and wall mounting.



Shock-Absorbing Medium Base Socket

Spring absorbs vibration to prolong lamp life. Porcelain construction for trouble-free operation in high ambient installations.



Globe

Attractive, tapered prismatic glass globes for glare elimination and uniform light distribution. Colors available – also vandal-resistant plastic globes. Globe seats firmly against gasket to exclude moisture, dirt and vapors.

Guard



Guard

Snap-on guards (and reflectors) – simply snap-in and twist. Spring action balls snap into detents of fixture body.

Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.
Hazardous Location.

NEC: Class I, Division 2, Groups A, B, C, D
CEC: Class I, Division 2, Groups A, B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Enclosure 4X

				Catalog Numbers		
		Type	Lamp Watts	Color	Glass ③	Polycarbonate ④
Glass and Polycarbonate Globes ①						
<p>Glass Globe ③ (VPGL-1HR)</p> <p>Polycarbonate Globe ④ (VPGL-2PL)</p>	A-23	60-200	Clear	—	VPGL-2PL	
			Clear Heat-Resistant	VPGL-1HR	—	
			Amber	VPGL-1AM	VPGL-2AMPL	
			Blue	VPGL-1BL	VPGL-2BLPL	
			Green	VPGL-1GR	VPGL-2GRPL	
			Red	VPGL-1RE	VPGL-2REPL	
Glass Globes						
<p>Glass Globe (VPGL-2HR) ③</p>	PS-30	200-300	Clear	—	—	
			Clear Heat-Resistant	VPGL-2HR	—	
			Amber	VPGL-2AM	—	
			Blue	VPGL-2BL	—	
			Green	VPGL-2GR	—	
			Red	VPGL-2RE	—	
Coated Tuff-Skin® ② Glass Globes Contains globe safely even if glass is broken ④						
<p>VPGL-2HRT ④</p>	Heat-Resistant			VPGL-2HRT ④	—	
				Catalog Numbers		
		Type	Lamp Watts	NEC	CSA	
Guards						
<p>VPGU-1</p> <p>VPGU-2</p>	A-23	60-200	VPGU-1	VCFGU-1		
	PS-30	200-300	VPGU-2	VCFGU-2		
Replacement Porcelain Shock-Absorbing Sockets						
<p>Medium Base</p>	A-23	60-200	VPLR-123	VCLR-1		
	PS-30	200-300				
Replacement Gasket for Globes						
<p>Globe Gasket</p>	Neoprene – for all Stylmaster globes		VPGL-GK	VCGL-GK		

① Shatter-resistant for use in food processing plants, canneries, dairies, breweries, bakeries or anywhere broken glass would prove a hazard. Ideally suited for areas where vandalism, high replacement and high maintenance costs are a problem. CAUTION: Use maximum 200 W lamp less reflector, 100 W max. with reflector or colored globe. Do not use in ambients exceeding 25 °C/77 °F. For burning in vertical base-up position only.

② Registered trademark of Thomas Manufacturing Corporation, Parkton, Md.

③ Only listed for UL/NEC Fixtures.

④ Not an UL Listed option.