

# Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.  
Hazardous Location.

NEC: Class I, Division 2, Groups A, B, C, D  
CEC: Class I, Division 2, Groups A, B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Enclosure 4X

## Applications

- Enclosed and gasketed lighting fixtures for use in storage areas, tunnels, subways, chemical plants and other areas where moisture, dirt or corrosive atmospheres are a problem.
- Suitable for use in wet locations.
- Standard fixtures designed for 60 to 300 Watt medium base incandescent lamps.
- Pendant, feed-thru, ceiling, stanchion and wall mounts available.

## Features

- Modern styling, with clean-line mounting hood and prismatic glass globe, plus optional guard.
- Prismatic globe, furnished as standard, eliminates glare and distributes light evenly.
- Globe seats firmly against composition gasket in mounting hood to keep out dirt and moisture. Full threads eliminate “cross threading.”
- Fixture is complete with gaskets and socket. Socket is shock-absorbing to prolong lamp life and can be easily removed for wiring without tools.
- Porcelain socket construction assures long trouble-free operation in high ambient installations.
- Guards have exclusive snap-on attachment feature for quick installation and fast servicing.
- Maximum input voltage 277 V (suitable for DC applications).

## Standard Materials

- Mounting hoods: copperfree (4/10 of 1% max.) aluminum
- Guards: pressure cast copperfree (4/10 of 1% max.) aluminum
- Socket: porcelain with brass screw shell
- Globes: prismatic glass

## Standard Finishes

- Mounting hoods and guards: epoxy powder coat
- Socket and globes: natural finish

## Options

- To order fixture with other than standard clear glass globe, add suffix letters to catalog number as indicated in table, and adjust difference in price.

Color	Glass Globe	Plastic Globe
Amber	-AM	-PAM
Blue	-BL	-PBL
Green	-GR	-PGR
Red	-RE	-PRE
Clear Heat-Resistant	-HR	—

## NEC/CEC Certifications and Compliances

- UL Standard: UL 1598, UL 844
- UL Listed: E10444
- CSA Standard: C22.2 No. 250, C22.2 No. 137
- CSA Certified: 025428




## Illustrated Features



### Mounting Hood

Pendant style shown has setscrew to prevent fixture stem from turning. Other styles include stanchion, ceiling and wall mounting.



### Shock-Absorbing Medium Base Socket

Spring absorbs vibration to prolong lamp life. Porcelain construction for trouble-free operation in high ambient installations.



### Globe

Attractive, tapered prismatic glass globes for glare elimination and uniform light distribution. Colors available – also vandal-resistant plastic globes. Globe seats firmly against gasket to exclude moisture, dirt and vapors.

## Guard

### Guard

Snap-on guards (and reflectors) – simply snap-in and twist. Spring action balls snap into detents of fixture body.



# Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.  
Hazardous Location.

NEC: Class I, Division 2, Groups A, B, C, D  
CEC: Class I, Division 2, Groups A, B, C, D | Class II, Division 1 and 2, Groups E, F, G | Class III | Enclosure 4X

---

## Weights

### Typical Mounting Hoods

Pendant	kg (lb)	Ceiling	kg (lb)	Wall	kg (lb)	Stanchion	kg (lb)
VPA75		VPX75		VPOBW10		VPAN-125	
VCA75	0.9 (1.98)	VCX75	0.9 (1.98)	VCOBW10	1.4 (3.09)	VCAN-125	1.4 (3.09)

### Globes and Guards

Type	Globe	kg (lb)	Guard	kg (lb)
60-200 W	VPGL-1	0.9 (1.98)	VPGU-1	0.5 (1.10)
200-300 W	VPGL-2	1.4 (3.09)	VPGU-2	0.5 (1.10)