


# REPLACEMENT ROLLERS

## Roller 3/4" Dia. x 20 Ga. with 1/4" Round Axle - Model B

B



Part Number	BF	Wt. (lbs.)	Capacity (lbs.)
B07	7"	.31	42
B08	8"	.35	42
B09	9"	.38	42
B10	10"	.42	42
B11	11"	.45	42
B12	12"	.49	42
B13	13"	.53	42
B14	14"	.56	42
B15	15"	.60	42
B16	16"	.64	42
B17	17"	.67	42
B18	18"	.71	42
B19	19"	.74	42
B20	20"	.78	42
B21	21"	.82	42
B22	22"	.85	42

### Construction:

**Tube:** 3/4" O.D. x 20 ga. plain steel

**Axle:** 1/4" diameter steel

**Bearing:** Light oil, press fit

**Axle Retention:** Spring retained

**Weight:** .06 + (.04 x BF)


**Shaft Length:** BF+1-1/2"

Shorter, longer, and in-between  
BF's available.

Replacement  
Rollers

## Roller 1-3/8" Dia. x 18 Ga. with 1/4" Round Axle - Model EG

EG



Part Number	BF	Wt. (lbs.)	Capacity (lbs.)
EG07	7"	.63	94
EG08	8"	.71	94
EG09	9"	.78	94
EG10	10"	.85	94
EG11	11"	.92	85
EG12	12"	.99	77
EG13	13"	1.06	71
EG14	14"	1.14	65
EG15	15"	1.21	60
EG16	16"	1.28	56
EG17	17"	1.35	53
EG18	18"	1.42	50
EG19	19"	1.50	47
EG20	20"	1.57	44
EG21	21"	1.64	42
EG22	22"	1.71	40

### Construction:

**Tube:** 1-3/8" O.D. x 18 ga. galvanized steel

**Axle:** 1/4" diameter steel

**Bearing:** Light oil, swaged

**Axle Retention:** Spring retained

**Weight:** .14 + (.07 x BF)

**Shaft Length:** BF+7/8"

Shorter, longer, and in-between  
BF's available.