


# AO CLOTH PSA DISCS



DISCS



### FEATURES

- Durable backing for heavy sanding and grinding
- Versatile grain for multiple applications

### APPLICATIONS

Blending, Surface Preparation

### METALS



### WORKPIECE GEOMETRY



● = *Arrive* / 48 HR. SHIPPING

DIAMETER	ITEM	GRIT	PK QTY
4"	30431T	100	50
4"	30432T	120	50
4"	30433T	150	50
4"	30434T	180	50
4"	30434Z1T	220	50
4"	30435T	240	50
4"	30436T	320	50
4"	30436Z2T	400	50
5"	30438	36	50
5"	30439	40	50
5"	30440	50	50
5"	30441T	60	50
5"	30442T	80	50
5"	30443T	100	50
5"	30444T	120	50
5"	30445T	150	50
5"	30446T	180	50
5"	30446TZ2	220	50
5"	30447T	240	50
5"	30448T	320	50
5"	30448TGR	400	50
6"	30450	36	50
6"	30451	40	50
6"	30452	50	50
6"	30453T	60	50
6"	30454T	80	50
6"	30455T	100	50
6"	30456T	120	50
6"	30457T	150	50
6"	30458T	180	50
6"	30458TZ1	220	50
6"	30459T	240	50
6"	30460T	320	50
6"	30460TGR	400	50
8"	30474	36	50

● = *Arrive* / 48 HR. SHIPPING

DIAMETER	ITEM	GRIT	PK QTY
8"	30475	40	50
8"	30476	50	50
8"	30477	60	50
8"	30478	80	50
8"	30479	100	50
8"	30480	120	50
8"	30481	150	50
8"	30482	180	50
8"	30482Z1	220	50
8"	30483	240	50
8"	30484	320	50
8"	30484Z1	400	50
10"	30498	36	25
10"	30499	40	25
10"	30500	50	25
10"	30501	60	25
10"	30502	80	25
10"	30503	100	25
10"	30504	120	25
10"	30505	150	25
10"	30506	180	25
10"	30506Z1	220	25
10"	30507	240	25
10"	30508	320	25
10"	30508GR	400	25
12"	30510	36	25
12"	30511	40	25
12"	30512	50	25
12"	30513	60	25
12"	30514	80	25
12"	30515	100	25
12"	30516	120	25
12"	30517	150	25
12"	30518	180	25
12"	30518Z2	220	25