


REPLACEMENT ROLLERS

EA

Roller 1-3/8" Dia. x 18 Ga. with 1/4" Round Axle - Model EA



Part Number	BF	Wt. (lbs.)	Capacity (lbs.)
EA07	7"	.39	94
EA08	8"	.43	94
EA09	9"	.46	94
EA10	10"	.49	94
EA11	11"	.53	85
EA12	12"	.56	77
EA13	13"	.60	71
EA14	14"	.63	65
EA15	15"	.66	60
EA16	16"	.70	56
EA17	17"	.73	53
EA18	18"	.77	50
EA19	19"	.80	47
EA20	20"	.83	44
EA21	21"	.87	42
EA22	22"	.90	40

Construction:

Tube: 1-3/8" O.D. x 18 ga. **aluminum**

Axle: 1/4" diameter steel

Bearing: Light oil, swaged

Axle Retention: Spring retained

Weight: .16 + (.04 x BF)


Shaft Length: BF+7/8"

Shorter, longer, and in-between

BF's available.

EFG

Roller 1-3/8" Dia. x 18 Ga. with 5/16" Hex Axle - Model EFG



Part Number	BF	Wt. (lbs.)	Capacity (lbs.)
EFG07	7"	.83	94
EFG08	8"	.91	94
EFG09	9"	.99	94
EFG10	10"	1.08	94
EFG11	11"	1.16	94
EFG12	12"	1.24	94
EFG13	13"	1.32	94
EFG14	14"	1.40	94
EFG15	15"	1.49	94
EFG16	16"	1.57	94
EFG17	17"	1.65	94
EFG18	18"	1.73	94
EFG19	19"	1.81	94
EFG20	20"	1.89	94
EFG21	21"	1.98	94
EFG22	22"	2.06	94

Construction:

Tube: 1-3/8" O.D. x 18 ga. **galvanized steel**

Axle: 5/16" hex steel

Bearing: Light oil, swaged

Axle Retention: Spring retained

Weight: .25 + (.08 x BF)

Shaft Length: BF+1-1/16"

Shorter, longer, and in-between

BF's available.