

# ASSOCIATED® WHEELED BATTERY CHARGERS

Associated Wheel Chargers are “Safe in Any Weather” with clamp bars for extra safety. Associated chargers are made with powder-coated steel enclosures, chrome tubular handles, 100% copper cable with flexible insulation (cold weather application), steel foot, and copper jaws on insulated steel clamps.

## FEATURES:

- Fan cooling mechanism prevents overheating and extends product life
- Heavy duty vacuum impregnated transformer to seal the unit against external agents
- Patented multi-diode rectifiers
- 400, 500 or 800 Amp fully insulated clamps (“flexi-spring” for select models)
- Patented “Stop/Go” light on some models
- Automatic reset AC and DC circuit breakers
- Automatic electric timer
- “Safe in any Weather” Wheeled Chargers
- Two-Year “bumper-to-bumper” Manufacturer’s Warranty and Five-Year Limited for Transformer/Rectifier
- DOE Compliant and Energy Efficient
- Made in USA of US and Global Components



### Model 6001A

#### 6/12 Volt Heavy Duty Fleet Charger

- 100 Amps/75 Amps Charger
- 375 Amp Crank Assist at 12V
- Provides 16 rates of charge
- Protective gauge cover
- Patented “Stop/Go” light for Polarity Indication
- Rugged 7” tires



### Model 6002B

#### 6/12/18/24 Volt Heavy Duty Fleet Charger

- 100/80/50/40 Amps Charger
- 400 Amp Crank Assist at 12V
- Protective gauge cover
- Patented “Stop/Go” light for Polarity Indication
- Rugged 7” tires