

pro^{sense}® SPTD25 Series Pressure Transmitters



Part No. SPTD25-20-0100H



The ProSense SPTD25 pressure transmitter series is engineered to meet many industrial, commercial, and OEM pressure measurement applications. The all-stainless steel thin film sensing element provides very fast response time and can be used to sense any compatible media. With a robust design resistant to vibration, shock, and EMI/RFI, the SPTD25 series provides high accuracy over a wide compensated temperature range. Pressure sensing ranges from 100 to 5000 psig are available with a 1/4 inch NPT male threaded process connection and a linear 4-20 mA output with an M12 quick-disconnect electrical connection.

Applications

- Process control & automation
- Pump & compressor control
- Hydraulic systems
- Pneumatic systems
- Engine monitoring
- Presses
- Machine tools

Features

- All-stainless steel sensing element
- Fast response time
- Pressure ranges from 100 to 5000 psig
- 1/4 inch NPT male threaded process connection
- 4-20 mA output
- M12 quick-disconnect electrical connection
- UL508 listed, CE marked
- 3-year warranty



Note: Check the chemical compatibility of the sensor's wetted parts with the medium to be measured.

ProSense SPTD25 Series Pressure Transmitters

Part Number	Description	Pcs/Pkg	Wt (lb)	Price
<u>SPTD25-20-0100H</u>	Pressure transmitter, 4 to 20 mA output, 0 to 100 psig range, 1/4" NPT male port, M12 connector	1	0.1	\$119.00
<u>SPTD25-20-0200H</u>	Pressure transmitter, 4 to 20 mA output, 0 to 200 psig range, 1/4" NPT male port, M12 connector	1	0.1	\$119.00
<u>SPTD25-20-0300H</u>	Pressure transmitter, 4 to 20 mA output, 0 to 300 psig range, 1/4" NPT male port, M12 connector	1	0.1	\$119.00
<u>SPTD25-20-0500H</u>	Pressure transmitter, 4 to 20 mA output, 0 to 500 psig range, 1/4" NPT male port, M12 connector	1	0.1	\$119.00
<u>SPTD25-20-1000H</u>	Pressure transmitter, 4 to 20 mA output, 0 to 1000 psig range, 1/4" NPT male port, M12 connector	1	0.1	\$119.00
<u>SPTD25-20-3000H</u>	Pressure transmitter, 4 to 20 mA output, 0 to 3000 psig range, 1/4" NPT male port, M12 connector	1	0.1	\$119.00
<u>SPTD25-20-5000H</u>	Pressure transmitter, 4 to 20 mA output, 0 to 5000 psig range, 1/4" NPT male port, M12 connector	1	0.1	\$119.00

ProSense SPTD25 Series General Specifications

Housing Material	Stainless steel 316L (DIN 1.4404); Stainless steel 17-4PH (DIN 1.4542); Polyamide (PA)
Materials (wetted parts)*	Stainless steel 17-4PH (DIN 1.4542)
Operating Temperature	-40 to 194°F (-40 to 90°C)
Medium Temperature	-40 to 194°F (-40 to 90°C)
Storage Temperature	-40 to 212°F (-40 to 100°C)
Protection	IP 67 / IP 69K
Accuracy¹	< ± 0.5% of full range
Linearity²	< ± 0.1% (BFSL) / < ± 0.2% (LS)
Hysteresis	< ± 0.2%
Repeatability³	< ± 0.05%
Long-Term Stability⁴	< ± 0.1%
* Not cleaned for oxygen service ¹ Zero point and span error, non-linearity, hysteresis ² BFSL = Best fit straight line / LS = limit value setting ³ With temperature fluctuations <10°C ⁴ In % of the span / 6 months	

prosense® SPTD25 Series Pressure Transmitters

ProSense SPTD25 Series General Specifications Continued


Operating Voltage	8.5 to 36 VDC*
Analog Output	4 to 20 mA
Maximum Load	$[(\text{supply voltage} - 8.5) / 21.5 \text{ mA}] \Omega$ For example: $[(24\text{VDC} - 8.5) / 0.0215] = 720 \Omega$
IEC Protection Class	Class III $\diamond$
Step Response Time Analog Output	1 ms
Short-Circuit Proof	yes
Overload Protection	yes
Reverse Polarity Protection	yes
Insulation Resistance	> 100 M Ω : (500 VDC)
Shock Resistance	50g (DIN 60068-2-27, 11ms)
Vibration Resistance	20g (DIN 60068-2-6, 10 - 2000 Hz)
EN 61000-4-2 ESD	4 kV / 8 kV AD
EN 61000-4-3 HF Radiated	30 V/m
EN 61000-4-4 Burst	2kV
EN 61000-4-6 HF Conducted	10V
EC Pressure Equipment Directive 97/23/EC	Article 3, section 3: Group 2 Non-Hazardous, Non-flammable, Non-oxidizing
EMC	DIN EN 61000-6-2; DIN EN 61000-6-3
MTTF (Years)	784
Min. Pressure Cycles	60 million lifetime (at 1.2 times the nominal pressure)
Agency Approvals	cULus (E320431), CE, RoHS
* per EN50178, SELV, PELV	



Warning! Avoid static and dynamic overpressure exceeding the given overload pressure.
Exceeding the bursting pressure for even a short time can cause destruction of the unit and possible injuries!

Dimensions

mm [inches]



See our website www.AutomationDirect.com for complete Engineering drawings.

prosense® SPTD25 Series Pressure Transmitters

Pressure Ratings


Applications (Type of Pressure: Gauge Pressure, Liquids and Gases)			
Part Number	Final Value of the Measuring Range	Static Proof Pressure Resistance (Max. Permissible Pressure)	Bursting Pressure
	Psig	Psig	Psig
<u>SPTD25-20-0100H</u>	100	250	2900
<u>SPTD25-20-0200H</u>	200	580	6525
<u>SPTD25-20-0300H</u>	300	940	8700
<u>SPTD25-20-0500H</u>	500	1450	11600
<u>SPTD25-20-1000H</u>	1000	2500	13050
<u>SPTD25-20-3000H</u>	3000	7250	14500
<u>SPTD25-20-5000H</u>	5000	14500	24650

All SPTD25 series transmitters can withstand vacuum down to -14.5 psig



Warning! Avoid static and dynamic overpressure exceeding the given overload pressure. Exceeding the bursting pressure for even a short time can cause destruction of the unit and possible injuries!

Current Output 4-20 mA




In the measuring range the output signal is between 4 and 20mA. If the system pressure is above or below the measuring range, the analog output performs as follows:

- System pressure above the measuring range: 20...25mA non-linear
- System pressure below the measuring range: 4...3mA non-linear

SPTD25-20 Wiring Diagrams



Cable Assembly Wiring Colors:
Pin 1 - Brown +
Pin 2 - White - Out
Pin 3 - Blue, not used
Pin 4 - Black, not used



See Proximity Sensor section for cable specs

Note: Wiring colors are based on AutomationDirect CD12L and CD12M 4-pole cable assemblies.