



Customer information packet

BSM63N-175AA

BSM63N-175AA (NEO) T'STAT, RESOLVE

Specifications

Enclosure	TENV
Nameplate Speed	4000
Agency Approvals	CE
	CSA
	TUV
	UR
Base Indicator	No Mounting
Dimensional Drawing Numbers	S1LYP100
Frame Material	Exposed Laminations
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Standards	Other
Mounting Arrangement	F1
Nameplate Output	0.24KW
Shaft Rotation	Reversible

Part detail


Revision	AD
Type	AC
Mech. spec.	S1P100
Base	
Status	PRD/A
Elec. spec.	S1WGW033
Layout	S1LYP100
Eff. date	12-02-2024
CD Diagram	CD0006A02
Poles	04
Leads	3#18
Proprietary	False
Created date	01-01-0001

Nameplate

NP2859L										
CAT.										
SPEC		S1P100W033G1								
MFG										
TORQ CONT STALL		0.7 NM								
CUR CONT STALL/A RMS		1.02								
POWER		0.24KW								
RATED SPEED/RPM(1/MIN)		4000								
RATED BUS VOLTS		320								
PEAK CUR/A RMS		4.08								
MAX SPEED/RPM(1/MIN)		10000					WT.		2.7	
CLASS		F	IP	54	IC	410	25C RATED			


Accessories

Part number	Description	Multiplier
GBSM63-MRP070-5	Std. Servo Gearbox Ratio 5:1	E4
GBSM63-MRP070-10	Std. Servo Gearbox Ratio 10:1	E4
GBSM63-MRP090-25	Std. Servo Gearbox Ratio 25:1	E4
GBSM63-MRP090-50	Std. Servo Gearbox Ratio 50:1	E4




CD1321

8 PIN THREADED CONNECTOR
(CRIMP STYLE)
(INSERTION SIDE)



12 PIN THREADED CONNECTOR
(CRIMP STYLE)
(INSERTION SIDE)



MOTOR CONNECTIONS

PIN	FUNCTION	INTERNAL/EXTERNAL MARKINGS
A	THERMAL SWITCH	YELLOW
B	THERMAL SWITCH	YELLOW
C	BRAKE (OPTIONAL)	BLACK (* RED)
D	BRAKE (OPTIONAL)	BLACK
1	U	BLACK OR T1
2	GROUND	GREEN OR **GREEN/YELLOW
3	W	BLUE OR T3
4	V	RED OR T2

* WHEN REQUIRED

**CE MOTORS REQUIRE GREEN/YELLOW GROUND

RESOLVER CONNECTIONS

PIN	FUNCTION	INTERNAL WIRE COLOR
1	REF HI R1	RED/WHITE
2	REF LO R2	YELLOW/WHITE
3	COS+ S1	RED
4	COS- S3	BLACK
5	SINE- S4	BLUE
6	SINE+ S2	YELLOW

REV. DESC: ADD CE NOTE AND GREEN/YELLOW GROUND

REV. LTR: F

VERSION: 03

TDR: 000001192301

FILE: \AAA\00055\309

REVISED: 02: 34: 44 06/13/2022

BY: ENDANDO

MTL: -




BALDOR - RELIANCE®

BSM WIRING DIAG, POWER & RESOLVER, 8 & 12 PIN THD CONNECT.

SH 1 of 1

CD1321

CD0006A02



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.

REV. DESC: REMOVED "OPTIONAL" FROM PRINT, SERVO REQ'S T'STATS		
REV. LTR: D	VERSION: 03	TDR: 000000414937
CD0006A02	FILE: \AAA\00068\606	REVISED: 10:02:28 11/21/2006
	MTL: -	BY: ENJEFO

BALDOR ELECTRIC Co.

3PH, SV, 3 LEADS, WYE CONNECTED

CD0006A02