



Customer information packet

CDP3590

2HP, 2500RPM, DC, 145TC, 3536P, TEFC, F1

Class - None

Division -

Specifications

Armature Voltage	180 V
Base Speed	2400 rpm
Enclosure	TEFC
Frame	145TC
Frame Material	Steel
Haz Area Class and Group	None
Output Power	2.000 HP
Agency Approvals	CE CSA UR
Ambient Temperature	40 °C
Armature Current	10.0 a
Armature Inertia	30.342 lb-ft ²
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
Lifting Lugs	No Lifting Lugs
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 14 AWG, A
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	16.37 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End

Part detail

Revision	AE
Type	DC
Mech. spec.	35P432
Base	
Status	PRD/A
Elec. spec.	35WGZ182
Layout	35LYP432
Eff. date	10-28-2024
CD Diagram	CD0194
Poles	00
Leads	2#14 A Y
Proprietary	False
Created date	01-01-0001

Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Nameplate

NP0891L					
CAT.NO.	CDP3590				
SPEC.	35P432Z182				
HP	2/KW1.5	ENCL		TEFC	
RPM	2500 1/MIN				
FRAME	145TC	TYPE		3536P	
ARM V	180	ARM A		10	
FLD V		FLD A			
INSUL	F	AMB.		40	
DUTY	CONT	SUPPLY		K	
BRG/DE	6205	BRG/ODE		6205	
BRUSHES	2/BP5000T15				
		BLANK		IP44	
SER.					
BLANK	IC411 KG29				
APRV-CE	Y	APRV-CSA	Y	APRV-UL	Y

Accessories

Part number	Description	Multiplier
TK3500	TACHO MOUTING KIT TK3500	A8

DC Motor Performance Data

Record # 387

Typical performance - not guaranteed values

Winding: 35WGZ182-R001		Type: 3536P	Enclosure: TEFC
Nameplate Data		General Characteristics	
Rated Output (HP)	2	Armature Resistance @ 25°C	0.494 Ω
R.P.M.	2400		
Armature Volts	180	Voltage Constant	68.3 v/krpm
Armature Amps	10		
Field Volts		Armature Inductance	6.797 mH
Field Amps		Armature Inertia	30.3419 LI^2
Rating - Duty	40C AMB-CONT		
Power Supply Code	K		

Load Characteristics at 180 Armature Volts

Load Point	1	2	3	4	5	6	7
Armature Amps	0.7	5.5	8	10.2	12.5	14.7	19.6
R.P.M.	2514	2499	2483	2448	2416	2387	2335
Torque (LB-FT)	0	2.25	3.375	4.375	5.5	6.625	8.75

ABB Motors and Mechanical Inc.

WINDING # 35WGZ182

Typical performance - not guaranteed values.

2 HP DC 2400 RPM 180 V 3536P

ENCL: TEFC DUTY: CONT CL: F





