

**BALDOR • RELIANCE**

---

# Customer information packet

## CDPT3330

.5HP, 1750RPM, DC, 56C, 3336P, TENV, F1, N

## Specifications

Armature Voltage	90 V
Base Speed	1750 rpm
Enclosure	TENV
Frame	56C
Frame Material	Steel
Output Power	0.500 HP
Agency Approvals	CE CSA UR WEEE
Ambient Temperature	40 °C
Armature Current	4.8 a
Armature Inertia	14.047 lb-ft <sup>2</sup>
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Drip Cover	No Drip Cover
Duty Rating	CONT
Feedback Device	TACHOMETER
Heater Indicator	No Heater
Insulation Class	F
Lifting Lugs	No Lifting Lugs
Motor Lead Quantity/Wire Size	2 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Mounting Arrangement	F1
Overall Length	16.74 IN
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding

## Part detail

Revision	K
Type	DC
Mech. spec.	33-2657
Base	
Status	PRD/A
Elec. spec.	33WGZ122
Layout	33LY2657
Eff. date	10-24-2024
CD Diagram	CD0194
Poles	00
Leads	
Proprietary	False
Created date	06-19-2019

**Shaft Rotation**

**Reversible**

**Shaft Slinger Indicator**

**No Slinger**

---

**Nameplate**

<b>NP0891L</b>					
<b>CAT.NO.</b>	CDPT3330				
<b>SPEC.</b>	33-2657Z122				
<b>HP</b>	.5/KW.37	<b>ENCL</b>	TENV		
<b>RPM</b>	1750 1/MIN				
<b>FRAME</b>	56C	<b>TYPE</b>	3336P		
<b>ARM V</b>	90	<b>ARM A</b>	4.8		
<b>FLD V</b>		<b>FLD A</b>			
<b>INSUL</b>	F	<b>AMB.</b>	40		
<b>DUTY</b>	CONT	<b>SUPPLY</b>	1.3		
<b>BRG/DE</b>	6203	<b>BRG/ODE</b>	6203		
<b>BRUSHES</b>	2/BP5011T01				
	IP44	<b>BLANK</b>	KG15		
<b>SER.</b>					
<b>BLANK</b>	IC410				
<b>APRV-CE</b>	Y	<b>APRV-CSA</b>	Y	<b>APRV-UL</b>	Y

**DC Motor Performance Data**

Record # 2408

Typical performance - not guaranteed values

<b>Winding: 33WGZ122-R001</b>		<b>Type: 3336P</b>		<b>Enclosure: TENV</b>	
<b>Nameplate Data</b>			<b>General Characteristics</b>		
<b>Rated Output (HP)</b>	0.5	<b>Armature Resistance @ 25°C</b>	1.163 Ω		
<b>R.P.M.</b>	1750	<b>Voltage Constant</b>	47.81 v/krpm		
<b>Armature Volts</b>	90	<b>Armature Inductance</b>	14.506 mH		
<b>Armature Amps</b>	4.8	<b>Armature Inertia</b>	14.05 LI <sup>2</sup>		
<b>Field Volts</b>					
<b>Field Amps</b>					
<b>Rating - Duty</b>	40C AMB-CONT				
<b>Form Factor</b>	1.3				

**Load Characteristics at 90 Armature Volts**

<b>Load Point</b>	<b>1</b>	<b>2</b>	<b>3</b>	<b>4</b>	<b>5</b>	<b>6</b>	<b>7</b>
<b>Armature Amps</b>	0.26	1.45	2.56	3.62	4.65	5.79	7
<b>R.P.M.</b>	1853	1777	1721	1658	1629	1579	1519
<b>Torque ( LB-FT )</b>	0	0.38	0.76	1.14	1.5	1.9	2.28


ABB Motors and Mechanical Inc.

WINDING # 33WGZ122


0.5 HP DC 1750 RPM 90 V 3336P

Typical performance - not guaranteed values.



ENCL: TENV DUTY: CONT CL: F



6/9/2025, DCPERF, VER 2.0.06, record 2408



CD0194



NOTES:

1. CCW ROTATION AS SHOWN FACING COMMUTATOR END. TO REVERSE MOTOR ROTATION OR TACHOMETER OUTPUT POLARITY INTERCHANGE LEADS A1(RED) & A2(BLACK)
2. LEAD COLORS FOR REFERENCE ONLY & NOT SPECIFIED BY THIS DRAWING. LEAD COLORS SPECIFIED BY LAYOUT DRAWING & BILL OF MATERIAL ONLY.

MATL: -			
REV: E	ADDED NOTE "LEAD COLORS FOR REFERENCE ONLY &..."		
CD0194	SCALE: -	BY: CK	REVISED: 07/28/95
	FILE: AAA00004503	TDR: 0078737	

**BALDOR ELECTRIC Co.**

CD TYPE P DC PERMANENT MAGNET MOTORS AND TACHOMETERS

CD0194