



Customer information packet

CEDM3615T

5HP, 1750RPM, 3PH, 60HZ, 184TC, 3642M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

| | |
|--------------------------------|---|
| Enclosure | TEFC |
| Frame | 184TC |
| Frame Material | Steel |
| Frequency | 60.00 Hz |
| Haz Area Class and Group | None |
| Haz Area Division | Not Applicable |
| Motor Letter Type | Three Phase |
| Output @ Frequency | 5.000 HP @ 60 HZ |
| Phase | 3 |
| Synchronous Speed @ Frequency | 1800 RPM @ 60 HZ |
| Voltage @ Frequency | 460.0 V @ 60 HZ 230.0 V @ 60 HZ |
| Agency Approvals | CCSA US CSA EEV NEMA PREMIUM NEMA_PREMIUM UR |
| Ambient Temperature | 40 °C |
| Auxillary Box | No Auxillary Box |
| Auxillary Box Lead Termination | None |
| Base Indicator | Rigid |
| Bearing Grease Type | Polyrex EM (-20F +300F) |
| Blower | None |
| Constant Torque Speed Range | 6 |
| Current @ Voltage | 6.700 A @ 460.0 V 13.900 A @ 208.0 V 13.400 A @ 230.0 V |
| Design Code | B |
| Drip Cover | No Drip Cover |
| Duty Rating | CONT |
| Efficiency @ 100% Load | 89.5 % |
| Electrically Isolated Bearing | Not Electrically Isolated |

Part detail

| | |
|--------------|------------|
| Revision | F |
| Type | AC |
| Mech. spec. | 36Q736 |
| Base | |
| Status | PRD/A |
| Elec. spec. | 36WGS268 |
| Layout | 36LYQ736 |
| Eff. date | 06-24-2021 |
| CD Diagram | CD0005 |
| Poles | 04 |
| Leads | 9#16 |
| Proprietary | False |
| Created date | 04-22-2016 |

| | |
|-------------------------------|-----------------------|
| Feedback Device | NO FEEDBACK |
| Front Face Code | Standard |
| Front Shaft Indicator | None |
| Heater Indicator | No Heater |
| High Voltage Full Load Amps | 6.7 a |
| Insulation Class | F |
| Inverter Code | Inverter Duty |
| KVA Code | J |
| Lifting Lugs | Standard Lifting Lugs |
| Locked Bearing Indicator | Locked Bearing |
| Max Speed | 2700 rpm |
| Motor Lead Exit | Ko Box |
| Motor Lead Quantity/Wire Size | 9 @ 16 AWG |
| Motor Lead Termination | Flying Leads |
| Motor Standards | NEMA |
| Motor Type | 3642M |
| Mounting Arrangement | F1 |
| Number of Poles | 4 |
| Overall Length | 18.10 IN |
| Power Factor | 78 |
| Product Family | Dirty Duty Plus |
| Pulley End Bearing Type | Ball |
| Pulley Face Code | C-Face |
| Pulley Shaft Indicator | Standard |
| Rodent Screen | None |
| Service Factor | 1.15 |
| Shaft Diameter | 1.125 IN |
| Shaft Extension Location | Pulley End |
| Shaft Ground Indicator | No Shaft Grounding |
| Shaft Rotation | Reversible |
| Shaft Slinger Indicator | No Slinger |
| Speed | 1750 rpm |
| Speed Code | Single Speed |
| Starting Method | Direct on line |

| | |
|-----------------------------------|---------------------|
| Thermal Device - Bearing | None |
| Thermal Device - Winding | None |
| Vibration Sensor Indicator | No Vibration Sensor |
| Winding Thermal 1 | None |
| Winding Thermal 2 | None |

Nameplate

NP3504

| | | | | | |
|---------------------|---------------|-----------------|------|-------------------|------|
| CAT NO | CEDM3615T | | | | |
| SPEC. | 36Q736S268G1 | ENCL | TEFC | | |
| FRAME | 184TC | HP | 5 | | |
| VOLTS | 230/460 | | | | |
| FLA | 13.4/6.7 | I.P. | 56 | | |
| RPM | 1750 | RPM MAX | 2700 | | |
| HZ | 60 | PH | 3 | CLASS | F |
| SER.F. | 1.15 | DES | B | CC | 010A |
| NEMA-NOM-EFF | 89.5 | | | | |
| RATING | 40C AMB-CONT | | | | |
| DE BRG | 6206 | ODE BRG | 6205 | | |
| GREASE | POLYREX EM | | | | |
| C HP FR | 60 | C HP TO | 90 | | |
| CT HZ FROM | 6 | CT HZ TO | 60 | VT HZ FROM | 6 |
| VT HZ TO | 60 | | | | |
| SER.NO | 50C AT 1.0 SF | | | | |

AC Induction Motor Performance Data

Record # 55772

Typical performance - not guaranteed values

| Winding: 36WGS268-R085 | | Type: 3642M | | Enclosure: TEFC | |
|-------------------------------|--------------------------|----------------------------|--|--------------------------|--|
| Nameplate Data | | | 460 V, 60 Hz: High Voltage Connection | | |
| Rated Output (HP) | 5 | Full Load Torque | 14.9 LB-FT | | |
| Volts | 230/460 | Start Configuration | direct on line | | |
| Full Load Amps | 13.4/6.7 | Breakdown Torque | 52.2 LB-FT | | |
| R.P.M. | 1750 | Pull-up Torque | 31.5 LB-FT | | |
| Hz | 60 Phase | 3 | Locked-rotor Torque | 34.9 LB-FT | |
| NEMA Design Code | B KVA Code | J | Starting Current | 49.1 A | |
| Service Factor (S.F.) | | 1.15 | No-load Current | 3.24 A | |
| NEMA Nom. Eff. | 89.5 Power Factor | 78 | Line-line Res. @ 25°C | 2.31 Ω | |
| Rating - Duty | | 40C AMB-CONT | Temp. Rise @ Rated Load | 71°C | |
| S.F. Amps | | | Temp. Rise @ S.F. Load | 87°C | |
| | | | Locked-rotor Power Factor | 39.8 | |
| | | | Rotor inertia | 0.391 LB-FT ² | |

Load Characteristics 460 V, 60 Hz, 5 HP

| % of Rated Load | 25 | 50 | 75 | 100 | 125 | 150 | S.F. |
|------------------------|-----------|-----------|-----------|------------|------------|------------|-------------|
| Power Factor | 39 | 60 | 72 | 78 | 83 | 83 | 81 |
| Efficiency | 84.9 | 89.7 | 90.3 | 89.8 | 88.8 | 87 | 89.2 |
| Speed | 1789.1 | 1776.2 | 1762.3 | 1749.7 | 1732.5 | 1714.3 | 1739 |
| Line amperes | 3.55 | 4.31 | 5.43 | 6.65 | 7.94 | 9.64 | 7.42 |


ABB Motors and Mechanical Inc.

WINDING # 36WGS268

5 HP 3 PH 60 HZ 1750 RPM 460 V 3642M


Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=52.2 PU=31.5 LR=34.9 LRA=49.1




6/9/2025 ACPERF, record # 55772

CD0005




LOW VOLTAGE (2Y)



LINE

HIGH VOLTAGE (1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

| | | | |
|---|---------|-------------------------|--------------|
| REV. DESC: REVISE TO SHOW OPTIONAL COLORS | | | |
| REV. LTR: E | BY: JLP | REVISED: 01/19/99 10:15 | TDR: 0171435 |
| S00000 | | FILE: AAA00005140 | MDL: - |
| | | MTL: - | |

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS