



Customer information packet

CEM2543T

50HP, 1775RPM, 3PH, 60HZ, 326TC, 4256M, OPSB, F

Specifications

Enclosure	OPSB
Frame	326TC
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	57.000 A @ 460.0 V 121.000 A @ 208.0 V 114.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part detail

Revision	W
Type	AC
Mech. spec.	42D102
Base	
Status	PRD/A
Elec. spec.	42WGW387
Layout	42LYD102
Eff. date	06-27-2024
CD Diagram	CD0180
Poles	04
Leads	9#8
Proprietary	False
Created date	08-03-2010

High Voltage Full Load Amps	57.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4256M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.69 IN
Power Factor	87
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP3554LUA											
CAT.NO.	CEM2543T			P/N						ENCL	OPSE
SPEC.	42D102W387G1	CC	010A	FRAME	326TC	SER.NO.					
HP	50		CLASS	F	HZ	60					
RPM	1775		PH	3	DES	A					
VOLTS	230/460			CODE	G	ODE BRG	6311	DE BRG	6312		
AMPS	114/57										
RATING	40C AMB-CONT		NEMA-NOM-EFF			94.5	GREASE	POLYREX EM			
PF	87	SER.F.	1.15	CT30-60(2:1) VT3-60(20:1)							
USABLE AT	50HZ 50HP 190/380V 136/68A			SF 1.0 <td colspan="3"></td>							
HTR-VOLTS	HTR-AMPS	MAX. SPACE HEATER TEMP.									

AC Induction Motor Performance Data

Record # 53755

Typical performance - not guaranteed values

Winding: 42WGW387-R001			Type: 4256M		Enclosure: OPSB	
Nameplate Data				460 V, 60 Hz: High Voltage Connection		
Rated Output (HP)		50		Full Load Torque		149 LB-FT
Volts		230/460		Start Configuration		direct on line
Full Load Amps		114/57		Breakdown Torque		420 LB-FT
R.P.M.		1775		Pull-up Torque		217 LB-FT
Hz		60 Phase		Locked-rotor Torque		311 LB-FT
NEMA Design Code		A KVA Code		Starting Current		373 A
Service Factor (S.F.)		1.15		No-load Current		20.2 A
NEMA Nom. Eff.		94.5 Power Factor		Line-line Res. @ 25°C		0.12266 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		39°C
S.F. Amps				Temp. Rise @ S.F. Load		47°C

Load Characteristics 460 V, 60 Hz, 50 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	54	75	83	87	88	88	88
Efficiency	92	94.5	94.9	94.7	94.2	93.4	94.4
Speed	1791	1786.1	1781.1	1775.2	1769.2	1762.1	1772
Line amperes	24.4	33.4	44.7	57.4	71	85.6	65.6


ABB Motors and Mechanical Inc.


WINDING # 42WGW387

Typical performance - not guaranteed values.


50 HP 3 PH 60 HZ 1775 RPM 460 V 4256M

TORQUES (LB-FT): PO=420 PU=217 LR=311 LRA=373





CD0180

LOW VOLTAGE
(2D)HIGH VOLTAGE
(1D)

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: —

**BALDOR - RELIANCE®**

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1