



Customer information packet

CEM3312T

10HP, 3500RPM, 3PH, 60HZ, 213TC, 3728M, OPSB, F

Class - None

Division - Not Applicable

Specifications

Enclosure	OPSB
Frame	213TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	26.000 A @ 208.0 V 24.000 A @ 230.0 V 12.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	90.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part detail

Revision	E
Type	AC
Mech. spec.	37B102
Base	
Status	PRD/A
Elec. spec.	37WGL866
Layout	37LYB102
Eff. date	06-11-2024
CD Diagram	CD0005
Poles	02
Leads	9#14
Proprietary	False
Created date	02-02-2021

Heater Indicator	No Heater
High Voltage Full Load Amps	12.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3728M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	17.07 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA

CAT.NO.	CEM3312T									
SPEC.	37B102L866G1									
HP	10									
VOLTS	230/460									
AMPS	24/12									
RPM	3500									
FRAME	213TC		HZ	60			PH	3		
SF	1.15	CODE	H	DES	B	CLASS	F			
NEMA NOM. EFF	90.2	PF	85							
RATING	40C AMB-CONT									
CC	010A									
ENCL	OPSB	SN								
DE	6307		ODE	6206						
VPWM INVERTER READY										
CT30-60(2:1) VT3-60(20:1)										
USABLE AT	50HZ 10HP 190/380V 28.4/14.2A							SF1.0		

AC Induction Motor Performance Data

Record # 86644

Preliminary Data Sheet

Winding: 37WGL866-R002			Type: 3728M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		10	Full Load Torque		15 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		24/12	Breakdown Torque		50.8 LB-FT		
R.P.M.		3475	Pull-up Torque		23.7 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		29 LB-FT	
NEMA Design Code		B	KVA Code	H	Starting Current		81.5 A
Service Factor (S.F.)		1.15	No-load Current		4.72 A		
NEMA Nom. Eff.		89.5	Power Factor	86	Line-line Res. @ 25°C		0.991 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		33°C
S.F. Amps		27.6/13.8	Temp. Rise @ S.F. Load		41°C		
			Locked-rotor Power Factor		39.9		
			Rotor inertia		0.255 lb-ft²		

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	49	71	81	85	87	88	87
Efficiency	85	90	90.8	90.3	89.2	87.8	89.6
Speed	3576	3552	3527	3499	3469	3436	3479
Line amperes	5.5	7.27	9.53	12.1	15	18.2	13.8

ABB Motors and Mechanical Inc.

WINDING # 37WGL866

Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 3475 RPM 460 V 3728M

TORQUES (LB-FT): PO=50.8 PU=23.7 LR=29 LRA=81.5





