



---

# Customer information packet

## CEM3770T-5

7.5HP, 1770RPM, 3PH, 60HZ, 213TC, 0738M, TEFC

Class - None

Division - Not Applicable

## Specifications

|                                |                                                           |
|--------------------------------|-----------------------------------------------------------|
| Enclosure                      | TEFC                                                      |
| Frame                          | 213TC                                                     |
| Frame Material                 | Iron                                                      |
| Frequency                      | 60.00 Hz                                                  |
| Haz Area Class and Group       | None                                                      |
| Haz Area Division              | Not Applicable                                            |
| Motor Letter Type              | Three Phase                                               |
| Output @ Frequency             | 7.500 HP @ 60 HZ                                          |
| Phase                          | 3                                                         |
| Synchronous Speed @ Frequency  | 1800 RPM @ 60 HZ                                          |
| Voltage @ Frequency            | 575.0 V @ 60 HZ                                           |
| Agency Approvals               | CSA EEV<br>CURUSEEV<br>NEMA PREMIUM<br>NEMA_PREMIUM<br>UR |
| Ambient Temperature            | 40 °C                                                     |
| Auxillary Box                  | No Auxillary Box                                          |
| Auxillary Box Lead Termination | None                                                      |
| Base Indicator                 | Rigid                                                     |
| Bearing Grease Type            | Polyrex EM (-20F +300F)                                   |
| Blower                         | None                                                      |
| Current @ Voltage              | 7.500 A @ 575.0 V                                         |
| Design Code                    | A                                                         |
| Drip Cover                     | No Drip Cover                                             |
| Duty Rating                    | CONT                                                      |
| Efficiency @ 100% Load         | 91.7 %                                                    |
| Electrically Isolated Bearing  | Not Electrically Isolated                                 |
| Feedback Device                | NO FEEDBACK                                               |
| Front Face Code                | Standard                                                  |
| Front Shaft Indicator          | None                                                      |
| Heater Indicator               | No Heater                                                 |

## Part detail

|              |            |
|--------------|------------|
| Revision     | V          |
| Type         | AC         |
| Mech. spec.  | 07H058     |
| Base         |            |
| Status       | PRD/A      |
| Elec. spec.  | 07WGX817   |
| Layout       | 07LYH058   |
| Eff. date    | 10-17-2024 |
| CD Diagram   | CD0006     |
| Poles        | 04         |
| Leads        | 3#14       |
| Proprietary  | False      |
| Created date | 03-20-2009 |

|                               |                       |
|-------------------------------|-----------------------|
| High Voltage Full Load Amps   | 7.5 a                 |
| Insulation Class              | F                     |
| Inverter Code                 | Inverter Ready        |
| KVA Code                      | J                     |
| Lifting Lugs                  | Standard Lifting Lugs |
| Locked Bearing Indicator      | Locked Bearing        |
| Motor Lead Exit               | Ko Box                |
| Motor Lead Quantity/Wire Size | 3 @ 14 AWG            |
| Motor Lead Termination        | Flying Leads          |
| Motor Standards               | NEMA                  |
| Motor Type                    | 0738M                 |
| Mounting Arrangement          | F1                    |
| Number of Poles               | 4                     |
| Overall Length                | 19.20 IN              |
| Power Factor                  | 81                    |
| Product Family                | General Purpose       |
| Pulley End Bearing Type       | Ball                  |
| Pulley Face Code              | C-Face                |
| Pulley Shaft Indicator        | Standard              |
| Rodent Screen                 | None                  |
| RoHS Status                   | ROHS COMPLIANT        |
| Service Factor                | 1.15                  |
| Shaft Diameter                | 1.375 IN              |
| Shaft Extension Location      | Pulley End            |
| Shaft Ground Indicator        | No Shaft Grounding    |
| Shaft Rotation                | Reversible            |
| Shaft Slinger Indicator       | No Slinger            |
| Speed                         | 1770 rpm              |
| Speed Code                    | Single Speed          |
| Starting Method               | Direct on line        |
| Thermal Device - Bearing      | None                  |
| Thermal Device - Winding      | None                  |
| Vibration Sensor Indicator    | No Vibration Sensor   |
| Winding Thermal 1             | None                  |

Winding Thermal 2

None

---

## Nameplate

| NP3441L                   |              |      |     |      |   |    |   |  |  |
|---------------------------|--------------|------|-----|------|---|----|---|--|--|
| CAT.NO.                   | CEM3770T-5   |      |     |      |   |    |   |  |  |
| SPEC.                     | 07H058X817   |      |     |      |   |    |   |  |  |
| HP                        | 7.5          |      |     |      |   |    |   |  |  |
| VOLTS                     | 575          |      |     |      |   |    |   |  |  |
| AMP                       | 7.5          |      |     |      |   |    |   |  |  |
| RPM                       | 1770         |      |     |      |   |    |   |  |  |
| FRAME                     | 213TC        |      | HZ  | 60   |   | PH | 3 |  |  |
| SER.F.                    | 1.15         | CODE | J   | DES  | A | CL | F |  |  |
| NEMA-NOM-EFF              | 91.7         | PF   | 81  |      |   |    |   |  |  |
| RATING                    | 40C AMB-CONT |      |     |      |   |    |   |  |  |
| CC                        | 010A         |      |     |      |   |    |   |  |  |
| DE                        | 6307         |      | ODE | 6206 |   |    |   |  |  |
| ENCL                      | TEFC         | SN   |     |      |   |    |   |  |  |
| VPWM INVERTER READY       |              |      |     |      |   |    |   |  |  |
| CT6-60H(10:1)VT3-60H(20:1 |              |      |     |      |   |    |   |  |  |
|                           | SFA 8.7      |      |     |      |   |    |   |  |  |

**AC Induction Motor Performance Data**

Record # 26661

Typical performance - not guaranteed values

| Winding: 07WGX817-R001 |  |      |  | Type: 0738M                           |  | Enclosure: TEFC           |  |
|------------------------|--|------|--|---------------------------------------|--|---------------------------|--|
| Nameplate Data         |  |      |  | 575 V, 60 Hz:<br>Single Voltage Motor |  |                           |  |
| Rated Output (HP)      |  | 7.5  |  | Full Load Torque                      |  | 22.1 LB-FT                |  |
| Volts                  |  | 575  |  | Start Configuration                   |  | direct on line            |  |
| Full Load Amps         |  | 7.5  |  | Breakdown Torque                      |  | 73 LB-FT                  |  |
| R.P.M.                 |  | 1770 |  | Pull-up Torque                        |  | 33.7 LB-FT                |  |
| Hz                     |  | 60   |  | Phase                                 |  | 3                         |  |
| NEMA Design Code       |  | A    |  | KVA Code                              |  | J                         |  |
| Service Factor (S.F.)  |  | 1.15 |  | No-load Current                       |  | 3.66 A                    |  |
| NEMA Nom. Eff.         |  | 91.7 |  | Power Factor                          |  | 81                        |  |
| Rating - Duty          |  | 40C  |  | AMB-CONT                              |  | Temp. Rise @ Rated Load   |  |
| S.F. Amps              |  |      |  |                                       |  | Temp. Rise @ S.F. Load    |  |
|                        |  |      |  |                                       |  | Locked-rotor Power Factor |  |
|                        |  |      |  |                                       |  | Rotor inertia             |  |

**Load Characteristics 575 V, 60 Hz, 7.5 HP**

| % of Rated Load | 25   | 50   | 75   | 100  | 125  | 150  | S.F. |
|-----------------|------|------|------|------|------|------|------|
| Power Factor    | 40   | 62   | 73   | 79   | 82   | 84   | 82   |
| Efficiency      | 86.9 | 91.4 | 92.2 | 91.7 | 90.9 | 89.7 | 90.9 |
| Speed           | 1793 | 1786 | 1779 | 1771 | 1761 | 1751 | 1764 |
| Line amperes    | 4.07 | 4.98 | 6.23 | 7.7  | 9.4  | 11.2 | 8.58 |


ABB Motors and Mechanical Inc.

WINDING # 07WGX817

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 1770 RPM 575 V 0738M

TORQUES (LB-FT): PO=73 PU=33.7 LR=44.4 LRA=58.7



## AC Induction Motor Performance Data

Record # 44991

Typical performance - not guaranteed values

| Winding: 07WGX817-R001 |  |              |  | Type: 0738M                           |  | Enclosure: TEFC     |  |                           |  |        |  |
|------------------------|--|--------------|--|---------------------------------------|--|---------------------|--|---------------------------|--|--------|--|
| Nameplate Data         |  |              |  | 550 V, 50 Hz:<br>Single Voltage Motor |  |                     |  |                           |  |        |  |
| Rated Output (HP)      |  | 7.5          |  | Full Load Torque                      |  | 26.6 LB-FT          |  |                           |  |        |  |
| Volts                  |  | 550          |  | Start Configuration                   |  | direct on line      |  |                           |  |        |  |
| Full Load Amps         |  | 9.1          |  | Breakdown Torque                      |  | 95.8 LB-FT          |  |                           |  |        |  |
| R.P.M.                 |  | 1450         |  | Pull-up Torque                        |  | 50.5 LB-FT          |  |                           |  |        |  |
| Hz                     |  | 50 Phase     |  | 3                                     |  | Locked-rotor Torque |  | 66.5 LB-FT                |  |        |  |
| NEMA Design Code       |  | A            |  | KVA Code                              |  | K                   |  | Starting Current          |  | 69.3 A |  |
| Service Factor (S.F.)  |  | 1.15         |  | No-load Current                       |  | 5.77 A              |  | Line-line Res. @ 25°C     |  | 2.23 Ω |  |
| NEMA Nom. Eff.         |  | 89.5         |  | Power Factor                          |  | 71                  |  | Temp. Rise @ Rated Load   |  | 56°C   |  |
| Rating - Duty          |  | 40C AMB-CONT |  | Temp. Rise @ S.F. Load                |  | 67°C                |  | Locked-rotor Power Factor |  | 44.1   |  |
| S.F. Amps              |  |              |  | Rotor inertia                         |  | 0.934 LB-FT2        |  |                           |  |        |  |

## Load Characteristics 550 V, 50 Hz, 7.5 HP

| % of Rated Load | 25   | 50   | 75   | 100  | 125  | 150  | S.F. |
|-----------------|------|------|------|------|------|------|------|
| Power Factor    | 29   | 48   | 61   | 70   | 75   | 78   | 74   |
| Efficiency      | 83.2 | 89.2 | 90.1 | 90.2 | 89.6 | 88.6 | 89.4 |
| Speed           | 1494 | 1487 | 1480 | 1473 | 1464 | 1456 | 1466 |
| Line amperes    | 6.09 | 6.83 | 7.9  | 9.29 | 10.9 | 12.7 | 10.1 |


ABB Motors and Mechanical Inc.


WINDING # 07WGX817

Typical performance - not guaranteed values.




7.5 HP 3 PH 50 HZ 1450 RPM 550 V 0738M

TORQUES (LB-FT): PO=95.8 PU=50.5 LR=66.5 LRA=69.3





CD0006



- NOTES:
1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
  2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
  3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
  4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
  5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

|                                   |                                |                   |
|-----------------------------------|--------------------------------|-------------------|
| REV. DESC: ADD CLASS CONN00000007 |                                |                   |
| REV. LTR: E                       | VERSION: 01                    | TDR: 000001099922 |
| FILE: \AAA\00005\141              | REVISED: 10: 24: 49 02/19/2019 | BY: ENBRIRO       |
| MTL: —                            |                                |                   |

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1