



Customer information packet

CL3711T

10HP, 3450RPM, 1PH, 60HZ, 215TC, 3744LC, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	10.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	40.000 A @ 230.0 V 43.000 A @ 208.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	40.0 a

Part detail

Revision	AS
Type	AC
Mech. spec.	37F395
Base	
Status	PRD/A
Elec. spec.	37WGW578
Layout	37LYF395
Eff. date	05-10-2024
CD Diagram	CD0086
Poles	02
Leads	2#10 A PH,2#14 B PH
Proprietary	False
Created date	01-01-0001

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 10 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3744LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	19.75 IN
Power Factor	98
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	CL3711T								
SPEC.	37F395W578								
HP	10								
VOLTS	208-230								
AMP	43-40								
RPM	3450								
FRAME	215TC		HZ	60			PH	1	
SER.F.	1.00	CODE	H	DES	L	CLASS		F	
NEMA-NOM-EFF	82	PF	98						
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	TEFC	SN							

AC Induction Motor Performance Data

Record # 68813

Typical performance - not guaranteed values

Winding: 37GW578-R004			Type: 3744LC		Enclosure: TEFC		
Nameplate Data			230 V, 60 Hz: Single Voltage Motor				
Rated Output (HP)		10	Full Load Torque		15.12 LB-FT		
Volts		208-230	Start Configuration		direct on line		
Full Load Amps		43-40	Breakdown Torque		54.9 LB-FT		
R.P.M.		3450	Pull-up Torque		27.5 LB-FT		
Hz	60	Phase	1	Locked-rotor Torque		41.7 LB-FT	
NEMA Design Code		L	KVA Code	H	Starting Current		264 A
Service Factor (S.F.)		1		No-load Current		4.78 A	
NEMA Nom. Eff.		82	Power Factor	98	Line-line Res. @ 25°C		0.17816 Ω A Ph 0.74071 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		97°C	

Load Characteristics 230 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	98	100	100	99	97	96
Efficiency	74.5	83.9	84.3	83.7	81.3	77.8
Speed	3570.1	3541.3	3511.9	3473.8	3425.9	3363.7
Line amperes	10.8	19.5	28.1	39.3	51.6	65.4

ABB Motors and Mechanical Inc.

WINDING # 37GW578

Typical performance - not guaranteed values.

10 HP 1 PH 60 HZ 3450 RPM 230 V 3744LC

TORQUES (LB-FT): PO=54.9 PU=27.5 LR=41.7 LRA=264





