



Customer information packet

EM2402T

10HP, 880RPM, 3PH, 60HZ, 284T, 1046M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	284T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM NEMA_PREMIUM UR CSA EEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	29.200 A @ 230.0 V 30.000 A @ 208.0 V 14.600 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part detail

Revision	R
Type	AC
Mech. spec.	10C151
Base	
Status	PRD/A
Elec. spec.	10WGZ392
Layout	10LYC151
Eff. date	03-28-2024
CD Diagram	CD0180
Poles	08
Leads	9#10
Proprietary	False
Created date	04-06-2015

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	14.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1046M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	27.76 IN
Power Factor	71
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	880 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138L																
CAT.NO.	EM2402T			P/N					ENCLOSURE		TEFC					
SPEC.	10C151Z392G1		CC	010A		FRAME		284T		S/N						
HP	10			CLASS		F		HZ		60						
RPM	880			PH		3		DES		B						
VOLT	230/460							KVA-CODE		H		ODE BRG		6309	DE BRG	6311
AMP	29.2/14.6															
RATING	40C AMB-CONT				GREASE		POLYREX EM									
NEMA-NOM-EFF	89.5	PF	71	SER.F.		1.15										
HTR-VOLTS	HTR-AMPS															

AC Induction Motor Performance Data

Record # 49978

Typical performance - not guaranteed values

Winding: 10WGZ392-R001			Type: 1046M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		10		Full Load Torque		59.3 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		29.2/14.6		Breakdown Torque		169 LB-FT	
R.P.M.		880		Pull-up Torque		76.4 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		137 LB-FT	
NEMA Design Code		B	KVA Code	G	Starting Current		80 A
Service Factor (S.F.)		1.15		No-load Current		8.76 A	
NEMA Nom. Eff.		89.5	Power Factor	71	Line-line Res. @ 25°C		0.956 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		65°C	
S.F. Amps				Temp. Rise @ S.F. Load		77°C	
				Locked-rotor Power Factor		30.5	
				Rotor inertia		5.67 LB-FT2	

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	32	51	64	71	75	77	73
Efficiency	81	87.8	89.5	89.8	89.6	88.7	89.7
Speed	896	893	890	886	881	876	883
Line amperes	9.23	10.6	12.3	14.6	17.4	20.4	16.3


ABB Motors and Mechanical Inc.


WINDING # 10WGZ392

Typical performance - not guaranteed values.




10 HP 3 PH 60 HZ 880 RPM 460 V 1046M

TORQUES (LB-FT): PO=169 PU=76.4 LR=137 LRA=80





CD0180

LOW VOLTAGE
(2D)HIGH VOLTAGE
(1D)

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10:25:29 02/19/2019

BY: ENBRIRO

MTL: —



BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1