



Customer information packet

EM2524T

15HP, 1180RPM, 3PH, 60HZ, 284T, 4038M, OPSB, F1

Specifications

Enclosure	OPSB
Frame	284T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	42.000 A @ 208.0 V 41.000 A @ 230.0 V 20.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part detail

Revision	V
Type	AC
Mech. spec.	40G48
Base	
Status	PRD/A
Elec. spec.	40WGX775
Layout	40LYG048
Eff. date	01-31-2025
CD Diagram	CD0005
Poles	06
Leads	9#10
Proprietary	False
Created date	10-22-2010

High Voltage Full Load Amps	20.5 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4038M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	23.81 IN
Power Factor	75
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1180 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP2138LUA												
CAT.NO.	EM2524T			P/N					ENCLOSURE			OPSB
SPEC.	40G048X775		CC	010A	FRAME		284T		S/N			
HP	15			CLASS		F	HZ		60			
RPM	1180			PH	3	DES		B				
VOLT	230/460			KVA-CODE			G		ODE BRG	6309	DE BRG	6311
AMP	41/20.5											
RATING	40C AMB-CONT			GREASE			POLYREX EM					
NEMA-NOM-EFF	91.7	PF	75	SER.F.	1.15							
	50Hz 15Hp 190/380V 48/24A						SF 1.0					
HTR-VOLTS			HTR-AMPS									

Accessories

Part number	Description	Multiplier
40-1400	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 30818

Typical performance - not guaranteed values

Winding: 40WGX775-R001			Type: 4038M		Enclosure: OPSB		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		15	Full Load Torque		66.8 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		41/20.5	Breakdown Torque		185 LB-FT		
R.P.M.		1180	Pull-up Torque		87.7 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		105 LB-FT	
NEMA Design Code		B	KVA Code	G	Starting Current		116 A
Service Factor (S.F.)		1.15	No-load Current		10.1 A		
NEMA Nom. Eff.		91.7	Power Factor	75	Line-line Res. @ 25°C		0.67748 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		26°C
S.F. Amps					Temp. Rise @ S.F. Load		31°C
					Locked-rotor Power Factor		34
					Rotor inertia		4.65 LB-FT2

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	37	58	69	75	78	79	77
Efficiency	85.5	90.7	91.8	91.8	91.2	89.9	91.4
Speed	1195.6	1191.7	1187.6	1182.8	1177.5	1169.8	1180
Line amperes	11.1	13.4	16.6	20.4	24.8	30.7	23

ABB Motors and Mechanical Inc.

WINDING # 40WGX775

Typical performance - not guaranteed values.

15 HP 3 PH 60 HZ 1180 RPM 460 V 4038M

TORQUES (LB-FT): PO=185 PU=87.7 LR=105 LRA=116





