



Customer information packet

EM2334T-12

20HP, 1770RPM, 3PH, 60HZ, 256T, 0960M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	256T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	20.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM NEMA_PREMIUM UR CSA EEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	48.000 A @ 230.0 V 52.000 A @ 208.0 V 24.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part detail

Revision	W
Type	AC
Mech. spec.	09P11
Base	
Status	PRD/A
Elec. spec.	09WGT512
Layout	09LYP011
Eff. date	04-16-2024
CD Diagram	CD0104
Poles	04
Leads	12#10
Proprietary	False
Created date	11-24-2017

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	24.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	12 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0960M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	23.36 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Wye Start - Delta Run
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441L

CAT.NO. EM2334T-12

SPEC. 09P011T512

HP 20

VOLTS 230/460

AMP 48/24

RPM 1770

FRAME 256T HZ 60 PH 3

SER.F. 1.15 CODE J DES A CL F

NEMA-NOM-EFF 93 PF 83

RATING 40C AMB-CONT

CC 010A

DE 6309 ODE 6208

ENCL TEFC SN

VPWM INVERTER READY

CT6-60H(10:1)VT3-60H(20:1)

AC Induction Motor Performance Data

Record # 68096

Typical performance - not guaranteed values

Winding: 09WGT512-R001				Type: 0960M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		20		Full Load Torque		59.27 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		48/24		Breakdown Torque		232 LB-FT	
R.P.M.		1770		Pull-up Torque		126 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		141 LB-FT	
NEMA Design Code		A	KVA Code	J	Starting Current		198 A
Service Factor (S.F.)		1.15		No-load Current		10.4 A	
NEMA Nom. Eff.		93	Power Factor	83	Line-line Res. @ 25°C		0.33814 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		58°C	
S.F. Amps				Temp. Rise @ S.F. Load		70°C	
				Locked-rotor Power Factor		26.5	

Load Characteristics 460 V, 60 Hz, 20 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	78	83	86	87	85
Efficiency	89.2	93	93.7	93.6	93.1	92.4	93.3
Speed	1793.2	1786.4	1779.1	1771.9	1763.7	1755.3	1767
Line amperes	11.8	15	19.2	24	29.3	34.9	27.2

ABB Motors and Mechanical Inc.

WINDING # 09WGT512

Typical performance - not guaranteed values.

20 HP 3 PH 60 HZ 1770 RPM 460 V 0960M

TORQUES (LB-FT): PO=232 PU=126 LR=141 LRA=198





