



Customer information packet

EM2544T

50HP, 1185RPM, 3PH, 60HZ, 365T, 4466M, OPSB, F1

Specifications

Enclosure	OPSB
Frame	365T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	62.000 A @ 460.0 V 132.000 A @ 208.0 V 124.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part detail

Revision	T
Type	AC
Mech. spec.	44E196
Base	
Status	PRD/A
Elec. spec.	44WGW235
Layout	44LYE196
Eff. date	10-31-2024
CD Diagram	CD0180
Poles	06
Leads	9#6
Proprietary	False
Created date	05-10-2010

High Voltage Full Load Amps	62.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 6 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4466M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	33.72 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138LUA												
CAT.NO.	EM2544T			P/N					ENCLOSURE		OPSB	
SPEC.	44E196W235G1		CC	010A	FRAME		365T		S/N			
HP	50			CLASS		F	HZ		60			
RPM	1185			PH	3	DES		B				
VOLT	230/460			KVA-CODE			G		ODE BRG	6312	DE BRG	6313
AMP	124/62											
RATING	40C AMB-CONT				GREASE		POLYREX EM					
NEMA-NOM-EFF	94.1	PF	80	SER.F.	1.15							
	50Hz 50Hp 190/380V 148/74A						SF 1.0					
HTR-VOLTS	HTR-AMPS											

AC Induction Motor Performance Data

Record # 22264

Typical performance - not guaranteed values

Winding: 44WGW235-R001				Type: 4466M		Enclosure: OPSB	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		50		Full Load Torque		221 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		124/62		Breakdown Torque		669 LB-FT	
R.P.M.		1185		Pull-up Torque		263 LB-FT	
Hz		60		Phase		3	
NEMA Design Code		B		KVA Code		G	
Service Factor (S.F.)		1.15		Starting Current		391 A	
NEMA Nom. Eff.		94.1		Power Factor		80	
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load	
S.F. Amps						Temp. Rise @ S.F. Load	
						Locked-rotor Power Factor	
						Rotor inertia	

Load Characteristics 460 V, 60 Hz, 50 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	76	79	80	80	80
Efficiency	91.1	93.7	94.7	94.2	93.5	92.4	93.8
Speed	1196	1193	1189	1185	1180	1175	1182
Line amperes	28.7	37.5	49.1	62.5	77.4	93.8	71.4


ABB Motors and Mechanical Inc.

WINDING # 44WG235


Typical performance - not guaranteed values.

50 HP 3 PH 60 HZ 1185 RPM 460 V 4466M

TORQUES (LB-FT): PO=669 PU=263 LR=343 LRA=391



6/9/2025 ACPERF, record # 22264



CD0180

LOW VOLTAGE
(2D)HIGH VOLTAGE
(1D)

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007

REV. LTR: D

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\148

REVISED: 10: 25: 29 02/19/2019

BY: ENBRIRO

MTL: —

**BALDOR - RELIANCE®**

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1