



Customer information packet

EM2557T-4

125HP, 1190RPM, 3PH, 60HZ, 445T, 1884M, OPEN

Class - None

Division - Not Applicable

Specifications

Enclosure	DP
Frame	445T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	125.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	146.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.0 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	146.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	F
Lifting Lugs	No Lifting Lugs
Motor Lead Quantity/Wire Size	6 @ 4 AWG
Motor Standards	NEMA
Motor Type	A44062M
Mounting Arrangement	F1

Part detail


Revision	M
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A44WG1482
Layout	617428-042
Eff. date	06-11-2020
CD Diagram	416820-008
Poles	06
Leads	6#4
Proprietary	False
Created date	10-19-2010

Number of Poles	6
Overall Length	39.71 IN
Power Factor	84
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	3.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1185 rpm
Speed Code	Single Speed
Starting Method	Wye Start - Delta Run
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2377L



CAT.NO.	EM2557T-4				SPEC NO.			P44G1772					
HP	125	AMPS	146			VOLTS			460		DESIGN	B	
FRAME	445T		RPM	1185	HZ	60	AMB	40	SF	1.15			
DRIVE END BEARING	90BC03J30X		PHASE		3	DUTY	CONT		INSUL.CLASS		F		
OPP D.E. BEARING	90BC03J30X		TYPE		P	ENCL	DP	CODE	F				
SER.NO.				POWER FACTOR			84		NEMA-NOM-EFFICIENCY			95	
							MAX CORR KVAR		30.0	GUARANTEED EFFICIENCY		94.5	
							NEMA NOM/CSA QUOTED EFF						
							MOTOR WEIGHT						



416820-008

A-C MOTOR
CONNECTION DIAGRAM

STANDARD 6 LEAD Y START – DELTA RUN



< N. P. 1767-DC >

REV. DESC: ADDED T4 TO Y CONNECT DIAGRAM		
REV. LTR: D	VERSION: 04	TDR: 000000847713
FILE: \RAG\00001\808	REVISED: 10: 41: 26 04/08/2014	BY: RAGJSS1
MTL: —	 	

BALDOR

CONNECT DIAGRAM STD 6 LEAD Y START DELTA RUN
SH 1 of 1

416820-008