



Customer information packet

EM2559T-4

125HP, 1775RPM, 3PH, 60HZ, 405T, 4488M, OPSB, F

Specifications

Enclosure	OPSB
Frame	405T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	125.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	CSA EEV UR NEMA_PREMIUM NEMA PREMIUM
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	143.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	143.0 a
Insulation Class	F
Inverter Code	Inverter Ready

Part detail

Revision	AA
Type	AC
Mech. spec.	44E195
Base	
Status	PRD/A
Elec. spec.	44WGW047
Layout	44LYE195
Eff. date	10-31-2024
CD Diagram	CD0382
Poles	04
Leads	6#4 Y
Proprietary	False
Created date	08-06-2009

KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 4 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4488M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	34.47 IN
Power Factor	86
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Wye Start - Delta Run
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138LUA													
CAT.NO.	EM2559T-4				P/N					ENCLOSURE		OPSB	
SPEC.	44E195W047		CC	010A	FRAME		405T		S/N				
HP	125				CLASS		F	HZ		60			
RPM	1775				PH	3	DES		B				
VOLT	460				KVA-CODE			G	ODE BRG		6312	DE BRG	6316
AMP	143												
RATING	40C AMB-CONT				GREASE		POLYREX EM						
NEMA-NOM-EFF	95.4	PF	86	SER.F.	1.15								
	50HZ 100HP 380V 138A SF 1.0												
HTR-VOLTS			HTR-AMPS										

Accessories

Part number	Description	Multiplier
44-1402	C FACE KIT 44/404-5UC TC 6316 BRG	A8

AC Induction Motor Performance Data

Record # 13893

Typical performance - not guaranteed values

Winding: 44WGW047-R001			Type: 4488M		Enclosure: OPSB			
Nameplate Data			460 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		125	Full Load Torque		369 LB-FT			
Volts		460	Start Configuration		direct on line			
Full Load Amps		143	Breakdown Torque		1004 LB-FT			
R.P.M.		1775	Pull-up Torque		454 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		540 LB-FT		
NEMA Design Code		B	KVA Code	G	Starting Current		914 A	
Service Factor (S.F.)		1.15	No-load Current		46 A			
NEMA Nom. Eff.		95.4	Power Factor		86	Line-line Res. @ 25°C		0.0379 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		48°C	
S.F. Amps					Temp. Rise @ S.F. Load		64°C	
					Locked-rotor Power Factor		25.5	
					Rotor inertia		16.6 lb-ft²	

Load Characteristics 460 V, 60 Hz, 125 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	56	77	84	86	87	86	87
Efficiency	93.5	95.5	95.7	95.4	94.9	94.1	95.1
Speed	1794	1789	1783	1777	1770	1762	1773
Line amperes	56.3	79.8	109.4	142.6	177.7	216	163.7

ABB Motors and Mechanical Inc.

WINDING # 44WG047

Typical performance - not guaranteed values.

125 HP 3 PH 60 HZ 1775 RPM 460 V 4488M

TORQUES (LB-FT): PO=1004 PU=454 LR=540 LRA=914





