



Customer information packet

EM2542T-8

50HP, 3525RPM, 3PH, 60HZ, 324TS, 4058M, OPSB, F

Specifications

Enclosure	OPSB
Frame	324TS
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	CSA EEV UR NEMA_PREMIUM NEMA PREMIUM
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	129.000 A @ 200.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	129.0 a
Insulation Class	F
Inverter Code	Inverter Ready

Part detail

Revision	K
Type	AC
Mech. spec.	40E213
Base	
Status	PRD/A
Elec. spec.	40WGX311
Layout	40LYE213
Eff. date	06-27-2024
CD Diagram	CD0695
Poles	02
Leads	6#6
Proprietary	False
Created date	08-12-2015

IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 6 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4058M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	25.69 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3525 rpm
Speed Code	Single Speed
Starting Method	Part Winding
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3554L											
CAT.NO.	EM2542T-8			P/N						ENCL	OPSB
SPEC.	40E213X311	CC	010A	FRAME		324TS	SER.NO.				
HP	50		CLASS		F	HZ	60				
RPM	3525		PH	3	DES		A				
VOLTS	200			CODE		G	ODE BRG	6309	DE BRG	6312	
AMPS	129										
RATING	40C AMB-CONT		NEMA-NOM-EFF			93	GREASE	POLYREX EM			
PF	90	SER.F.	1.15		VPWM INVERTER READY						
HTR-VOLTS	HTR-AMPS	MAX. SPACE HEATER TEMP.									

AC Induction Motor Performance Data

Record # 52219

Typical performance - not guaranteed values

Winding: 40WGX311-R001			Type: 4058M		Enclosure: OPSB			
Nameplate Data			200 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		50	Full Load Torque		74.7 LB-FT			
Volts		200	Start Configuration		direct on line			
Full Load Amps		129	Breakdown Torque		174 LB-FT			
R.P.M.		3525	Pull-up Torque		119 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		139 LB-FT		
NEMA Design Code		A	KVA Code	G	Starting Current		892 A	
Service Factor (S.F.)		1.15	No-load Current		34.3 A			
NEMA Nom. Eff.		93	Power Factor		90	Line-line Res. @ 25°C		0.0243 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		46°C		
S.F. Amps				Temp. Rise @ S.F. Load		57°C		
				Locked-rotor Power Factor		23		
				Rotor inertia		2.49 LB-FT2		

Load Characteristics 200 V, 60 Hz, 50 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	63	82	88	90	90	90	90
Efficiency	92.5	94.5	94.2	93.4	92.2	90.5	92.7
Speed	3582	3566	3547	3529	3508	3479	3516
Line amperes	46.8	70	98.2	129	162	205	149


ABB Motors and Mechanical Inc.


WINDING # 40WGX311

Typical performance - not guaranteed values.



50 HP 3 PH 60 HZ 3525 RPM 200 V 4058M

TORQUES (LB-FT): PO=174 PU=119 LR=139 LRA=892







CD0695



START CONNECTION



RUN CONNECTION



- NOTES:
- 1. MOTOR MAY BE WYE CONNECTED OR DELTA CONNECTED.
 - 2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 - 5. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0695

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: C	BY: JLP	REVISED: 01/21/99 3:19	TDR: 0171435
S69000		FILE: AAA00005151	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, SV, 6 LEADS, PART WINDING START