



Customer information packet

EM31104-5

.33HP, 1725RPM, 3PH, 60HZ, 56, 3416M, OPEN, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.330 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.500 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	73.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	0.5 a
Insulation Class	B
Inverter Code	Not Inverter

Part detail

Revision	F
Type	AC
Mech. spec.	34F779
Base	
Status	PRD/A
Elec. spec.	34WGR271
Layout	34LYF779
Eff. date	10-29-2024
CD Diagram	CD0006
Poles	04
Leads	3#18
Proprietary	False
Created date	01-12-2015

KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3416M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	9.51 IN
Power Factor	66
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.35
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2116L									
CAT.NO.	EM31104-5								
SPEC.	34F779R271G1								
HP	.33								
VOLTS	575								
AMP	.5								
RPM	1725								
FRAME	56			HZ		60		PH	3
SER.F.	1.35	CODE	N	DES		B	CL	B	
NEMA-NOM-EFF	73.4	PF	66						
RATING	40C AMB-CONT								
CC									
DE	6203	ODE	6203						
ENCL	OPEN	SN							
	SFA .6								

AC Induction Motor Performance Data

Record # 48811

Typical performance - not guaranteed values

Winding: 34WGR271-R001				Type: 3416M		Enclosure: OPEN					
Nameplate Data				575 V, 60 Hz: High Voltage Connection							
Rated Output (HP)		.33		Full Load Torque		1.01 LB-FT					
Volts		575		Start Configuration		direct on line					
Full Load Amps		.5		Breakdown Torque		4.53 LB-FT					
R.P.M.		1725		Pull-up Torque		3.16 LB-FT					
Hz		60 Phase		3		Locked-rotor Torque		3.79 LB-FT			
NEMA Design Code		B		KVA Code		N		Starting Current		3.77 A	
Service Factor (S.F.)		1.35		No-load Current		0.353 A					
NEMA Nom. Eff.		73.4		Power Factor		66		Line-line Res. @ 25°C		66.3 Ω	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		18°C					
S.F. Amps		.6		Temp. Rise @ S.F. Load		23°C					
				Locked-rotor Power Factor		58.6					
				Rotor inertia		0.0381 LB-FT2					

Load Characteristics 575 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	45	57	66	73	78	75
Efficiency	55.6	69.9	74.7	77	76.5	76.4	76.5
Speed	1786	1772	1758	1743	1726	1709	1719
Line amperes	0.364	0.396	0.438	0.492	0.556	0.629	0.585


ABB Motors and Mechanical Inc.


WINDING # 34WGR271

Typical performance - not guaranteed values.



0.33 HP 3 PH 60 HZ 1725 RPM 575 V 3416M

TORQUES (LB-FT): PO=4.53 PU=3.16 LR=3.79 LRA=3.77





CD0006



- NOTES:
- 1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
 - 2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 - 5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10: 24: 49 02/19/2019	BY: ENBRIRO
MTL: —		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1