



Customer information packet

EM3215T

2HP, 1175RPM, 3PH, 60HZ, 184T, 3636M, OPSB, F1

Class - None

Division - Not Applicable

Specifications

| | |
|--------------------------------|---|
| Enclosure | OPSB |
| Frame | 184T |
| Frame Material | Steel |
| Frequency | 60.00 Hz |
| Haz Area Class and Group | None |
| Haz Area Division | Not Applicable |
| Motor Letter Type | Three Phase |
| Output @ Frequency | 2.000 HP @ 60 HZ |
| Phase | 3 |
| Synchronous Speed @ Frequency | 1200 RPM @ 60 HZ |
| Voltage @ Frequency | 230.0 V @ 60 HZ 460.0 V @ 60 HZ |
| Agency Approvals | CSA EEV NEMA PREMIUM NEMA_PREMIUM UR |
| Ambient Temperature | 40 °C |
| Auxillary Box | No Auxillary Box |
| Auxillary Box Lead Termination | None |
| Base Indicator | Rigid |
| Bearing Grease Type | Polyrex EM (-20F +300F) |
| Blower | None |
| Current @ Voltage | 6.800 A @ 230.0 V 6.800 A @ 208.0 V 3.400 A @ 460.0 V |
| Design Code | B |
| Drip Cover | No Drip Cover |
| Duty Rating | CONT |
| Efficiency @ 100% Load | 87.5 % |
| Electrically Isolated Bearing | Not Electrically Isolated |
| Feedback Device | NO FEEDBACK |
| Front Shaft Indicator | None |

Part detail

| | |
|--------------|------------|
| Revision | C |
| Type | AC |
| Mech. spec. | 36G548 |
| Base | |
| Status | PRD/A |
| Elec. spec. | 36WGQ036 |
| Layout | 36LYG548 |
| Eff. date | 05-01-2024 |
| CD Diagram | CD0005 |
| Poles | 06 |
| Leads | 9#16 |
| Proprietary | False |
| Created date | 12-14-2020 |

| | |
|-------------------------------|---------------------|
| Heater Indicator | No Heater |
| High Voltage Full Load Amps | 3.4 a |
| Insulation Class | F |
| Inverter Code | Inverter Ready |
| KVA Code | L |
| Lifting Lugs | No Lifting Lugs |
| Locked Bearing Indicator | No Locked Bearing |
| Motor Lead Quantity/Wire Size | 9 @ 16 AWG |
| Motor Lead Termination | Flying Leads |
| Motor Standards | NEMA |
| Motor Type | 3636M |
| Mounting Arrangement | F1 |
| Number of Poles | 6 |
| Overall Length | 16.50 IN |
| Power Factor | 63 |
| Product Family | General Purpose |
| Pulley End Bearing Type | Ball |
| Pulley Face Code | Standard |
| Pulley Shaft Indicator | Standard |
| Rodent Screen | None |
| Service Factor | 1.15 |
| Shaft Diameter | 1.125 IN |
| Shaft Ground Indicator | No Shaft Grounding |
| Shaft Rotation | Reversible |
| Shaft Slinger Indicator | No Slinger |
| Speed | 1175 rpm |
| Speed Code | Single Speed |
| Starting Method | Direct on line |
| Thermal Device - Bearing | None |
| Thermal Device - Winding | None |
| Vibration Sensor Indicator | No Vibration Sensor |
| Winding Thermal 1 | None |
| Winding Thermal 2 | None |

Nameplate

| NP1259LUA | | | | | | | | | |
|-----------------------|----------------------------|-------------|-------------|------------|---|--------------|---|-------|--|
| CAT.NO. | EM3215T | | | | | | | | |
| SPEC. | 36G548Q036G1 | | | | | | | | |
| HP | 2 | | | | | | | | |
| VOLTS | 230/460 | | | | | | | | |
| AMPS | 6.8/3.4 | | | | | | | | |
| R.P.M. | 1175 | | | | | | | | |
| FRAME | 184T | | HZ | 60 | | PH | 3 | | |
| SER.F. | 1.15 | CODE | L | DES | B | CLASS | F | | |
| NEMA NOM. EFF. | 87.5 | | P.F. | 63 | | | | | |
| RATING | 40C AMB-CONT | | | | | | | | |
| CC | 010A | | | | | | | | |
| DE | 6206 | | ODE | 6205 | | | | | |
| ENCL | OPSB | SN | | | | | | | |
| USABLE AT | 50HZ 2HP 190/380V 8.0/4.0A | | | | | | | SF1.0 | |

Accessories

| Part number | Description | Multiplier |
|--------------------|--------------------|-------------------|
| 36-3403 | C FACE KIT | A8 |
| 36EP1405A09SP | D-FLANGE KIT | |

AC Induction Motor Performance Data

Record # 85840

Typical performance - not guaranteed values

| Winding: 36WGQ036-R001 | | Type: 3636M | Enclosure: OPSB | |
|------------------------|-------------------|---------------------------|--|--|
| Nameplate Data | | | 460 V, 60 Hz: High Voltage Connection | |
| Rated Output (HP) | 2 | Full Load Torque | 8.95 LB-FT | |
| Volts | 230/460 | Start Configuration | direct on line | |
| Full Load Amps | 6.8/3.4 | Breakdown Torque | 33.9 LB-FT | |
| R.P.M. | 1175 | Pull-up Torque | 20.3 LB-FT | |
| Hz | 60 Phase | Locked-rotor Torque | 24.7 LB-FT | |
| NEMA Design Code | B KVA Code | Starting Current | 23.7 A | |
| Service Factor (S.F.) | 1.15 | No-load Current | 2.25 A | |
| NEMA Nom. Eff. | 87.5 Power Factor | Line-line Res. @ 25°C | 5.23 Ω | |
| Rating - Duty | 40C AMB-CONT | Temp. Rise @ Rated Load | 25°C | |
| S.F. Amps | 7.4/3.7 | Temp. Rise @ S.F. Load | 32°C | |
| | | Locked-rotor Power Factor | 47.5 | |
| | | Rotor inertia | 0.338 lb-ft ² | |

Load Characteristics 460 V, 60 Hz, 2 HP

| % of Rated Load | 25 | 50 | 75 | 100 | 125 | 150 | S.F. |
|-----------------|------|------|------|------|------|------|------|
| Power Factor | 26 | 43 | 55 | 62 | 68 | 72 | 66 |
| Efficiency | 77.5 | 85.3 | 87.5 | 87.8 | 87.4 | 86.5 | 87.7 |
| Speed | 1194 | 1187 | 1181 | 1173 | 1166 | 1156 | 1169 |
| Line amperes | 2.36 | 2.62 | 2.99 | 3.44 | 3.96 | 4.55 | 3.74 |


ABB Motors and Mechanical Inc.

WINDING # 36WGQ036


Typical performance - not guaranteed values.

2 HP 3 PH 60 HZ 1175 RPM 460 V 3636M


TORQUES (LB-FT): PO=33.9 PU=20.3 LR=24.7 LRA=23.7




6/9/2025 ACPERF, record # 85840



CD0005




LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

| | | | |
|---|---------|-------------------------|--------------|
| REV. DESC: REVISE TO SHOW OPTIONAL COLORS | | | |
| REV. LTR: E | BY: JLP | REVISED: 01/19/99 10:15 | TDR: 0171435 |
| S00000 | | FILE: AAA00005140 | MDL: - |
| | | MTL: - | |

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS