

BALDOR • RELIANCE

Customer information packet

EM3220T

1.5HP, 855RPM, 3PH, 60HZ, 184T, 3642M, OPEN, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA CURUSEEV UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.000 A @ 208.0 V 6.000 A @ 230.0 V 3.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	77.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part detail

Revision	L
Type	AC
Mech. spec.	36B001
Base	
Status	PRD/A
Elec. spec.	36WGR623
Layout	36LYB001
Eff. date	05-01-2024
CD Diagram	CD0005
Poles	08
Leads	9#16
Proprietary	False
Created date	04-27-2015

Heater Indicator	No Heater
High Voltage Full Load Amps	3.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3642M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	16.50 IN
Power Factor	60
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	855 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1

None

Winding Thermal 2

None

Nameplate

NP2116L									
CAT.NO.	EM3220T								
SPEC.	36B001R623G1								
HP	1.5								
VOLTS	230/460								
AMP	6/3								
RPM	855								
FRAME	184T		HZ	60		PH	3		
SER.F.	1.15	CODE	K	DES	B	CL	F		
NEMA-NOM-EFF	77	PF	60						
RATING	40C AMB-CONT								
CC	010A								
DE	6206	ODE	6205						
ENCL	OPEN	SN							

AC Induction Motor Performance Data

Record # 66592

Typical performance - not guaranteed values

Winding: 36WGR623-R011		Type: 3642M	Enclosure: OPEN	
Nameplate Data			460 V, 60 Hz: High Voltage Connection	
Rated Output (HP)	1.5	Full Load Torque	9.45 LB-FT	
Volts	230/460	Start Configuration	direct on line	
Full Load Amps	6/3	Breakdown Torque	28.64 LB-FT	
R.P.M.	855	Pull-up Torque	20.44 LB-FT	
Hz	60 Phase	3	Locked-rotor Torque	27.45 LB-FT
NEMA Design Code	B KVA Code	K	Starting Current	16.03 A
Service Factor (S.F.)	1.15	No-load Current	2.2 A	
NEMA Nom. Eff.	77 Power Factor	60	Line-line Res. @ 25°C	8.07 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	61°C	
S.F. Amps		Temp. Rise @ S.F. Load	76°C	
		Locked-rotor Power Factor	48.6	
		Rotor inertia	0.394 LB-FT ²	

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	40	51	60	67	71	64
Efficiency	66.6	75.6	78.4	78.2	76.9	74.2	77.9
Speed	889	879	868	856	841	823	847
Line amperes	2.24	2.43	2.71	3.06	3.5	4.05	3.31


ABB Motors and Mechanical Inc.

WINDING # 36WGR623


Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 855 RPM 460 V 3642M

TORQUES (LB-FT): PO=28.64 PU=20.44 LR=27.45 LRA=16.03



6/9/2025 ACPERF, record # 66592



CD0005



LOW VOLTAGE
(2Y)



LINE

HIGH VOLTAGE
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS