



---

# Customer information packet

## EM3615T-9

5HP, 1755RPM, 3PH, 60HZ, 184T, 3644M, TEFC, F1

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	184T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.100 A @ 460.0 V 14.200 A @ 230.0 V 14.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

## Part detail

Revision	F
Type	AC
Mech. spec.	36Q306
Base	
Status	PRD/A
Elec. spec.	36WGR929
Layout	36LYQ306
Eff. date	04-15-2024
CD Diagram	CD0005
Poles	04
Leads	9#16
Proprietary	False
Created date	02-25-2016

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.1 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3644M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.04 IN
Power Factor	74
Product Family	WP Below Decks Marine Duty
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1755 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

<b>Vibration Sensor Indicator</b>	<b>No Vibration Sensor</b>
<b>Winding Thermal 1</b>	<b>None</b>
<b>Winding Thermal 2</b>	<b>None</b>

**Nameplate**

<b>NP1267L</b>									
<b>CAT.NO.</b>	EM3615T-9								
<b>SPEC.</b>	36Q306R929G1								
<b>HP</b>	5								
<b>VOLTS</b>	230/460								
<b>AMP</b>	14.2/7.1								
<b>RPM</b>	1755								
<b>FRAME</b>	184T		<b>HZ</b>	60		<b>PH</b>	3		
<b>SER.F.</b>	1.15	<b>CODE</b>	L	<b>DES</b>	A	<b>CL</b>	F		
<b>NEMA-NOM-EFF</b>	89.5	<b>PF</b>	74						
<b>RATING</b>	40C AMB-CONT								
<b>CC</b>	010A								
<b>DE</b>	6206	<b>ODE</b>	6205						
<b>ENCL</b>	TEFC	<b>SN</b>							
	DES C TORQUE								

**AC Induction Motor Performance Data**

Record # 51113

Typical performance - not guaranteed values

Winding: 36WGR929-R001		Type: 3644M		Enclosure: TEFC	
<b>Nameplate Data</b>			<b>460 V, 60 Hz: High Voltage Connection</b>		
Rated Output (HP)	5	Full Load Torque	14.87 LB-FT		
Volts	230/460	Start Configuration	direct on line		
Full Load Amps	14.2/7.1	Breakdown Torque	66.64 LB-FT		
R.P.M.	1755	Pull-up Torque	40.43 LB-FT		
Hz	60 Phase	Locked-rotor Torque	44.86 LB-FT		
NEMA Design Code	A KVA Code	Starting Current	61.49 A		
Service Factor (S.F.)	1.15	No-load Current	4.27 A		
NEMA Nom. Eff.	89.5 Power Factor	Line-line Res. @ 25°C	1.83 Ω		
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	65°C		
S.F. Amps		Temp. Rise @ S.F. Load	77°C		
		Locked-rotor Power Factor	40.3		
		Rotor inertia	0.41 LB-FT <sup>2</sup>		

**Load Characteristics 460 V, 60 Hz, 5 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	31	52	65	73	78	81	77
Efficiency	81.2	87.9	89.8	89.7	89.5	88.3	89.6
Speed	1787	1777	1768	1757	1745	1732	1749
Line amperes	4.51	5.16	6.02	7.13	8.39	9.83	7.82


ABB Motors and Mechanical Inc.

WINDING # 36WGR929


5 HP 3 PH 60 HZ 1755 RPM 460 V 3644M

Typical performance - not guaranteed values.


TORQUES (LB-FT): PO=66.64 PU=40.43 LR=44.86 LRA=61.49




6/9/2025 ACPERF, record # 51113



CD0005




LOW VOLTAGE  
(2Y)



LINE

HIGH VOLTAGE  
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
S00000		FILE: AAA00005140	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 9 LEADS