



---

# Customer information packet

## EM3311T

7.5HP, 1770RPM, 3PH, 60HZ, 213T, 3734M, OPSB, F

Class - None

Division - Not Applicable

## Specifications

|                                |                                                               |
|--------------------------------|---------------------------------------------------------------|
| Enclosure                      | OPSB                                                          |
| Frame                          | 213T                                                          |
| Frame Material                 | Steel                                                         |
| Frequency                      | 60.00 Hz                                                      |
| Haz Area Class and Group       | None                                                          |
| Haz Area Division              | Not Applicable                                                |
| Motor Letter Type              | Three Phase                                                   |
| Output @ Frequency             | 7.500 HP @ 60 HZ                                              |
| Phase                          | 3                                                             |
| Synchronous Speed @ Frequency  | 1800 RPM @ 60 HZ                                              |
| Voltage @ Frequency            | 230.0 V @ 60 HZ<br>460.0 V @ 60 HZ                            |
| Agency Approvals               | CSA EEV<br>NEMA PREMIUM<br>NEMA_PREMIUM<br>UR                 |
| Ambient Temperature            | 40 °C                                                         |
| Auxillary Box                  | No Auxillary Box                                              |
| Auxillary Box Lead Termination | None                                                          |
| Base Indicator                 | Rigid                                                         |
| Bearing Grease Type            | Polyrex EM (-20F +300F)                                       |
| Blower                         | None                                                          |
| Current @ Voltage              | 9.800 A @ 460.0 V<br>20.600 A @ 208.0 V<br>19.600 A @ 230.0 V |
| Design Code                    | A                                                             |
| Drip Cover                     | No Drip Cover                                                 |
| Duty Rating                    | CONT                                                          |
| Efficiency @ 100% Load         | 91.0 %                                                        |
| Electrically Isolated Bearing  | Not Electrically Isolated                                     |
| Feedback Device                | NO FEEDBACK                                                   |
| Front Shaft Indicator          | None                                                          |

## Part detail

|              |            |
|--------------|------------|
| Revision     | F          |
| Type         | AC         |
| Mech. spec.  | 37F614     |
| Base         |            |
| Status       | PRD/A      |
| Elec. spec.  | 37WGL863   |
| Layout       | 37LYF614   |
| Eff. date    | 06-11-2024 |
| CD Diagram   | CD0005     |
| Poles        | 04         |
| Leads        | 9#14       |
| Proprietary  | False      |
| Created date | 11-10-2020 |

|                               |                       |
|-------------------------------|-----------------------|
| Heater Indicator              | No Heater             |
| High Voltage Full Load Amps   | 9.8 a                 |
| Insulation Class              | F                     |
| Inverter Code                 | Inverter Ready        |
| KVA Code                      | J                     |
| Lifting Lugs                  | Standard Lifting Lugs |
| Locked Bearing Indicator      | No Locked Bearing     |
| Motor Lead Quantity/Wire Size | 9 @ 14 AWG            |
| Motor Lead Termination        | Flying Leads          |
| Motor Standards               | NEMA                  |
| Motor Type                    | 3734M                 |
| Mounting Arrangement          | F1                    |
| Number of Poles               | 4                     |
| Overall Length                | 16.32 IN              |
| Power Factor                  | 79                    |
| Product Family                | General Purpose       |
| Pulley End Bearing Type       | Ball                  |
| Pulley Face Code              | Standard              |
| Pulley Shaft Indicator        | Standard              |
| Rodent Screen                 | None                  |
| RoHS Status                   | ROHS COMPLIANT        |
| Service Factor                | 1.15                  |
| Shaft Diameter                | 1.375 IN              |
| Shaft Ground Indicator        | No Shaft Grounding    |
| Shaft Rotation                | Reversible            |
| Shaft Slinger Indicator       | No Slinger            |
| Speed                         | 1770 rpm              |
| Speed Code                    | Single Speed          |
| Starting Method               | Direct on line        |
| Thermal Device - Bearing      | None                  |
| Thermal Device - Winding      | None                  |
| Vibration Sensor Indicator    | No Vibration Sensor   |
| Winding Thermal 1             | None                  |
| Winding Thermal 2             | None                  |

## Nameplate

## NP3553LUA

|                           |                                |      |     |    |      |   |       |  |   |  |       |
|---------------------------|--------------------------------|------|-----|----|------|---|-------|--|---|--|-------|
| CAT.NO.                   | EM3311T                        |      |     |    |      |   |       |  |   |  |       |
| SPEC.                     | 37F614L863G1                   |      |     |    |      |   |       |  |   |  |       |
| HP                        | 7.5                            |      |     |    |      |   |       |  |   |  |       |
| VOLTS                     | 230/460                        |      |     |    |      |   |       |  |   |  |       |
| AMPS                      | 19.6/9.8                       |      |     |    |      |   |       |  |   |  |       |
| RPM                       | 1770                           |      |     |    |      |   |       |  |   |  |       |
| FRAME                     | 213T                           |      | HZ  |    | 60   |   | PH    |  | 3 |  |       |
| SF                        | 1.15                           | CODE |     | J  | DES  | A | CLASS |  | F |  |       |
| NEMA NOM. EFF             | 91                             | PF   |     | 79 |      |   |       |  |   |  |       |
| RATING                    | 40C AMB-CONT                   |      |     |    |      |   |       |  |   |  |       |
| CC                        | 010A                           |      |     |    |      |   |       |  |   |  |       |
| ENCL                      | OPSB                           | SN   |     |    |      |   |       |  |   |  |       |
| DE                        | 6307                           |      | ODE |    | 6206 |   |       |  |   |  |       |
| VPWM INVERTER READY       |                                |      |     |    |      |   |       |  |   |  |       |
| CT30-60(2:1) VT3-60(20:1) |                                |      |     |    |      |   |       |  |   |  |       |
| USABLE AT                 | 50HZ 7.5HP 190/380V 23.2/11.6A |      |     |    |      |   |       |  |   |  |       |
|                           |                                |      |     |    |      |   |       |  |   |  | SF1.0 |

**Accessories**

| Part number | Description | Multiplier |
|-------------|-------------|------------|
| 37-1404     | C FACE KIT  | A8         |

## AC Induction Motor Performance Data

Record # 85452

Preliminary Data Sheet

| Winding: 37WGL863-R001 |    |              | Type: 3734M  |                                          | Enclosure: OPSB       |                |        |
|------------------------|----|--------------|--------------|------------------------------------------|-----------------------|----------------|--------|
| Nameplate Data         |    |              |              | 460 V, 60 Hz:<br>High Voltage Connection |                       |                |        |
| Rated Output (HP)      |    | 7.5          |              | Full Load Torque                         |                       | 22.2 LB-FT     |        |
| Volts                  |    | 230/460      |              | Start Configuration                      |                       | direct on line |        |
| Full Load Amps         |    | 19.6/9.8     |              | Breakdown Torque                         |                       | 74.8 LB-FT     |        |
| R.P.M.                 |    | 1770         |              | Pull-up Torque                           |                       | 37.1 LB-FT     |        |
| Hz                     | 60 | Phase        | 3            | Locked-rotor Torque                      |                       | 45.4 LB-FT     |        |
| NEMA Design Code       |    | A            | KVA Code     | J                                        | Starting Current      |                | 72 A   |
| Service Factor (S.F.)  |    | 1.15         |              | No-load Current                          |                       | 4.87 A         |        |
| NEMA Nom. Eff.         |    | 91           | Power Factor | 79                                       | Line-line Res. @ 25°C |                | 1.67 Ω |
| Rating - Duty          |    | 40C AMB-CONT |              | Temp. Rise @ Rated Load                  |                       | 35°C           |        |
| S.F. Amps              |    | 22.0/11.0    |              | Temp. Rise @ S.F. Load                   |                       | 47°C           |        |
|                        |    |              |              | Locked-rotor Power Factor                |                       | 45.8           |        |
|                        |    |              |              | Rotor inertia                            |                       | 0.836 lb-ft²   |        |

## Load Characteristics 460 V, 60 Hz, 7.5 HP

| % of Rated Load | 25   | 50   | 75   | 100  | 125  | 150  | S.F. |
|-----------------|------|------|------|------|------|------|------|
| Power Factor    | 39   | 60   | 73   | 79   | 82   | 83   | 81   |
| Efficiency      | 85   | 90.1 | 91.1 | 90.9 | 90.1 | 89   | 90.3 |
| Speed           | 1793 | 1786 | 1779 | 1772 | 1764 | 1755 | 1766 |
| Line amperes    | 5.34 | 6.47 | 7.99 | 9.87 | 11.9 | 14.2 | 11.1 |

ABB Motors and Mechanical Inc.

WINDING # 37WGL863

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 3734M

TORQUES (LB-FT): PO=74.8 PU=37.1 LR=45.4 LRA=72







