



Customer information packet

EM3550T

1.5HP, 3500RPM, 3PH, 60HZ, 3520M, 143T, N

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	143T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	1.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM NEMA_PREMIUM UR CSA EEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.800 A @ 230.0 V 4.000 A @ 208.0 V 1.900 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	84.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part detail

Revision	Z
Type	AC
Mech. spec.	35T638
Base	
Status	PRD/A
Elec. spec.	35WGM760
Layout	35LYT638
Eff. date	08-22-2024
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	04-28-2010

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.9 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3520M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	12.29 IN
Power Factor	85
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3500 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA

CAT.NO.	EM3550T									
SPEC	35T638M760G1									
HP	1.5									
VOLTS	230/460									
AMPS	3.8/1.9									
RPM	3500									
FRAME	143T		HZ	60		PH	3			
SF	1.15	CODE	L	DES	B	CLASS	F			
NEMA NOM. EFF	84	PF	85							
RATING	40C AMB-CONT									
CC	010A									
ENCL	TEFC	SER								
DE	6205		ODE	6203						
VPWM INVERTER READY	SFA 4.4/2.2									
CT6-60H(10:1)VT3-60H(20:1										
	50Hz 1.5HP 190/380V 4.6/2.3A									

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data

Record # 52482

Typical performance - not guaranteed values

Winding: 35WGM760-R051				Type: 3520M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection				
Rated Output (HP)		1.5		Full Load Torque		2.22 LB-FT		
Volts		230/460		Start Configuration		direct on line		
Full Load Amps		3.8/1.9		Breakdown Torque		9.49 LB-FT		
R.P.M.		3500		Pull-up Torque		3.61 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		7.35 LB-FT		
NEMA Design Code		B		KVA Code	L		Starting Current	17.9 A
Service Factor (S.F.)		1.15		No-load Current		0.932 A		
NEMA Nom. Eff.		84		Power Factor	85		Line-line Res. @ 25°C	12.2 Ω
Rating - Duty		40C		AMB-CONT		Temp. Rise @ Rated Load		43°C
S.F. Amps						Temp. Rise @ S.F. Load		50°C
						Locked-rotor Power Factor		60.1
						Rotor inertia		0.0553 LB-FT2

Load Characteristics 460 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	79	85	89	90	87
Efficiency	72.3	82.2	84.4	84.8	84.3	82.8	84.5
Speed	3575	3551	3526	3498	3466	3433	3479
Line amperes	1.03	1.25	1.55	1.91	2.31	2.79	2.15


ABB Motors and Mechanical Inc.

WINDING # 35WGM760

Typical performance - not guaranteed values.

1.5 HP 3 PH 60 HZ 3500 RPM 460 V 3520M

TORQUES (LB-FT): PO=9.49 PU=3.61 LR=7.35 LRA=17.9



AC Induction Motor Performance Data

Record # 59170

Typical performance - not guaranteed values

Winding: 35WGM760-R051			Type: 3520M		Enclosure: TEFC		
Nameplate Data				230 V, 60 Hz: Low Voltage Connection			
Rated Output (HP)		1.5		Full Load Torque		2.22 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		3.8/1.9		Breakdown Torque		9.49 LB-FT	
R.P.M.		3500		Pull-up Torque		3.61 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		7.35 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		35.8 A
Service Factor (S.F.)		1.15		No-load Current		1.86 A	
NEMA Nom. Eff.		84	Power Factor	85	Line-line Res. @ 25°C		3.04 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		43°C	
S.F. Amps				Temp. Rise @ S.F. Load		50°C	
				Locked-rotor Power Factor		60.1	
				Rotor inertia		0.0553 LB-FT2	

Load Characteristics 230 V, 60 Hz, 1.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	45	67	79	85	89	90	87
Efficiency	72.3	82.2	84.4	84.8	84.3	82.8	84.5
Speed	3575	3551	3526	3498	3466	3433	3479
Line amperes	2.06	2.5	3.1	3.82	4.62	5.58	4.3


ABB Motors and Mechanical Inc.


WINDING # 35WGM760

Typical performance - not guaranteed values.



1.5 HP 3 PH 60 HZ 3500 RPM 230 V 3520M

TORQUES (LB-FT): PO=9.49 PU=3.61 LR=7.35 LRA=35.8





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005