



Customer information packet

EM3710T-5

7.5HP, 1770RPM, 3PH, 60HZ, 213T, 3738M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	7.600 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.6 a

Part detail

Revision	G
Type	AC
Mech. spec.	37H244
Base	
Status	PRD/A
Elec. spec.	37WGR907
Layout	37LYH244
Eff. date	05-02-2024
CD Diagram	CD0006
Poles	04
Leads	3#14
Proprietary	False
Created date	12-10-2015

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3738M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.02 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441L

CAT.NO. EM3710T-5

SPEC. 37H244R907G1

HP 7.5

VOLTS 575

AMP 7.6

RPM 1770

FRAME 213T HZ 60 PH 3

SER.F. 1.15 CODE J DES A CL F

NEMA-NOM-EFF 91.7 PF 82

RATING 40C AMB-CONT

CC 010A

DE 6307 ODE 6206

ENCL TEFC SN

VPWM INVERTER READY

CT6-60H(10:1)VT3-60H(20:1)

Accessories

Part number	Description	Multiplier
37-3301	C FACE KIT	P1

AC Induction Motor Performance Data

Record # 54313

Typical performance - not guaranteed values

Winding: 37WGR907-R004				Type: 3738M		Enclosure: TEFC			
Nameplate Data				575 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		7.5		Full Load Torque		22.2 LB-FT			
Volts		575		Start Configuration		direct on line			
Full Load Amps		7.6		Breakdown Torque		71 LB-FT			
R.P.M.		1770		Pull-up Torque		32.6 LB-FT			
Hz		60 Phase		3		Locked-rotor Torque		43 LB-FT	
NEMA Design Code		A		KVA Code		J		Starting Current	56.9 A
Service Factor (S.F.)		1.15		No-load Current		3.48 A			
NEMA Nom. Eff.		91.7		Power Factor		82		Line-line Res. @ 25°C	2.22 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		63°C			
S.F. Amps				Temp. Rise @ S.F. Load		77°C			
				Locked-rotor Power Factor		37.3			
				Rotor inertia		0.934 LB-FT2			

Load Characteristics 575 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	42	63	75	80	83	84	82
Efficiency	87.1	91.7	91.9	92.1	91	89.9	91.4
Speed	1793	1786	1778	1770	1760	1750	1764
Line amperes	3.9	4.84	6.1	7.61	9.29	11.1	8.62


ABB Motors and Mechanical Inc.


WINDING # 37WGR907

Typical performance - not guaranteed values.




7.5 HP 3 PH 60 HZ 1770 RPM 575 V 3738M

TORQUES (LB-FT): PO=71 PU=32.6 LR=43 LRA=56.9





CD0006



- NOTES:
1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
 2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10: 24: 49 02/19/2019	BY: ENBRIRO
MTL: —		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1