



Customer information packet

EM3770T

7.5HP, 1770RPM, 3PH, 60HZ, 213T, 0738M, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV NEMA PREMIUM NEMA_PREMIUM UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.500 A @ 460.0 V 20.000 A @ 208.0 V 19.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part detail

Revision	F
Type	AC
Mech. spec.	07H002
Base	
Status	PRD/A
Elec. spec.	07WGT510
Layout	07LYH002
Eff. date	04-29-2024
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	11-11-2020

Heater Indicator	No Heater
High Voltage Full Load Amps	9.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0738M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.45 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA

CAT.NO.	EM3770T									
SPEC	07H002T510									
HP	7.5									
VOLTS	230/460									
AMPS	19/9.5									
RPM	1770									
FRAME	213T		HZ	60			PH	3		
SF	1.15		CODE	J	DES	A	CLASS	F		
NEMA NOM. EFF	91.7		PF	81						
RATING	40C AMB-CONT									
CC	010A									
ENCL	TEFC		SER							
DE	6307		ODE	6206						
VPWM INVERTER READY			SFA 21.4/10.7							
CT6-60H(10:1)VT3-60H(20:1										
	50HZ 7.5HP 190/380V 22.4/11.2A								SF1.0	

Accessories

Part number	Description	Multiplier
37-1304	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 85534

Preliminary Data Sheet

Winding: 07WGT510-R001				Type: 0738M		Enclosure: TEFC	
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		7.5		Full Load Torque		22.3 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		19/9.5		Breakdown Torque		69.1 LB-FT	
R.P.M.		1770		Pull-up Torque		28.7 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		39.1 LB-FT	
NEMA Design Code		A	KVA Code	J	Starting Current		67.4 A
Service Factor (S.F.)		1.15		No-load Current		4.07 A	
NEMA Nom. Eff.		91.7	Power Factor	81	Line-line Res. @ 25°C		1.55 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		48°C	
S.F. Amps		21.4/10.7		Temp. Rise @ S.F. Load		62°C	
				Locked-rotor Power Factor		41.2	
				Rotor inertia		0.934 lb-ft²	

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	44	66	76	81	84	85	83
Efficiency	88	91.7	92.2	91.7	90.7	89.3	90.9
Speed	1792	1785	1777	1769	1759	1749	1761
Line amperes	4.61	5.85	7.48	9.43	11.6	13.9	10.7

ABB Motors and Mechanical Inc.

WINDING # 07WGT510

Typical performance - not guaranteed values.

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 0738M

TORQUES (LB-FT): PO=69.1 PU=28.7 LR=39.1 LRA=67.4





