



Customer information packet

EM4107T-8

44M 2P TEFC HOR 284TS SE

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	284TS
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	CSA EEV UR NEMA_PREMIUM NEMA PREMIUM
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	66.000 A @ 200.0 V 64.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	66.0 a

Part detail

Revision	L
Type	AC
Mech. spec.	09F629
Base	
Status	PRD/A
Elec. spec.	09WGT586
Layout	09LYF629
Eff. date	09-11-2024
CD Diagram	CD0695
Poles	02
Leads	6#6
Proprietary	False
Created date	08-21-2019

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 6 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0944M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	24.77 IN
Power Factor	88
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3515 rpm
Speed Code	Single Speed
Starting Method	Part Winding
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3443L													
CAT.NO.	EM4107T-8				CUST. P/N							ENCL	TEFC
SPEC.	09F629T586G1		CC	010A	FRAME	284TS		SER.NO.					
HP	25			CLASS	F	HZ	60						
R.P.M.	3515			PH	3	DES	A						
VOLTS	200				CODE	H		ODE BRG	6208	DE BRG	6311		
AMPS	66												
RATING	40C AMB-CONT			NEMA NOM. EFF.				91.7		GREASE	POLYREX EM		
P.F.	88	SER.F.	1.15		VPWM INVERTER READY								
HTR-VOLTS		HTR-AMPS					HTR-WATTS						

Accessories

Part number	Description	Multiplier
09-1310	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 78305

Typical performance - not guaranteed values

Winding: 09WGT586-R001				Type: 0944M		Enclosure: TEFC	
Nameplate Data				200 V, 60 Hz: Single Voltage Motor			
Rated Output (HP)		25		Full Load Torque		37.39 LB-FT	
Volts		200		Start Configuration		direct on line	
Full Load Amps		66		Breakdown Torque		139 LB-FT	
R.P.M.		3515		Pull-up Torque		52.41 LB-FT	
Hz		60		Phase		3	
NEMA Design Code		A		KVA Code		H	
Service Factor (S.F.)		1.15		Starting Current		461 A	
NEMA Nom. Eff.		91.7		Power Factor		88	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		75°C	
S.F. Amps				Temp. Rise @ S.F. Load		93°C	
				Locked-rotor Power Factor		29.1613	
				Rotor inertia		1.12 lb-ft²	

Load Characteristics 200 V, 60 Hz, 25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	62	81	87	90	90	90	90
Efficiency	88.3	91.8	92.2	91.7	90.7	89.5	91.1
Speed	3579	3559	3540	3518	3494	3468	3504
Line amperes	25.28	36.7	50.52	65.58	82.26	100	75.6


ABB Motors and Mechanical Inc.


WINDING # 09WGT586

Typical performance - not guaranteed values.



25 HP 3 PH 60 HZ 3515 RPM 200 V 0944M

TORQUES (LB-FT): PO=139 PU=52.41 LR=67.2 LRA=461







CD0695



START CONNECTION



RUN CONNECTION



- NOTES:
1. MOTOR MAY BE WYE CONNECTED OR DELTA CONNECTED.
 2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
 5. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS

REV. LTR: C BY: JLP REVISED: 01/21/99 3:19 TDR: 0171435

S69000

FILE: AAA00005151

MDL: -

MTL: -

BALDOR ELECTRIC Co.

3PH, SV, 6 LEADS, PART WINDING START

CD0695