



Customer information packet

EM3660T

3HP, 3470RPM, 3PH, 60HZ, 182T, 0618M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	182T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CURUSEEV NEMA PREMIUM
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.700 A @ 460.0 V 7.400 A @ 230.0 V 7.800 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.7 a

Part detail

Revision	C
Type	AC
Mech. spec.	06C101
Base	
Status	PRD/A
Elec. spec.	06WGY620
Layout	06LYC101
Eff. date	08-05-2024
CD Diagram	CD0005
Poles	02
Leads	9#16
Proprietary	False
Created date	12-17-2020

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0618M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	15.24 IN
Power Factor	87
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3470 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1259L											
CAT.NO.	EM3660T										
SPEC.	06C101Y620G1										
HP	3										
VOLTS	230/460										
AMP	7.4/3.7										
RPM	3470										
FRAME	182T		HZ	60				PH	3		
SER.F.	1.15		CODE	J	DES	B		CL	F		
NEMA-NOM-EFF	86.5		PF	87							
RATING	40C AMB-CONT										
CC	010A										
DE	6206		ODE	6205							
ENCL	TEFC		SN								

Accessories

Part number	Description	Multiplier
36-1749	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 85919

Preliminary Data Sheet

Winding: 06WGY620-R001			Type: 0618M		Enclosure: TEFC			
Nameplate Data			460 V, 60 Hz: High Voltage Connection					
Rated Output (HP)		3	Full Load Torque		4.54 LB-FT			
Volts		230/460	Start Configuration		direct on line			
Full Load Amps		7.4/3.7	Breakdown Torque		23.1 LB-FT			
R.P.M.		3470	Pull-up Torque		9.16 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		12.7 LB-FT		
NEMA Design Code		B	KVA Code	J	Starting Current		29.1 A	
Service Factor (S.F.)		1.15	No-load Current		1.66 A			
NEMA Nom. Eff.		86.5	Power Factor		87	Line-line Res. @ 25°C		6.35 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		50°C	
S.F. Amps		20/10	Temp. Rise @ S.F. Load		66°C			
			Locked-rotor Power Factor		67.5			
			Rotor inertia		0.0795 lb-ft²			

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	47	70	82	87	90	91	89
Efficiency	80.2	86.4	87.5	86.7	85.3	83.2	85.9
Speed	3568	3538	3506	3469	3429	3386	3446
Line amperes	1.83	2.3	2.93	3.69	4.55	5.51	4.19

ABB Motors and Mechanical Inc.

WINDING # 06WGY620

Typical performance - not guaranteed values.

3 HP 3 PH 60 HZ 3470 RPM 460 V 0618M

TORQUES (LB-FT): PO=23.1 PU=9.16 LR=12.7 LRA=29.1





