



Customer information packet

EM4348T

40HP, 890RPM, 3PH, 60HZ, 365T, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	365T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	900 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CCSAUSEEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Current @ Voltage	104.000 A @ 230.0 V 111.000 A @ 208.0 V 52.000 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	52.0 a
Insulation Class	F
Inverter Code	Inverter Ready
IP Rating	NONE
KVA Code	G
Lifting Lugs	Standard Lifting Lugs

Part detail

Revision	K
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	A36WG1044
Layout	617428-077
Eff. date	11-16-2023
CD Diagram	416820-002
Poles	08
Leads	3#6,6#8
Proprietary	False
Created date	11-23-2015


Motor Lead Quantity/Wire Size	3 @ 6 AWG
Motor Standards	NEMA
Motor Type	A36062M
Mounting Arrangement	F1
Number of Poles	8
Overall Length	33.47 IN
Power Factor	77
Product Family	General Industrial
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Service Factor	1.15
Shaft Diameter	2.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	890 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Nameplate

NP2496L	
MOBIL POLYREX EM	



NP2349L

SPEC NO.	A36-7200-1044			CAT.NO.	EM4348T				FRAME	365T	
HP	40	VOLTS	230/460		PHASE	3	DESIGN	B	TYPE	P	
RPM	890	AMPS	104/52		HZ	60	AMB	40	SF	1.15	
DRIVE END BEARING	65BC03J30X			DUTY	CONT	INSUL.CLASS		F			
OPP D.E. BEARING	65BC03J30X			ENCL	TEFC	CODE	G				
SER.NO.				POWER FACTOR		77	NEMA-NOM-EFFICIENCY				93
						MAX CORR KVAR		15	GUARANTEED EFFICIENCY		91.7
						NEMA NOM/CSA QUOTED EFF					
						MOTOR WEIGHT				875	



416820-002

A-C MOTOR
CONNECTION DIAGRAM
STANDARD 9 LEAD DELTA-CONNECTED



(N.P. 1575-B)

REV. DESC: FONT CHANGE FOR PDF SEARCHABLE		
REV. LTR: A	VERSION: 01	TDR: 000001009382
FILE: \MGA\00000\661	REVISED: 02:46:19 02/13/2020	BY: MGHMTT
MTL: —		

BALDOR - RELIANCE®

CONN DIAG — STANDARD 9 LEAD, DELTA-CONNECTED
SH 1 of 1

416820-002