



Customer information packet

EM3774T-8

10HP, 1760RPM, 3PH, 60HZ, 215T, 0748M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM CURUSEEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	28.000 A @ 200.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	28.0 a
Insulation Class	F
Inverter Code	Inverter Ready

Part detail

Revision	AF
Type	AC
Mech. spec.	07H002
Base	
Status	PRD/A
Elec. spec.	07WGY762
Layout	07LYH002
Eff. date	04-29-2024
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	05-10-2010

KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0748M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.45 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1259L											
CAT.NO.	EM3774T-8										
SPEC.	07H002Y762G1										
HP	10										
VOLTS	200										
AMP	28										
RPM	1760										
FRAME	215T		HZ	60			PH	3			
SER.F.	1.15	CODE	H	DES	B	CL	F				
NEMA-NOM-EFF	91.7	PF	83								
RATING	40C AMB-CONT										
CC	010A										
DE	6307		ODE	6206							
ENCL	TEFC	SN									

Accessories

Part number	Description	Multiplier
37-1304	C FACE KIT	A8

AC Induction Motor Performance Data

Record # 31203

Typical performance - not guaranteed values

Winding: 07WGY762-R001			Type: 0748M		Enclosure: TEFC			
Nameplate Data			200 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		10	Full Load Torque		29.8 LB-FT			
Volts		200	Start Configuration		direct on line			
Full Load Amps		28	Breakdown Torque		80.4 LB-FT			
R.P.M.		1760	Pull-up Torque		39.9 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		52.2 LB-FT		
NEMA Design Code		B	KVA Code	H	Starting Current		186 A	
Service Factor (S.F.)		1.15	No-load Current		10.2 A			
NEMA Nom. Eff.		91.7	Power Factor		83	Line-line Res. @ 25°C		0.207 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		65°C		
S.F. Amps				Temp. Rise @ S.F. Load		81°C		
				Locked-rotor Power Factor		35		
				Rotor inertia		1.18 LB-FT2		

Load Characteristics 200 V, 60 Hz, 10 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	50	71	80	83	85	85	84
Efficiency	90.3	92.6	93.1	92.2	90.9	89	91.4
Speed	1791	1782	1774	1763	1751	1737	1756
Line amperes	12	16.3	21.7	28	35.1	43.1	32.3


ABB Motors and Mechanical Inc.

WINDING # 07WGY762


Typical performance - not guaranteed values.

10 HP 3 PH 60 HZ 1760 RPM 200 V 0748M



TORQUES (LB-FT): PO=80.4 PU=39.9 LR=52.2 LRA=186



6/9/2025 ACPERF, record # 31203



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007

REV. LTR: E

VERSION: 01

TDR: 000001099922

FILE: \AAA\00005\141

REVISED: 10: 24: 49 02/19/2019

BY: ENBRIRO

MTL: -



BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1