



Customer information packet

EMVM3546C

0.75KW, 1770RPM, 3PH, 60HZ, D80C, 3520M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	D80C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 KW @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.600 A @ 460.0 V 3.200 A @ 208.0 V 3.200 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	85.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Frame Prefix	D
Front Shaft Indicator	None
Heater Indicator	No Heater

Part detail

Revision	A
Type	AC
Mech. spec.	35M366
Base	
Status	PRD/A
Elec. spec.	35WGG004
Layout	35LYM366
Eff. date	04-30-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	03-11-2022

High Voltage Full Load Amps	1.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Motor Type	3520M
Mounting Arrangement	B14
Number of Poles	4
Overall Length	11.38 IN
Power Factor	69
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.748 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3386L						
CAT.NO.	EMVM3546C					
SPEC.	35M366G004G1					
IEC FRAME	D80C	KW	0.75			
VOLTS	230/460					
AMP	3.2/1.6					
RPM	1770		ENCL		TEFC	
HZ	60	PH	3	CL	F	
SER.F.	1.15	DES	B	CODE	N	
NEMA-NOM-EFF	85.5	I.P.	54			
RATING	40C AMB-CONT					
CC	010A	USABLE AT 208V				N/A
DE	6205	ODE	6203			
SER. #						
	SFA 3.4/1.7					

AC Induction Motor Performance Data

Record # 87097

Preliminary Data Sheet

Winding: 35WGG004-R011			Type: 3520M		Enclosure: TEFC			
Nameplate Data			460 V, 60 Hz: High Voltage Connection					
Rated Output (KW)		.75	Full Load Torque		2.99 LB-FT			
Volts		230/460	Start Configuration		direct on line			
Full Load Amps		3.2/1.6	Breakdown Torque		13.68 LB-FT			
R.P.M.		1770	Pull-up Torque		7.85 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		9.01 LB-FT		
NEMA Design Code		B	KVA Code	N	Starting Current		14.13 A	
Service Factor (S.F.)		1.15	No-load Current		1.08 A			
NEMA Nom. Eff.		85.5	Power Factor		69	Line-line Res. @ 25°C		16.9 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		24°C	
S.F. Amps		3.4/1.7	Temp. Rise @ S.F. Load		28°C			
			Locked-rotor Power Factor		61.5			
			Rotor inertia		0.144 lb-ft²			

Load Characteristics 460 V, 60 Hz, 0.75 KW

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	48	60	69	76	79	73
Efficiency	72.1	81.7	84.6	85.7	85.5	84.7	85.6
Speed	1791	1784	1776	1768	1759	1750	1763
Line amperes	1.11	1.22	1.38	1.6	1.83	2.1	1.74

ABB Motors and Mechanical Inc.

WINDING # 35WGG004

Typical performance - not guaranteed values.

0.75 KW 3 PH 60 HZ 1770 RPM 460 V 3520M

TORQUES (LB-FT): PO=13.68 PU=7.85 LR=9.01 LRA=14.13





