



Customer information packet

KEL11205

.33HP, 3475RPM, 1PH, 60HZ, 56C, 3413LC, OPEN, F

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.330 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 115.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.500 A @ 230.0 V 1.600 A @ 208.0 V 3.000 A @ 115.0 V
Design Code	N
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	70.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Drip Cover Mounting
Front Shaft Indicator	None
Heater Indicator	No Heater

Part detail

Revision	M
Type	AC
Mech. spec.	34F534
Base	
Status	PRD/A
Elec. spec.	34WGR144
Layout	34LYF534
Eff. date	10-29-2024
CD Diagram	CD0055
Poles	02
Leads	6#18
Proprietary	False
Created date	10-03-2014

High Voltage Full Load Amps	1.5 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3413LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.85 IN
Power Factor	97
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.35
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3475 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP3155L														
CAT.NO.	KEL11205													
SPEC.	34F534R144G1													
HP	.33													
VOLTS	115/208-230													
AMP	3/1.6-1.5													
RPM	3475													
FRAME	56C			HZ	60			PH	1					
SER.F.	1.35	CODE		H	DES	N	CL	B						
F.L. AVG. EFF.	70.5	PF		97										
RATING	40C AMB-CONT													
CC														
DE	6203			ODE	6203									
ENCL	OPEN	SN												
SFA 3.9/2.1-1.95														

AC Induction Motor Performance Data

Record # 47424

Typical performance - not guaranteed values

Winding: 34WGR144-R002			Type: 3413LC		Enclosure: OPEN		
Nameplate Data				115 V, 60 Hz: Low Voltage Connection			
Rated Output (HP)		.33		Full Load Torque		0.495 LB-FT	
Volts		115/208-230		Start Configuration		direct on line	
Full Load Amps		3/1.6-1.5		Breakdown Torque		1.37 LB-FT	
R.P.M.		3475		Pull-up Torque		1.11 LB-FT	
Hz	60	Phase	1	Locked-rotor Torque		1.63 LB-FT	
NEMA Design Code		N	KVA Code	H	Starting Current		21.7 A
Service Factor (S.F.)		1.35		No-load Current		0.91 A	
NEMA Nom. Eff.		70.5	Power Factor	97	Line-line Res. @ 25°C		1.8711 Ω A Ph 3.6847 Ω B Ph
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		14°C	
S.F. Amps		3.9/2.1-1.95		Temp. Rise @ S.F. Load		17°C	

Load Characteristics 115 V, 60 Hz, 0.33 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	97	98	98	99	99	98	99
Efficiency	43.3	61.5	70.3	74.5	76.4	77.7	76.9
Speed	3567.1	3549.9	3526.5	3501.3	3474.4	3445.4	3463
Line amperes	1.29	1.76	2.32	2.91	3.54	4.2	3.8

ABB Motors and Mechanical Inc.

WINDING # 34WGR144

Typical performance - not guaranteed values.

0.33 HP 1 PH 60 HZ 3475 RPM 115 V 3413LC

TORQUES (LB-FT): PO=1.37 PU=1.11 LR=1.63 LRA=21.7





